


6 Watts

- International Medical Approvals
- 4000 VAC Reinforced Insulation
- Meets IEC60601-1, 3rd Edition
- 2 MOPP Isolation at 250 VAC
- 2 μ A Patient Leakage Current
- DIP24 Package
- EN55011 Level A With No External Components
- 3 Year Warranty



Dimensions:

JHL06:
1.25 x 0.80 x 0.40" (31.15 x 20.32 x 10.20 mm)


Models & Ratings

Input Voltage	Output Voltage	Output Current	Input Current		Maximum Capacitive Load ⁽³⁾	Efficiency ⁽⁴⁾	Model Number
			No Load ⁽¹⁾	Full Load ⁽²⁾			
10-17 V	5.0V	1200 mA	59 mA	640 mA	1200 μ F	78%	JHL0612S05
	12.0V	500 mA	92 mA	640 mA	500 μ F	78%	JHL0612S12
	15.0V	400 mA	79 mA	605 mA	400 μ F	82%	JHL0612S15
	\pm 12.0V	\pm 250 mA	52 mA	605 mA	\pm 250 μ F	83%	JHL0612D12
	\pm 15.0V	\pm 200 mA	68 mA	600 mA	\pm 250 μ F	83%	JHL0612D15
20-30 V	5.0V	1200 mA	38 mA	315 mA	1200 μ F	78%	JHL0624S05
	12.0V	500 mA	34 mA	300 mA	500 μ F	83%	JHL0624S12
	15.0V	400 mA	23 mA	290 mA	400 μ F	85%	JHL0624S15
	\pm 12.0V	\pm 250 mA	29 mA	295 mA	\pm 250 μ F	85%	JHL0624D12
	\pm 15.0V	\pm 200 mA	33 mA	295 mA	\pm 250 μ F	83%	JHL0624D15

Notes

1. Input current measured at nominal input voltage.
2. Input current measured at lowest input voltage.
3. Maximum capacitive load is per output.
4. Typical values.

Mechanical Details



Pin	Pin Connections	
	Single	Dual
2	-Vin	-Vin
3	-Vin	-Vin
9	No Pin	Common
10	Trim	Trim
11	No Pin	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin	+Vin
23	+Vin	+Vin

Notes

1. All dimensions are in inches (mm)
2. Weight: 0.04 lbs (20 g) approx.
3. Pin diameter: 0.02 \pm 0.002 (0.5 \pm 0.05)
4. Pin pitch tolerance: \pm 0.014 (\pm 0.35)
5. Case tolerance: \pm 0.02 (\pm 0.5)

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	10		17	VDC	12 V nominal
	20		30	VDC	24 V nominal
Input Current					See Models and Ratings table
Inrush Current			25	A	At 30VDC input
Input Filter	Pi type				
Patient Leakage Current			2	µA	
Undervoltage Lockout	On at >8.8V. Off <8.3V				12 V models
	On at >17.5V. Off <17.0V				24 V models
Input Surge			25	VDC	12 V models for 3 s
			50	VDC	24 V models for 3 s

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	5		30	V	See Models and Ratings table
Output Voltage Trim			±10	%	Via external resistors, see Application Notes
Initial Set Accuracy			±1	%	on V1
			±2	%	on V2 of dual output models
Minimum Load	0			A	No minimum load required
Start Up Delay		5		ms	
Start Up Rise Time		2		ms	
Line Regulation			±0.3	%	
Load Regulation			±1	%	0 - 100% load
Cross Regulation			±4	%	On dual output models with one output set to 50% load and the other varied from 10% to 100% load (D05 20% to 100%)
Transient Response			4	% deviation	Recovery to within 1% in <500 µs for a 50% load change at 0.25 A/µs rate
Ripple & Noise			1	% pk-pk	20 MHz bandwidth
Short Circuit Protection					Trip & Restart (hiccup mode), auto recovery
Overload Protection	120		200	%	Trip & Restart (hiccup mode)
Overvoltage Protection	115		140	%	
Temperature Coefficient			0.03	%/°C	

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		80		%	See Models and Ratings table
Isolation	4000			VAC	For 1 min. Double/reinforced with a working voltage of 250 VAC. Meets 2 x MOPP per 3rd edition of IEC60601-1 5000 VAC for 10 ms in accordance with IEC60664-1
Patient Leakage Current			2	µA	
Input to Output Capacitance			20	pF	
Switching Frequency		250		kHz	
Power Density			15	W/in ³	
Mean Time Between Failure		>1		MHrs	MIL-HDBK-217F, +25 °C GB
Weight		0.04 (20.0)		lb (g)	

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-20		+80	°C	See derating curve
Storage Temperature	-40		+100	°C	
Case Temperature			+100	°C	
Humidity	5		90	%RH	Non-condensing
Cooling					Natural convection
Shock	±3 shocks in each plane, total 18 shocks of 30 g : 11 ms halfsine. Conforms to EN60068-2-27 & EN60068-2-47				
Vibration	10-500 Hz at 2 g sweep and endurance at resonance in all 3 planes. Conforms to EN60068-2-6				

EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55011	Level A	
Radiated	EN55011	Level A	

EMC: Immunity


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Immunity	IEC60601-1-2	Ed 4.0: 2014	As Below	
ESD Immunity	EN61000-4-2	±8 kv Contact, ±15 kv Air	A	
Radiated Immunity	EN61000-4-3	10 V/m	A	80 MHz - 2.7 GHz plus discrete communication proximity field frequencies
EFT/Burst	EN61000-4-4	2	A	
Surges	EN61000-4-5	1	A	
Conducted Immunity	EN61000-4-6	3 Vm	A	
Magnetic Fields	EN61000-4-8	30 A/m	A	
Safety Approvals	ANSI/AMMI ES60601-1 3rd Edition, CSA-22.2 No.60601-1:2008, IEC60601-1 3rd Edition			

Safety Approvals


Safety Agency	Safety Standard	Notes & Conditions
CB Report	IEC60601-1 Including Risk Management	Medical
UL	ANSI/AAMI ES60601-1 3rd Ed. & CSA C22.2, No.60601-1:2008	Medical
EN	EN60601-1	Medical

Application Notes

Derating Curve



External Output Trim



For 5 V output:
 Trim +10%, R = 3.4 k typical
 Trim -10%, R = 1.1 k typical

For 12 V output:
 Trim +10%, R = 5.9 k typical
 Trim -10%, R = 11.3 k typical

For 15 V output:
 Trim +10%, R = 8.4 k typical
 Trim -10%, R = 10.4 k typical

For ±12 V output:
 Trim +10%, R = 12.8 k typical
 Trim -10%, R = 9.5 k typical

For ±15 V output:
 Trim +10%, R = 18 k typical
 Trim -10%, R = 14.8 k typical

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[XP Power:](#)

[JHL0624S12](#) [JHL0624D12](#) [JHL0612S05](#) [JHL0612S12](#) [JHL0612D15](#) [JHL0612S15](#) [JHL0624D15](#) [JHL0624S15](#)
[JHL0612D12](#) [JHL0624S05](#)