



3169 - EXTENDED MALE STUD ELBOW BSPP AND METRIC THREAD



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
vacuum capability	755 mm Hg
body	TECHNICAL POLYMER
sub-base	NICKEL PLATED BRASS
'O'-rings	NBR
gripping ring	STAINLESS STEEL

[inch Part numbers](#)
[Convert to inch](#)
[Convert to oz](#)
[Reset Filters](#)

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3169 04 10	4	G1/8	5	13	8.5	22.5	19	.009
3169 04 13	4	G1/4	5.5	16	8.5	22.5	19	.014
3169 04 19	4	M5x0,8	3.5	8	8.5	23	19	.006
3169 06 10	6	G1/8	5	13	10.5	27	23	.011
3169 06 13	6	G1/4	5.5	16	10.5	27	23	.016
3169 06 19	6	M5x0,8	3.5	10	10.5	27.5	23	.008
3169 06 55	6	M7x1	4.5	10	10.5	26	23	.012
3169 08 10	8	G1/8	5	13	13.5	36	29.5	.018
3169 08 13	8	G1/4	5.5	16	13.5	33	29.5	.021
3169 08 17	8	G3/8	5.5	20	13.5	33	29.5	.028
3169 10 13	10	G1/4	5.5	16	16	40.5	34.5	.028
3169 10 17	10	G3/8	5.5	20	16	40.5	34.5	.036
3169 10 21	10	G1/2	7	24	16	40.5	34.5	.049
3169 12 13	12	G1/4	5.5	19	19	44.5	40.5	.044
3169 12 17	12	G3/8	5.5	20	19	42	40.5	.038
3169 12 21	12	G1/2	7	24	19	42	40.5	.043
3169 14 17	14	G3/8	5.5	22	22	51	46.5	.059
3169 14 21	14	G1/2	7	24	22	48.5	46.5	.063
3169 16 17	16	G3/8	7.5	27	27	82.5	52	.22
3169 16 21	16	G1/2	9	27	27	82.5	52	.206