


**Part Number: 503398-0891**

1.10mm Pitch microSD Memory Card Connector, Normal Mount SMT, Push-Push Type, 1.28mm Height



Series image - Reference only

<b>Status:</b>	Contact Molex
<b>Series:</b>	<a href="#">503398</a>
<b>Category:</b>	Memory Card Sockets
<b>Overview:</b>	<a href="#">microSD Memory Card Connector</a>

**Use With:**

microSD Card

**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:** Contains SVHC: No**Low-Halogen Status:** Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Contact Molex</b>
Category	Memory Card Sockets
Series	<a href="#">503398</a>
Component Type	Header & Ejector (Host)
Overview	<a href="#">microSD Memory Card Connector</a>
Product Name	microSD Card
Style	Push-Push
Type	N/A

**Physical**

Card Detection Switch	Yes
Circuits (Loaded)	8
Color - Resin	Black
Durability (mating cycles max)	10,000
Ejector Button	No
Ejector Button Side	N/A
Entry Angle	90° Angle
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Gold, Tin
PCB Locator	No
PCB Mounting Side	Normal
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.09mm
Ports	1
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount

**Electrical****(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	10V AC (RMS)/DC

**Material Info**

UPC	883906688820
-----	--------------

**Reference - Drawing Numbers**

Packaging Specification	SPK-503398-001
Product Specification	PS-503398-001, RPS-503398-001
Sales Drawing	SD-503398-001, SD-503398-002

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

---

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)