## **Specification of Crystal Unit**



1 NDK PART NUMBER NX2520SA-16.000000MHz-W1

2 CHIPSET MAKER FREESCALE

3 APPLICATION Wireless LAN, ZIGBEE

4 CHIPSET NAME MC13192

5 Type NX2520SA

6 Electrical characteristics

6.1 Nominal frequency(F0)6.2 Overtone order16.000MHzFundamental

6.3 Adjustment tolerance  $\pm 20 \times 10^{-6}$  max. (+25 °C)

6.4 Tolerance over the temperature range ±20×10<sup>-6</sup> max. (-40~+85 °C) The reference temperature shall be +25 °C.

 $\begin{array}{lll} 6.5 & \mbox{Equivalent resistance (R1)} & 120\Omega \mbox{ max.} \\ 6.6 & \mbox{Shunt Capacitance (C0)} & 7.0 \mbox{ pF max.} \\ 6.7 & \mbox{Maximum Drive Level} & 200 \mbox{$\mu$W max.} \end{array}$ 

7 Measurement circuit


7.2 Frequency measurement

7.1.1 Measuring instrument  $\pi$  circuit 7.1.2 Load capacitance(CL) 8pF 7.1.3 Level of drive 50 $\mu$ W

7.2 Equivalent resistance measurement

7.2.1 Measuring instrument  $\pi$  circuit 7.2.2 Load capacitance(CL) Series 7.2.3 Level of drive  $50\mu W$ 

## 8 Dimension



## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NDK:

NX2520SA-16.000000MHZ-W1