

TABLE 1 ,DIM INFORMATION

DASH No. Dim.	Amount of Pins	Dim.A	Dim.B
-000 06 XX LF	06	2.54	10.11
-000 10 XX LF	10	5.08	12.65
-000 12 XX LF	12	6.35	13.92
-000 14 XX LF	14	7.62	15.19
-000 16 XX LF	16	8.89	16.46
-000 20 XX LF	20	11.43	19.00
-000 26 XX LF	26	15.24	22.81
-000 30 XX LF	30	17.78	25.35

1

DASH No.	Dim.	Amount of Pin⊆	Dim.A	Dim.B
-000 34 XX	LF	34	20.32	27.89
-000 40 XX	LF	40	24.13	31.70
-000 44 XX	ΓĿ	44	26.67	34.24
-000 50 XX	LF	50	30.48	38.05
-000 60 XX	LF	60	36.83	44.40
-000 64 XX	LF	64	39.37	46.94
-000 68 XX	ΓF	68	41.91	49.48
-000 80 XX	LF	80	49.53	57.10
-000 A0 XX	LF	100	62.23	69.90





1. MATERIAL, HOUSING: HIGH TEMP PLASTIC, UL94-VO, BLACK TERMINAL: COPPER ALLOY, SQ=0.40±0.03MM

2. FINISH: TERMINAL: GOLD AT CONTACT, G/F OVER lum(40u")MIN Ni OVER ALL

3

- 3. SPEC.: PRODUCT SPEC: GS-12-629 PACKING SPEC: GS-14-1420
- 4. THE HSG. WILL WITHSTAND EXPOSURE TO 260C PEAK TEMP. FOR 10 SEC. IN A WAVE SOLDER APPLICATION WITH A PCB.
- 5. PRODUCT NUMBERING:





Recommended P.C.B. Layout Layout Tolerance = ± 0.05 mm

mat	t'l. c	code	5			sur	fac	:e /	tol	era	nce	pro	jec	tio	nproduct family									
						ISD1	302	\vee	ISD1:	LO1 IS	0406	Ē	7 5	1	MIŇITEK									
ltr	lecr	n nd	bdr	da	te	tole	tolerances unless otherwise specified title																	
A	T09-	1117	S.LIN	09/1	5/09	lano	۽ م	3	0.X±	0.38			мм		1.27X1.27MM BTB HEADER						,			
в	T10-	0023	S.LIN	01/2	21/10	ung	2	-	0.XX:	±0.25		-		-										
С	T10-	0110	S.LIN	07/1	3/10	0°±2	<u>r</u> =	-	0.XX>	(±0.10	1	scale 8:1 SHROUDED RIGHT ANGLE						EI	1					
D	ELX-N-	010363	ΖK	01/1	6/12	dr	STE	ERLING	LIN	09/1	5/09			dwg	nc)		S	hee	2.t10	of 1	siz	Þ	
						eng	rste	ERLING	LIN	09/1	5/09	F	C	, İ	20021512 A							A4		
						chr	GF	AY HS	SIEH	091	5/09		Ľ	1		2002131					<u> </u>		H4	
						۵pp	d	JOSEP	н	09/1	5/09		<u> </u>	/	type Product Customer D				Draw	ing				
she	et	rev	'isio	nD																				
ind	ex	she	et	1																				

Α

4

PDS: Rev :D 3

2

2.30

1.20

1.27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

20021512-00006T1LF 20021512-00010T1LF 20021512-00012T1LF 20021512-00014T1LF 20021512-00016T1LF
<u>20021512-00020T1LF</u> <u>20021512-00026T1LF</u> <u>20021512-00030T1LF</u> <u>20021512-00034T1LF</u> <u>20021512-00040T1LF</u>
<u>20021512-00044T1LF</u> <u>20021512-00050T1LF</u> <u>20021512-00060T1LF</u> <u>20021512-00064T1LF</u> <u>20021512-00068T1LF</u>
<u>20021512-00080T1LF</u> <u>20021512-000A0T1LF</u> <u>20021512-00006T4LF</u> <u>20021512-00010T4LF</u> <u>20021512-00012T4LF</u>
<u>20021512-00014T4LF</u> <u>20021512-00016T4LF</u> <u>20021512-00020T4LF</u> <u>20021512-00026T4LF</u> <u>20021512-00030T4LF</u>
20021512-00034T4LF 20021512-00040T4LF 20021512-00044T4LF 20021512-00050T4LF 20021512-00060T4LF
20021512-00064T4LF 20021512-00068T4LF 20021512-00080T4LF 20021512-000A0T4LF 20021512-00006T8LF
20021512-00010T8LF 20021512-00012T8LF 20021512-00014T8LF 20021512-00016T8LF 20021512-00020T8LF
20021512-00026T8LF 20021512-00030T8LF 20021512-00034T8LF 20021512-00040T8LF 20021512-00044T8LF
20021512-00050T8LF 20021512-00060T8LF 20021512-00064T8LF 20021512-00068T8LF 20021512-00080T8LF
20021512-000A0T8LF 20021512-00008T1LF