


5353928-2 Product Details

[Live Product Chat](#)



5353928-2

TE Part Number: 5353928-2

Active

[Add to Part List](#)

Universal Serial Bus (USB) Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Size = Standard
- A Series
- Receptacle
- Without Locking Feature
- 1 Ports

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [EMBOSS ASSY REVERSE TYPE USB CONN. REC. WITH COVER...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 0)
- [3D Model](#) (IGES, Version 0)
- [3D Model](#) (STEP, Version 0)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Size = Standard
- Gender = Receptacle
- Number of Ports = 1
- Orientation = Right Angle
- Number of Positions = 4

Mechanical Attachment:

- Mount Location = Bottom

Electrical Characteristics:

- Panel Ground Type = M2 Threaded Hole

Termination Related Features:

- Termination Method = Solder to PC Board

Body Related Features:

- [Series](#) = A
- Locking Feature = Without
- [Panel Ground](#) = With
- PCB Retention Method = SMT Hold Down
- Shell Plating = Bright Tin over Nickel
- Pick and Place Cover = With
- Locating Posts = With

Contact Related Features:

- Contact Termination Type = Surface Mount
- [Contact Mating Area Plating Material](#) = Gold Flash over Palladium Nickel
- Contact Mating Area Plating Thickness = 30 Microinches

Housing Related Features:

- [Housing Color](#) = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = Printed Circuit Board

Packaging Related Features:

- Panel Ground Location = Right/Left
- [Packaging Method](#) = Tape & Reel

Other:

- Brand = AMP