

Customer Information Sheet

DRAWING No.: M50-303XX42

SHEET 2 OF 2



IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



SPECIFICATIONS:

MATERIAL:

MOULDING = NYLON 6T, UL94V-0, BLACK
CONTACT = PHOSPHOR BRONZE
FINISH = 0.76-1.52µ NICKEL ALL OVER,
0.012µ MIN GOLD ON CONTACT AREA,
2.54-5.08µ 100% TIN ON TAILS

ELECTRICAL:

CURRENT RATING = 1A
VOLTAGE PROOF = 500V AC FOR ONE MINUTE
CONTACT RESISTANCE = 20mΩ MAX
INSULATION RESISTANCE = 1000MΩ MIN

MECHANICAL:



DURABILITY = 300 CYCLES MIN
CONTACT INSERTION FORCE = 1.17N MAX PER CONTACT
CONTACT WITHDRAWAL FORCE = 0.19N MIN PER CONTACT

ENVIRONMENTAL:


OPERATING TEMPERATURE = -40°C TO +105°C

PACKING:

TUBE (02 CONTACT SIZE PACKED IN BOX)
FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C029XX (LATEST ISSUE)



RECOMMENDED PCB LAYOUT (TOLERANCE = ±0.05)



ORDER CODE
M50-303XX42
No. OF CONTACTS: _____
02 TO 06, 08, 10, 20

MSP	I	02.08.16	-----
NAME	ISS.	DATE	C/NOTE
APPROVED:		M.PERREN	
CHECKED:		S.BENNETT	
DRAWN:		M.PERREN	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

1.27mm PITCH SIL VERTICAL
SOCKET

DRAWING NUMBER:

M50-303XX42

SHT
2 OF
2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M50-3031042](#) [M50-3030342](#) [M50-3030642](#) [M50-3032042](#) [M50-3030842](#) [M50-3030442](#) [M50-3030542](#) [M50-3030242](#)