SMD Seam Sealing Crystals 3.2 x 2.5 x 0.7 mm AM Series

Features


- · Reliable seam sealed ceramic package.
- · Wide operating temperature range.
- · Superior performance and stringent reliability in harsh environment.
- · Application: TPMS, ECM, ABS and sensor modules.
- · Compact size.
- · RoHS Compliant / Pb Free.





Electrical Specifications	
ltem / Type	AM
Frequency Range	9.84~62.4 MHz
Overtone	Fundamental
Frequency Tolerance (at 25 °C)	\pm 10 ppm, \pm 20 ppm, \pm 50 ppm Max
Frequency Stability Over Operating Temperature Range	\pm 150 ppm Max. , or specify
Operating Temperature Range	- 40 \sim +125 $^{\circ}\text{C}$, or specify
Drive Level	10 μW (typical) ; 100 μW (Max.)
Load Capacitance	12 pF, or specify
Storage Temperature Range	- 40 ~ +125 °C
Reliability Standard	AEC-Q200

Equivalent Series Resistance(ESR)		
Fundamental		
10 ~ 12 MI	lz 180 Ω Max.	
12 ~ 20 MI	lz 100 Ω Max.	
20 ~ 30 MI	Hz 80 Ω Max.	
30 ~ 50 MI	Hz 60 Ω Max.	

Dimensions







Top View Suggested Layout

Units: mm