



NOTES

△ 図示の斜線部の範囲は、接点部のため傷、打痕、汚れなどをつけないようにしてください
 PLEASE DON'T DAMAGE, DON'T DENT, AND DON'T MAKE IT DIRTY, BECAUSE THE RANGE IN THE HATCHING AREA SHOWN IN FIGURE IS THE CONTACT AREA.

2. 適用電線違い：213029 シリーズ (ケーブルサイズ：AWG #26-28)
 SIMILAR PRODUCT THAT DIFFERENCE IS APPLICABLE CABLE SIZE: 213029 SERIES (CABLE SIZE: AWG #26-28)

TABLE 1

部品 PART	材質 MATERIAL	
ターミナル TERMINAL	銅合金 COPPER ALLOY	
	コンタクト部 CONTACT AREA	金めっき：表参照 (前めっき) GOLD PLATING: SEE CHART (PRE-PLATING)
	圧着部 CRIMPING AREA	錫めっき MATTE TIN PLATING
	リフロー処理(前めっき) REFLOW TREATMENT (PRE-PLATING)	
ニッケルめっき(下地)：1.27 micro-meters MIN NICKEL (UNDER PLATING)		

Ø1.00-1.28mm	AWG#24-26	0.76micro-meters MIN	ポリ袋 POLY BAG	バラ状 LOOSE	213028 7100
			リール REEL	連鎖状 CHAIN	213028 7000
		0.38micro-meters MIN	ポリ袋 POLY BAG	バラ状 LOOSE	213028 3100
			リール REEL	連鎖状 CHAIN	213028 3000
		0.10micro-meters MIN	ポリ袋 POLY BAG	バラ状 LOOSE	213028 1100
			リール REEL	連鎖状 CHAIN	213028 1000
絶縁被覆外径範囲 INS RANGE	適用電線範囲 WIRE RANGE	接点部金めっき厚 PLATING THK AT CONTACT AREA	梱包形態 PACKAGING	端子形状 FORM	オーダー番号 ORDER No

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS mm	SCALE NTS	CURRENT REV DESC:		
GENERAL TOLERANCES (UNLESS SPECIFIED)		 CLIK-MATE 1.5 CRIMP TERM GOLD 24-26		
ANGULAR TOL	± 3.0°			
4 PLACES	± 0.2	EC NO: 627408	2019/10/01	
3 PLACES	± 0.2	DRWN: MIKEDA01	2019/11/15	
2 PLACES	± 0.2	CHK'D: SAKIYAMA	2019/11/20	
1 PLACE	± 0.2	APPR: KOMURAKAMI	2019/11/20	
0 PLACES	± 0.2	INITIAL REVISION:		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRWN: MIKEDA01	2019/10/01	
THIRD ANGLE PROJECTION		APPR: KOMURAKAMI	2019/11/20	
DRAWING		SERIES	MATERIAL NUMBER	CUSTOMER
A3-SIZE		213028	SEE CHART	
SHEET NUMBER		1 OF 2		

適用製品及び各種仕様書

APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKING SPECIFICATION	PART NUMBER 213028 **00	SPECIFICATION NUMBER 2130289200-SPK
--------------------------------	----------------------------	--

適用ハウジング APPLICABLE HOUSING	SINGLE TYPE	
シリーズ番号 SERIES No	502578	
適用嵌合相手 MATE WITH	SMT	
	GOLD PLATING	
	VERTICAL	RIGHT ANGLE
シリーズ番号 SERIES No	213225	213226
製品仕様書 PRODUCT SPECIFICATION	5025780004-PS	
取扱説明書 APPLICATION SPECIFICATION	AS-502578-001(JAPANESE)/-002(ENGLISH)	

適用ハウジング APPLICABLE HOUSING	DUAL TYPE	
シリーズ番号 SERIES No	503149	
適用嵌合相手 MATE WITH	SMT	
	GOLD PLATING	
	VERTICAL	RIGHT ANGLE
シリーズ番号 SERIES No	213227	213228
製品仕様書 PRODUCT SPECIFICATION	5031490001-PS	
取扱説明書 APPLICATION SPECIFICATION	AS-503149-001(Japanese) 5031490000/PS/000 (English)	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS	SCALE	CURRENT REV DESC:				molex				
mm	NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 627408 DRWN: MIKEDA01 2019/10/01 CHK'D: SAKIYAMA 2019/11/15 APPR: KOMURAKAMI 2019/11/20 INITIAL REVISION: DRWN: MIKEDA01 2019/10/01 APPR: KOMURAKAMI 2019/11/20				CLIK-MATE 1.5 CRIMP TERM GOLD 24-26				
ANGULAR TOL	± 3.0 °					PRODUCT CUSTOMER DRAWING				
4 PLACES	± 0.2					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
3 PLACES	± 0.2					2130280000-SD		PSD	000	A
2 PLACES	± 0.2					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
1 PLACE	± 0.2					SEE CHART				2 OF 2
0 PLACES	± 0.2									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER			
			A3-SIZE	213028	SEE CHART		2 OF 2			