

## Completely pre-assembled Signal Towers / KOMPAKT 37

## K37cl sr cable EM Pulse tone 12VAC/DC YE



Part No.:	699.330.74
Series:	Kompakt 37



MECHANICAL DATA	
Height	141 mm
Diameter	38 mm
Materials	PC
Dome colour	Clear
Housing colour	Black
Protection category	IP65
Connection	Cable
cross-sectional area maximum	0,34mm <sup>2</sup> / 22AWG
Cable entry	Membrane grommet
Cable entry minimum	d = 1  mm
Cable entry maximum	d = 9 mm
Cable length	2000 mm
Tension relief	Pull-out protection
Type of fixing	Built-in mounting
Service life optical	50,000 h maximum
Acoustic service life	5,000 h minimum
Working temperature minimum	-20°C
Working temperature maximum	+50°C
UL Type Rating	Type 12 Type 4X
Weight with packaging	90 g
Product weight	90 g

ELECTRICAL DATA	
Operating voltage	12V
Operating voltage type	AC/DC
Operating voltage type	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	12 VDC
Rated operational current	225 mA
Rated inrush current	500 mA
Protection class	Protection class 2
Pollution degree	3 In the connection area: 2

OPTICAL DATA			
Light source	LED		
Light colour	Red Yellow		


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



Completely pre-assembled Signal Towers / KOMPAKT 37

## K37cl sr cable EM Pulse tone 12VAC/DC YE

Optical signal image	Permanent		
ACUSTICAL DATA			
Volume/dB(max) at 1m distance	80,0 dB (A)		
Acoustic signal image	Pulse tone		
Audio frequency	2900 Hz		



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.