



(SKC) COTES CARACTERISTIQUES SPECIALES
 SPECIAL KEY CHARACTERISTICS
 [Symbol] INDICATION DIMENSIONS S.P.C
 DENOTES S.P.C DIMENSIONS
 [Symbol] INDICATION DIMENSIONS CRITIQUES
 DENOTES CRITICAL DIMENSIONS
 [Symbol] INDICATION DIMENSIONS FONCTIONNELLES
 DENOTES FUNCTIONAL DIMENSIONS
 QUANTITE PAR FEUILLE INDIVIDUELLE
 QUANTITY PER INDIVIDUAL SHEET
 [Symbol] 1 [Symbol] 0 [Symbol] 4 (SKC) 0

NOTE :
 - MARKING "A" is used to identify "STANDARD" terminal
 - CRIMPING SPECIFICATION ACCORDING TO CS-64322-001

MARK	DESIGNATION	MATERIAL
2	BOX TERMINAL	STAINLESS STEEL thickness=0.15 mm
1	BODY TERMINAL	high conductivity copper alloy thickness=0.2 mm

PART NUMBER	CONTACT AREA	CRIMPING AREA	UNDERLAYER	CRIMPING RANGE (mm2)	A±0.2	B±0.2	rC ±0.15 / -0.1	D±0.2	E±0.2	rF±0.1	WEIGHT (g)
0643221029	Sn	Sn		0.75	2.5	2.4	0.6	3.3	2.8	0.75	0.119
0643221219	Au 1.27µ MINI	Sn	Ni	0.50	2.3	2.2	0.6	3.1	2.6	0.75	0.117
0643221039	Sn	Sn		0.50	2.3	2.2	0.6	3.1	2.6	0.75	0.117
0643221239	Au 1.27µ MINI	Sn	Ni	0.50	2.3	2.2	0.6	3.1	2.6	0.75	0.117
0643221019	Sn	Sn		0.22 TO 0.44	2.0	1.7	0.6	3.1	2.6	0.75	0.112
0643221229	Au 1.27µ MINI	Sn	Ni	0.22 TO 0.44	2.0	1.7	0.6	3.1	2.6	0.75	0.112

Revised Dwg
 EC NO: GZ008-0440
 DRAWN BY: JAUOU
 CHKD BY: PARLARI
 APPR'D BY: LECHEIR
 2008/05/19
 2008/05/19
 2008/05/19

GENERAL TOLERANCES (UNLESS SPECIFIED)
 mm INCH
 4 PLACES ± --- ± ---
 3 PLACES ± --- ± ---
 2 PLACES ± 0.10 ± ---
 1 PLACE ± 0.1 ± ---
 ANGULAR ± 2°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM ONLY
 DRAWN BY: DATE: FPARLARI 2007/09/17
 CHECKED BY: DATE: JDUCLIOS 2007/09/17
 APPROVED BY: DATE: LSTICKEIR 2007/09/17

SCALE: 20:1
 DESIGN UNITS: METRIC
 FIRST ANGLE PROJECTION

TITLE: CP RCPT TRM 0.6

MATERIAL NO.:
 DOCUMENT NO.:
 MOLEX INCORPORATED
 SD-64322-001

SHEET NO.: 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION