


| CKTS | A | B | C |
|------|----------------|----------------|----------------|
| 2 | .380 9.65 | .118 3.00 | .354 9.00 |
| 3 | .498 12.65 | .236 6.00 | .472 12.00 |
| 4 | .616 15.65 | .354 9.00 | .591 15.00 |
| 5 | .734 18.64 | .472 12.00 | .709 18.00 |
| 6 | .852 21.64 | .591 15.00 | .827 21.00 |
| 7 | .970 24.64 | .709 18.00 | .945 24.00 |
| 8 | 1.088 27.64 | .827 21.00 | 1.063 27.00 |
| 9 | 1.206 30.63 | .945 24.00 | 1.181 30.00 |
| 10 | 1.325 33.66 | 1.063 27.00 | 1.299 33.00 |
| 11 | 1.443 36.65 | 1.181 30.00 | 1.417 36.00 |
| 12 | 1.561 39.65 | 1.299 33.00 | 1.535 39.00 |

| CKTS | FINISH A | | FINISH B | | FINISH C | |
|------|--------------|-----------|--------------|-----------|--------------|-----------|
| | MATERIAL NO: | VOID CKTS | MATERIAL NO: | VOID CKTS | MATERIAL NO: | VOID CKTS |
| 02 | 43650-0227 | | 43650-0228 | | 43650-0229 | |
| 03 | 43650-0327 | | 43650-0328 | | 43650-0329 | |
| 04 | 43650-0427 | | 43650-0428 | | 43650-0429 | |
| 05 | 43650-0527 | | 43650-0528 | | 43650-0529 | |
| 06 | 43650-0627 | | 43650-0628 | | 43650-0629 | |
| 07 | 43650-0727 | | 43650-0728 | | 43650-0729 | |
| 08 | 43650-0827 | | 43650-0828 | | 43650-0829 | |
| 09 | 43650-0927 | | 43650-0928 | | 43650-0929 | |
| 10 | 43650-1027 | | 43650-1028 | | 43650-1029 | |
| 11 | 43650-1127 | | 43650-1128 | | 43650-1129 | |
| 12 | 43650-1227 | | 43650-1228 | | 43650-1229 | |
| 04 | 43650-0451 | 2,3 | | | | |
| 05 | 43650-0551 | 2,3,4 | | | | |
| 06 | | | 43650-0652 | 2,3,4,5 | | |



NOTES:

- HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, GLASS FILLED, UL94V-0, COLOR: BLACK
TERMINAL MATERIAL: BRASS ALLOY
- FINISH:
A = .000100/(0.00254) MIN. BRIGHT TIN OVER .000050/(0.00127) MIN. NICKEL
B = .000015/(0.00038) MIN. SELECT GOLD IN CONTACT AREA .000100/(0.00254) MIN. SELECT MATTE TIN ON SOLDER TAILS BOTH OVER .000050/(0.00127) NICKEL OVERALL
C = .000030/(0.00076) MIN. SELECT GOLD IN CONTACT AREA .000100/(0.00254) MIN. SELECT MATTE TIN ON SOLDER TAILS BOTH OVER .000050/(0.00127) NICKEL OVERALL
* THE PRIMARY SHIPPING CARTON WILL BE LABELED *COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC.* CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN/LEAD IN THE PC TAIL AREA.
- PRODUCT SPECIFICATION: PS-43650
- TRAY PACKAGED : SEE MOLEX DRAWING PK-70873-0811
- MATES WITH MICRO FIT (3.0) RECEPTACLE SERIES 43645
- PARTS CONFORM TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

| | |
|---------------------|-------------|
| ADD VOID PARTS | DESCRIPTION |
| EC NO: UCP2010-0036 | 2009/07/13 |
| DRWN:SSOUSEK | 2009/07/13 |
| CHKD:JBELL | 2009/07/13 |
| APPR:FSMITH | 2009/07/14 |
| D1 | REV |

| | |
|-----------------|--|
| QUALITY SYMBOLS | GENERAL TOLERANCES (UNLESS SPECIFIED) |
| ▽=0 | mm |
| ▽=0 | INCH |
| | 4 PLACES ± --- ± --- |
| | 3 PLACES ± --- ± .010 |
| | 2 PLACES ± 0.25 ± .014 |
| | 1 PLACE ± 0.36 ± --- |
| | ANGULAR ±1/2° |
| | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |

| | | | |
|-----------------|---|-------------------------|------------------------|
| DIMENSION STYLE | SCALE | DESIGN UNITS | THIRD ANGLE PROJECTION |
| IN/MM | --- | METRIC | |
| DRAWN BY | DATE | TITLE | |
| SAMIEC | 2000/07/07 | MICRO FIT (3.0) | |
| CHECKED BY | DATE | SINGLE ROW / VERTICAL | |
| MUELLER | 2000/07/07 | THRU HOLE / PEGS / TRAY | |
| APPROVED BY | DATE | MOLEX INCORPORATED | |
| EDGLEY | 2000/07/07 | MOLEX INCORPORATED | |
| MATERIAL NO. | DOCUMENT NO. | SHEET NO. | |
| SEE CHART | SD-43650-010 | 1 OF 1 | |
| SIZE | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | |