

Rectangular Type, BI-COLOR LED lamp
BL-L2519
■ Features:

- 2.0*5.0mm Rectangular Type BI-COLOR LED Lamps, with 3 leads.
- Ultra brightness.
- Choice of various viewing angles.
- Diffused, Transparent and Water clear lens are available.
- IC compatible /Low current capability.
- RoHs Compliance


■ Electrical-optical characteristics: (Ta=25°C) (Test Condition: IF=20mA)

Part Number	Chip			Lens Type	Forward Voltage(VF) Unit:V		Luminous Intensity (Iv) Unit:mcd		Viewing Angle 2θ 1/2(d eg)
	Emitted Color	Material	λ _p (nm)		Typ	Max	Min.	Typ	
					BL-L2519EGW	Orange	GaAsP/GaP	635	
	Green	GaP/GaP	570	2.20	2.50	4	15		
BL-L2519YGW	Yellow	GaAsP/GaP	585	2.10	2.50	4	15		
	Green	GaP/GaP	570	2.20	2.50	4	15		
BL-L2519UEUGW	Ultra Yellow	AlGaInP	630	2.10	2.50	80	160		
	Ultra Green	AlGaInP	574	2.20	2.50	60	110		


■ Absolute maximum ratings (Ta=25°C)

Parameter	E	UE	Y	G	UG	Unit
Forward Current I _F	25	30	25	30	30	mA
Power Dissipation P _d	60	65	60	65	75	mW
Reverse Voltage V _R	5	5	5	5	5	V
Peak Forward Current I _{PF} (Duty 1/10 @1KHZ)	150	150	150	150	150	mA
Operation Temperature T _{OPR}	-40 to +80					℃
Storage Temperature T _{STG}	-40 to +85					℃
Lead Soldering Temperature T _{SOL}	Max.260±5℃ for 3 sec Max. (1.6mm from the base of the epoxy bulb)					℃


Rectangular Type, BI-COLOR LED lamp

BL-L2519


■ Typical electrical-optical characteristics curves:




- (1) - GaAsP/GaAs 655nm/Red
- (2) - GaP 570nm/Yellow Green
- (3) - GaAsP/GaP 585nm/Yellow
- (4) - GaAsP/GaP 635nm/Orange & Hi-Eff Red
- (5) - GaP 700nm/Bright Red
- (6) - GaAlAs/GaAs 660nm/Super Red
- (8) - GaAsP/GaP 610nm/Super Red
- (9) - GaAlAs 880nm
- (10) - GaAs/GaAs & GaAlAs/GaAs 940nm
- (A) - GaN/SiC 430nm/Blue
- (B) - InGaN/SiC 470nm/Blue
- (C) - InGaN/SiC 505nm/Ultra Green
- (D) - InGaAlSiC 525nm/Ultra Green




FORWARD VOLTAGE (V)
FORWARD CURRENT VS.
FORWARD VOLTAGE





FORWARD CURRENT (mA)
RELATIVE LUMINOUS
INTENSITY VS. FORWARD
CURRENT



AMBIENT TEMPERATURE (°C)
FORWARD CURRENT VS. AMBIENT
TEMPERATURE



AMBIENT TEMPERATURE (°C)



NO TESTED free air temperature unless otherwise specified

2(.079)

