

High power thin film chip resistors (short side terminal)

■ HRG series

AEC-Q200 Compliant

Features

- Wider bottom terminal enabling higher power capability (short side terminal)
- Significantly larger power handling capability than existing same size resistors
Size: 3216, Power rating: 1.0W, Resistance range: 10 ~ 100K Ω
- Precision resistance tolerance: $\pm 0.1\%$, very small TCR: $\pm 25\text{ppm}/^\circ\text{C}$
- Thin film structure enabling low noise and anti-sulfur

Applications

- Power source related devices
- DC motors, inverters
- Robotics, Industrial control system



Thin film surface mount resistors

HRG series

◆ Part numbering system

HRG 3216 P - 1001 - B - T5

Series code

Size: HRG3216

Temperature coefficient of resistance

Nominal resistance value (E-24, E-96: all 4 digit)


Resistance tolerance

Packaging quantity:
T1(1,000pcs), T5(5,000pcs)

◆ Electrical Specification

Type	Power ratings	Temperature coefficient of resistance (ppm/ $^\circ\text{C}$)	Resistance range(Ω) Resistance tolerance		Maximum voltage	Resistance value series	Operating temperature	Packaging quantity
			$\pm 0.1\%$ (B)	$\pm 0.5\%$ (D)				
HRG3216	1.0W	± 25 (P)	$47 \leq R \leq 100\text{k}$		200V	E-24, E-96	$-55^\circ\text{C} \sim 155^\circ\text{C}$	T1 T5
		± 50 (Q)	$47 \leq R \leq 100\text{k}$	$10 \leq R \leq 100\text{k}$				

◆ Dimensions



Type	Size (inch)	L	W	a	b	t
HRG3216	1206	3.20 ± 0.20	1.60 ± 0.20	0.50 ± 0.25	1.10 ± 0.20	0.45 ± 0.10

(unit : mm)

◆ Reliability specification


Test items	Condition (test methods (JIS C5201-1))	Standard	
		≤47Ω	≥47Ω
Life (biased)	70°C, rated voltage, ^{*1} 90min on 30min off, 1000hours	±(0.5%+0.05Ω)	±(0.25%+0.01Ω)
High temperature high humidity	85°C, 85%RH, 1/10 of rated power, 90min on 30min off, 1000hours	±(0.25%+0.05Ω)	±(0.1%+0.01Ω)
Temperature shock	-55°C (30min) ~ 125°C (30min) 1000cycles	±(0.25%+0.05Ω)	±(0.1%+0.01Ω)
High temperature exposure	155°C, no bias, 1000hours	±(0.25%+0.05Ω)	±(0.1%+0.01Ω)
Resistance to soldering heat	260±5°C, 10 seconds (reflow)	±(0.25%+0.05Ω)	±(0.1%+0.01Ω)

*1 Rated voltage is given by $E = \sqrt{R \times P}$
 E= rated voltage (V), R=nominal resistance value(Ω), P=rated power(W)
 If rated voltage exceeds maximum voltage /element, maximum voltage/element is the rated voltage.


Thin film surface mount resistors

◆ Reliability test data


○ Biased life test




○ High temperature high humidity (biased)



○ Temperature shock




○ High temperature exposure



HRG series

◆ Derating Curve



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Susumu:

[HRG3216Q-16R0-D-T1](#) [HRG3216P-2260-D-T1](#) [HRG3216P-2800-D-T1](#) [HRG3216Q-38R3-D-T1](#) [HRG3216P-76R8-D-T1](#) [HRG3216P-6980-B-T1](#) [HRG3216P-2210-B-T1](#) [HRG3216P-5102-D-T1](#) [HRG3216Q-11R5-D-T1](#) [HRG3216P-2200-B-T1](#) [HRG3216Q-19R1-D-T1](#) [HRG3216P-8661-D-T1](#) [HRG3216P-1782-B-T1](#) [HRG3216P-3402-D-T1](#) [HRG3216P-1102-B-T1](#) [HRG3216Q-33R2-D-T1](#) [HRG3216P-2670-B-T1](#) [HRG3216P-2050-D-T1](#) [HRG3216P-4702-B-T1](#) [HRG3216P-1020-B-T1](#) [HRG3216P-6651-B-T1](#) [HRG3216P-4121-D-T1](#) [HRG3216P-2321-B-T1](#) [HRG3216P-7150-D-T1](#) [HRG3216P-1872-B-T1](#) [HRG3216P-3830-D-T1](#) [HRG3216P-2150-D-T1](#) [HRG3216Q-14R3-D-T1](#) [HRG3216P-1101-D-T1](#) [HRG3216P-4752-D-T1](#) [HRG3216P-48R7-D-T1](#) [HRG3216P-5601-D-T1](#) [HRG3216P-3090-D-T1](#) [HRG3216P-9101-B-T1](#) [HRG3216P-3601-D-T1](#) [HRG3216P-5602-D-T1](#) [HRG3216P-4702-D-T1](#) [HRG3216P-8871-B-T1](#) [HRG3216P-1500-B-T1](#) [HRG3216P-3010-B-T1](#) [HRG3216P-1270-B-T1](#) [HRG3216P-2941-D-T1](#) [HRG3216Q-39R0-D-T1](#) [HRG3216P-3010-D-T1](#) [HRG3216P-4301-D-T1](#) [HRG3216P-2201-D-T1](#) [HRG3216P-2431-B-T1](#) [HRG3216P-57R6-D-T1](#) [HRG3216P-56R0-B-T1](#) [HRG3216P-4221-B-T1](#) [HRG3216P-5362-D-T1](#) [HRG3216P-4751-B-T1](#) [HRG3216P-4751-D-T1](#) [HRG3216P-5111-D-T1](#) [HRG3216P-69R8-D-T1](#) [HRG3216P-1690-D-T1](#) [HRG3216P-7500-D-T1](#) [HRG3216P-3902-D-T1](#) [HRG3216P-1180-D-T1](#) [HRG3216P-2052-B-T1](#) [HRG3216P-4222-B-T1](#) [HRG3216P-1271-B-T1](#) [HRG3216P-5602-B-T1](#) [HRG3216P-8251-B-T1](#) [HRG3216P-7500-B-T1](#) [HRG3216P-1821-D-T1](#) [HRG3216P-1271-D-T1](#) [HRG3216P-1371-B-T1](#) [HRG3216P-6981-D-T1](#) [HRG3216Q-33R0-D-T1](#) [HRG3216P-1201-D-T1](#) [HRG3216P-61R9-B-T1](#) [HRG3216P-6192-B-T1](#) [HRG3216P-1431-B-T1](#) [HRG3216P-3602-B-T1](#) [HRG3216P-4750-D-T1](#) [HRG3216P-2402-D-T1](#) [HRG3216P-6810-D-T1](#) [HRG3216P-2551-B-T1](#) [HRG3216P-4641-B-T1](#) [HRG3216Q-18R2-D-T1](#) [HRG3216Q-10R5-D-T1](#) [HRG3216P-49R9-D-T1](#) [HRG3216P-8250-B-T1](#) [HRG3216P-1801-B-T1](#) [HRG3216Q-21R0-D-T1](#) [HRG3216P-4020-D-T1](#) [HRG3216P-1602-B-T1](#) [HRG3216P-97R6-D-T1](#) [HRG3216P-1782-D-T1](#) [HRG3216P-3920-D-T1](#) [HRG3216P-1600-D-T1](#) [HRG3216P-4642-B-T1](#) [HRG3216P-5102-B-T1](#) [HRG3216P-4300-D-T1](#) [HRG3216P-1402-B-T1](#) [HRG3216P-3401-D-T1](#) [HRG3216Q-11R0-D-T1](#) [HRG3216P-7321-D-T1](#) [HRG3216P-4321-D-T1](#)