## **192A.20CPE** | 192A.CPE High-performance diagonal cutters



## Standards: NF ISO 5749, ISO 5749, DIN ISO 5749, ASME B107.500 Description:

• New head design to increase durability and cutting capacity

• Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 192A.16CPE : 2.0mm 210 kg/mm<sup>2</sup> - 192A.18CPE : 2.2mm 205 kg/mm<sup>2</sup> - 192A.20CPE : 2.5mm 200 kg/mm<sup>2</sup>

• High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.

• High durability Carbon alloy steel, with induction hardened cutting edges.

• Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal lenght)

Chrome finish for corrosion
resistance

	192A.20CPE
Diameter D Maxi [mm]	2.5

Length L [mm]	200.0
Thickness E [mm]	11.5
Head Height C [mm]	22.0
Head Width B [mm]	28.0
Head Width B1 [mm]	22.0
Weight [Kg]	0.32