



Part Number : 430201210

Product Description : Micro-Fit 3.0 Plug Housing, Dual Row, 12 Circuits, UL 94V-2, Panel Mount Ears, Glow-Wire Capable, Black

Series Number : 43020

Status : Active

Product Category : Connector Housings

Documents & Resources

Drawings

Drawing 430201210_sd.pdf

3D Models and Design Files

3D Model 430201210_stp.zip

Specifications

Packaging Specification PK-43020-001-001.pdf

Product Specification 430450001-PS-KO-000.pdf

Product Specification 430450001-PS-SP-000.pdf

Product Specification PS-43045-001.pdf

Test Summary 430450005-TS-000.pdf

Test Summary 430450006-TS-000.pdf


Test Summary TS-43045-001-001.pdf

Test Summary TS-43045-003-001.pdf

Test Summary TS-46235-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	43020
Description	Micro-Fit 3.0 Plug Housing, Dual Row, 12 Circuits, UL 94V-2, Panel Mount Ears, Glow-Wire Capable, Black
Application	Power, Wire-to-Wire
Comments	<p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.</p>
Product Family	Micro-Fit Connector System
Product Name	Micro-Fit 3.0

UPC	889056704816
-----	--------------

Agency

CSA	LR19980
-----	---------

Physical

Circuits (maximum)	12
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.476/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Receptacle Housings	<u>43025</u>

Use with Part(s)

Description	Part Number
Micro-Fit Male Crimp Terminals	<u>43031</u>
Pre-Crimped Lead Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male	<u>214762</u>

Pre-Crimped Lead Micro-Fit 3.0 Male-to-Pigtail	<u>214763</u>
---	---------------

This document was generated on Jun 18, 2024