




WN 1452



380 HV



BN 20138

Pan head PT® screws

Torx®

Steel heat-treated 380 HV

zinc plated blue



ISO 4042


Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!

Further notice to residual risks can be found in the introduction section.



A technical brochure is available on request

Article#	ø nominal	d ₁	d ₂	k		A~	t min.	t max.	L
3268973	K18	1,8	3,6	1,3	T6	1,75	0,5	0,65	6
3351664	K20	2	3,6	1,5	T6	1,75	0,7	0,85	10
3218789	K22	2,2	4	1,4	T6	1,75	0,7	0,85	12
3351665									18
3216012	K30	3	5,6	2,1	T10	2,8	1	1,3	5
3216013									6
3216014									7
3216015									8
3216016									10
3216018									12
3216019									14
3216020									16
3216021									20
3216022	K35	3,5	6,9	2,3	T10	2,8	1,1	1,4	8
3216023									10
3216024									12
3216026									14
3216027									16
3216029									18
3216030									20
3216031									25
3216033									30
3216034	K40	4	7,5	2,6	T20	3,95	1,25	1,7	8
3216035									10
3216037									12
3216038									14

Article#	ø nominal	d ₁	d ₂	k		A~	t min.	t max.	L
3216039	K40	4	7,5	2,6	T20	3,95	1,25	1,7	16
3216040									18
3216041									20
3216042									25
3216044									30
3351666									40
3216045	K50	5	8,2	2,9	T20	3,95	1,4	1,8	10
3216046									12
3216047									14
3216048									16
3216050									20
3216051									25
3216052									30