


**Panasonic**  
ideas for life

## POLARIZED, MONOSTABLE SAFETY RELAY WITH FORCIBLY GUIDED DOUBLE CONTACTS

# SF2D RELAY



### Features

- Relay complies with EN 50205, Type A
- Overvoltage category as per IEC 60664-1 III / 4kV
- Rated voltage as per IEC 60664-1 basic insulation

	Pollution degree		
	2 inside	2 outside	3 inside
Coil-contact	400V	400V	250V
Contact-contact	400V	400V	400V

## SPECIFICATIONS

### Contact

Contact configuration (a = normally open / NO, b = normally closed / NC)	2a2b
Contact material	AgSnO <sub>2</sub> , with Au flash
Contact resistance (initial at 6V DC, 1A)	30mΩ
Making and breaking capacities (breathing hole open) <sup>1</sup>	6A 250V / 3A 24V
Max. switching voltage	400V
Min. switching voltage / min. switching current	10V / 10mA
Pick-up / drop-out / bounce time (approx. values at U <sub>nominal</sub> )	17.5 / 7 / 2ms
Mechanical life	10 <sup>7</sup> ops

### Coil

Operate / release voltage (% of U <sub>nominal</sub> at 20°C)	75% / 10%
Pick-up/nominal power consumption at 20°C	280 / 500mW

### Remarks

\*1 According to EN 60947-5-1: 1997, table 4 AC15 / DC13

\*2 Contact interruption <10μs

\*3 Breathing hole open

### Characteristics

Max. switching frequency (without load)	10Hz
Permissible ambient temperature at nominal power consumption	-40°C to +70°C
Upper temperature limit	105°C
Test voltage: open contact / contact-contact / contact-coil	2500 / 2500 / 2500V <sub>rms</sub>
Insulation resistance at 500V DC (initial)	10 <sup>9</sup> Ω
Shock resistance (11ms) NO/NC <sup>2</sup>	30G
Vibration resistance 10 – 200 Hz (10 – 55 Hz, amplitude 2 mm) <sup>2</sup>	10G
Degree of protection	IP67 / IP30 <sup>3</sup>


### Important: Relay characteristics may be influenced by:

- strong external magnetic fields
- magnetic conductive materials near the relay
- narrow top-to-top mounting (printed surface to printed surface)

### Note:

Suitable for most common washing methods except ultrasonic cleaning.

## ORDERING INFORMATION



# SF2D

## COIL DATA

Part number	Coil nominal voltage V DC	Operate voltage V DC	Release voltage V DC	Coil resistance $\Omega$ ( $\pm 10\%$ , 20°C)	Coil inductance (mH)
SF2D-DC5V	5	3.75	0.5	50	47
SF2D-DC9V	9	6.75	0.9	162	145
SF2D-DC12V	12	9.00	1.2	288	252
SF2D-DC18V	18	13.50	1.8	648	551
SF2D-DC21V	21	15.75	2.1	882	742
SF2D-DC24V	24	18.00	2.4	1152	959
SF2D-DC36V	36	27.00	3.6	2592	2097
SF2D-DC48V	48	36.00	4.8	4608	3654
SF2D-DC60V	60	45.00	6.0	7200	5612

## ELECTRICAL LIFE

Voltage	Current	Load type	Frequency	Duty cycle	No. of contacts	No. of ops.
230V AC	8A	AC 1	0.25Hz	25%	2 <sup>*2</sup>	85,000 <sup>*5</sup>
250V AC	6A	AC 1	0.33Hz	50%	4 <sup>*2</sup>	100,000 <sup>*5</sup>
230V AC	6A	AC 1	0.33Hz	10%	2 <sup>*3</sup>	200,000 <sup>*4,*5</sup>
230V AC	30 / 3A	AC 15 <sup>*1</sup>	0.33Hz	10%	1 <sup>*3</sup>	150,000 <sup>*4,*5</sup>
24V DC	8A	DC 1	0.33Hz	10%	2 <sup>*3</sup>	200,000 <sup>*4,*5</sup>
24V DC	3A	DC 13 <sup>*1</sup>	0.33Hz	10%	1 <sup>*3</sup>	50,000 <sup>*4,*5</sup>
24V DC	3A	L/R = 40ms	0.33Hz	10%	1 <sup>*3</sup>	100,000 <sup>*4,*5</sup>

\*1 EN 60947-5-1: 1997; table C.1

\*2 Breathing hole closed


\*3 Breathing hole open

\*4 Ambient temperature +70°C

\*5 Dielectric strength according to EN61810-1:2004.


## REFERENCE DATA

### Load limit curve




Loads in the range under the curve can be switched safely.  
The arc will extinguish before the opposite contact makes.

### Coil voltage characteristics




Permissible coil voltages and pick-up and drop-out characteristics at various ambient temperatures.


## Connection diagram and pcb bore hole data




Bottom view  
The contacts are shown in the deenergized condition.



## Contact current characteristics



## APPLICATION NOTES



Nipple

If required a breathing hole can be made in the cover by removing the nipple.  
However be aware that the degree of protection will reduce from IP67 to IP30!

**For Cautions for Use, see Relay Technical Information (see catalog).**