

# xckp2106p16

limit switch XCKP - cat's whisker - 1NC+1NO - snap  
- M16



## Main

|                               |                             |
|-------------------------------|-----------------------------|
| Range of product              | OsiSense XC                 |
| Series name                   | Standard format             |
| Product or component type     | Limit switch                |
| Device short name             | XCKP                        |
| Sensor design                 | Compact                     |
| Body type                     | Fixed                       |
| Head type                     | Multi-directional head      |
| Material                      | Plastic                     |
| Body material                 | Plastic                     |
| Head material                 | Zamak                       |
| Fixing mode                   | By the body                 |
| Movement of operating head    | Multi-directional           |
| Type of operator              | Spring return cat's whisker |
| Type of approach              | Multi-directional approach  |
| Number of poles               | 2                           |
| Contacts type and composition | 1 NC + 1 NO                 |
| Contacts operation            | Snap action                 |

## Complementary

|  |   |
|--|---|
| Switch actuation                       | By any moving part  |
| Electrical connection                  | Screw-clamp terminals, clamping capacity: 1 x 0.34...2 x 1.5 mm <sup>2</sup>  |
| Cable entry                            | 1 entry tapped for M16 x 1.5 cable gland, cable outer diameter: 4...8 mm  |
| Contacts insulation form               | Zb  |
| Positive opening                       | Without   |
| Minimum torque for tripping            | 0.13 N.m  |
| Maximum actuation speed                | 1 m/s   |
| Repeat accuracy                        | 0.1 mm on the tripping points with 1 million operating cycles   |
| Contact code designation               | , AC-15 (U <sub>e</sub> = 240 V, I <sub>e</sub> = 3 A) , I <sub>th</sub> = 10 A conforming to EN/IEC 60947-5-1 appendix A<br>, DC-13 (U <sub>e</sub> = 250 V, I <sub>e</sub> = 0.27 A) conforming to EN/IEC 60947-5-1 appendix A  |
| [Ui] rated insulation voltage          | 500 V degree of pollution 3 conforming to IEC 60947-1<br>300 V conforming to UL 508<br>300 V conforming to CSA C22.2 No 14  |
| Resistance across terminals            | <= 25 MOhm conforming to IEC 60255-7 category 3   |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60664<br>6 kV conforming to IEC 60947-1  |
| Short circuit protection               | 10 A by gG cartridge fuse   |
| Electrical durability                  | 5000000 cycles, DC-13, 120 V, 4 W, operating rate: <= 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C<br>5000000 cycles, DC-13, 24 V, 10 W, operating rate: <= 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C<br>5000000 cycles, DC-13, 48 V, 7 W, operating rate: <= 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C |
| Mechanical durability                  | 5000000 cycles  |
| Width                                  | 31 mm   |
| Height                                 | 65 mm   |
| Depth                                  | 30 mm   |
| Product weight                         | 0.085 kg  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|  |   |
|--|---|
| Shock resistance                           | 50 gn (duration = 11 ms) conforming to IEC 60068-2-27                                   |
| Vibration resistance                       | 25 gn (f = 10...500 Hz) conforming to IEC 60068-2-6                                     |
| IP degree of protection                    | IP66 conforming to IEC 60529<br>IP67 conforming to IEC 60529                            |
| IK degree of protection                    | IK04 conforming to EN 50102   |
| Class of protection against electric shock | Class II conforming to IEC 61140<br>Class II conforming to NF C 20-030                  |
| Ambient air temperature for operation      | -25...70 °C   |
| Ambient air temperature for storage        | -40...70 °C   |
| Protective treatment                       | TC  |
| Product certifications                     | CCC<br>CSA<br>UL  |
| Standards                                  | EN 60204-1<br>EN 60947-5-1<br>IEC 60204-1<br>IEC 60947-5-1<br>UL 508<br>CSA C22.2 No 14 |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS                             | Compliant - since 1002 - Schneider Electric declaration of conformity |
| Product environmental profile    | Available   |
| Product end of life instructions | Available   |