

Specification for Two Mode Speaker	Page	2/9
Model No. :                    KP1810SP1-3985	Revision No.	1.0
	Drawing No.	KFC3985

## CONTENTS

1. Scope
2. General
3. Electrical and Acoustic Characteristics.
4. Reliability Test
5. Measurement Block Diagram & Response curve
6. Structure
7. Dimensions
8. Packing
9. Revision

Specification for Two Mode Speaker		Page	3/9
Model No. : KP1810SP1-3985		Revision No.	1.0
		Drawing No.	KFC3985

## 1. Scope

This specification is applied to the two mode dynamic speaker which is used all of the electrical acoustic product.

-- compact, rich sound

-- applications: mobile phone, PDA, notebook computer, etc. ...

## 2. General

2.1 Out-Diameter : 1810 mm

2.2 Height : 4.0 mm

2.3 Weight : 1.0 gr.

2.4 Operating Temperature range:

-20~+70°C without loss of function

2.5 Store Temperature range:

-40~+85°C without loss of function

## 3. Electrical and Acoustic Characteristics.

Test condition : 15 ~ 35 °C, 25% ~ 85% RH, 860~1060 mbar


### 3.1 Speaker

	Items	Specification
1	Impedance	8 Ω ± 15%(at 1Vrms,1.5kHz)
2	Sound Pressure Level	85dB ± 3dB( 1kHz/0.1W/0.1M )
3	Resonance Frequency	1300 Hz ± 20%
4	Frequency Range	F <sub>0</sub> ~ 10.0kHz
5	Input Power	Rated 0.5W / Max. 1.0W
6	Distortion	<10% Max. at 2kHz/2Vrms
7	Buzz and Rattle	Should not be audible buzzes,rattles when the 2.0V sine wave signal swept at frequency range.
8	Polarity	When supplied plus D.C. voltage to (+) terminal, the cone diaphragm must move to forward.

Specification for Two Mode Speaker		Page	4/9
Model No. : KP1810SP1-3985		Revision No.	1.0
		Drawing No.	KFC3985

## 4. Reliability Test


After test(1~7item), the speaker S.P.L . difference shall be within  $\pm 3\text{dB}$ , and the appearance not exist any change to be harmful to normal operation(e.g. cracks,rusts,damages and especially distortion).

	Item	Specification
1	High Temperature Test	After being placed in a chamber with $+85\pm 3\text{ }^\circ\text{C}$ for 96 hours and then being placed in natural condition for 1 hour, speaker shall be measured.
2	Low Temperature Test	After being placed in a chamber with $-40\pm 3\text{ }^\circ\text{C}$ for 96 hours and then being placed in natural condition for 1 hour, speaker shall be measured.
3	Humidity Test	After being placed in a chamber with 85 to 90%R.H. at $+40\pm 2\text{ }^\circ\text{C}$ for 96 hours and then being placed in natural condition for 1 hour, speaker shall be measured.
4	Thermal Shock Test	<p>After being placed in a chamber at <math>+80\text{ }^\circ\text{C}</math> for 1 hour, then speaker shall be placed in a chamber at <math>-40\text{ }^\circ\text{C}</math> for 1 hour(1 cycle is the below diagram).</p> <p>After 6 above cycles, speaker shall be measured after being placed in natural condition for 1 hour.</p>  <p>The diagram shows a temperature profile starting at <math>+80\text{ }^\circ\text{C}</math> for a 1-hour dwell. It then drops linearly to <math>-40\text{ }^\circ\text{C}</math> over a 20-second period. At <math>-40\text{ }^\circ\text{C}</math>, it remains for another 1-hour dwell before returning to the starting point.</p>
5	Vibration Test	After being applied vibration of amplitude of 1.5mm with 10 to 55Hz band of vibration frequency to each of 3 perpendicular directions for 1 hour, then placed in natural condition for 1 hour, speaker shall be measured.
6	Drop Test	The speaker when mounted in the jig which weight 85g~100g, shall with stand 15 times random drops from a height of 1.5 meter to a concrete floor faced with 5mm thick hard wood board.and be nothing mechanical damage.
7	Load test	The speaker after being applied loading white noise with input power 0.5W(2.0Vrms.) for 96 hours, then placed in natural condition for 1 hour, speaker shall be measured.
8	Insulation test	When they are measured with DC 100V the insulation resistance between v.c. terminal and frame must be more than 1 M $\Omega$

Specification for Two Mode Speaker		Page	5/9
Model No. : KP1810SP1-3985		Revision No.	1.0
		Drawing No.	KFC3985

## 5. Measurement Block Diagram & Response curve


### 5.1 Speaker



[dB/20.0u Pa]


Output Response (Signal 1) - Input (Magnitude)

Working : Input : Input : SSR Analyzer



Specification for Two Mode Speaker		Page	6/9
		Revision No.	1.0
Model No. :	KP1810SP1-3985	Drawing No.	KFC3985


## 6. Structure



7	Terminal	1	Epoxy PCB	
6	Frame	1	SPC	
5	Magnet	1	Nd-Fe-B	
4	Plate	1	SPC	
3	Diaphragm	1	PEI	
2	Coil	1	Copper	
1	Cap	1	SUS304	
No.	Part Name	Q'TY	Material	Remarks

Specification for Two Mode Speaker		Page	7/9
		Revision No.	1.0
Model No. :	KP1810SP1-3985	Drawing No.	KFC3985

## 7. Dimensions




FIRST ANGLE PROJECTION






UNIT : mm  
Tolerance :  $\pm 0.2$

Specification for Two Mode Speaker		Page	8/9
		Revision No.	1.0
Model No. :	KP1810SP1-3985	Drawing No.	KFC3985

## 8. Packing



100Pcs



QTY: 2000Pcs  
440 x290 x220