



**Product:** [3106A](#) 

RS-485, 1 Pr, 22AWG, Str TC, PE Ins, with OS, 1C 22AWG Str, PVC Ins, OA TC Brd, PVC Jkt, CM, PLTC, Sun Res, Oil Resistant

 [Request Sample](#)

## Product Description

RS-485, 120 Ohm, 1 pair 22AWG (7x30) tinned copper Datalene® insulation, with Foil Shield, 1 Conductor 22AWG (7x30) Tinned Copper, PVC Insulated, Overall 65% Tinned Copper Braid, PVC jacket, CM, PLTC, SUN RES and oil-resistant

## Technical Specifications

### Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper
Conductor(s)	1	22 AWG	7x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.033 in (0.84 mm)	White/Orange Stripe & Orange/White Stripe	HDPE
Conductor(s)	PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	Blue/White Stripe	

#### Inner Shield

Element	Shield Type	Material	Coverage	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	Single conductor is not under tape

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC
Braid	Tinned Copper (TC)	65%	

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.041 in (1.0 mm)	0.300 in (7.62 mm)

Overall Cable Diameter (Nominal):	0.300 in (7.62 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.7 Ohm/1000ft (48.2 Ohm/km)	11 pF/ft (36 pF/m)	20.9 pF/ft	120 Ohm	78%	2.7 Amps per Conductor at 25°C
Conductor(s)	14.7 Ohm/1000ft (48.2 Ohm/km)					

Nom. Outer Shield DCR:	2.8 Ohm/1000ft (9.2 Ohm/km)
------------------------	-----------------------------

#### High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
---------	-----------------	-----------------------------------

Pair(s)	1	0.5 dB/100ft
---------	---	--------------

## Voltage

<b>UL Voltage Rating</b>
300 V (CM, PLTC)

## Mechanical Characteristics

### Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

### Bend Radius

Stationary Min.	Installation Min.
3.0 in (76 mm)	3.0 in

Max. Pull Tension:	65 lbs (29 kg)
Bulk Cable Weight:	48 lbs/1000ft (71 kg/km)

## Standards and Compliance

Environmental Suitability:	Indoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1685 UL Loading, FT1, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CM, PLTC
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

## Product Notes

Notes:	Oil Resistance: Passes Oil Res II Per UL1277, Table 10.17. For CPE jacketed version order YR46721.
--------	--

## History

Update and Revision:	Revision Number: 0.399 Revision Date: 12-15-2021
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN
3106A.00152	Black	Reel	152 m	8719605005892
3106A.00305	Black	Reel	305 m	8719605005915
3106A 010500	Black	Reel	500 ft	612825141662
3106A 0101000	Black	Reel	1,000 ft	612825141655
3106A.001525	Black	Reel	1,525 m	8719605005908
3106A 0105000	Black	Reel	5,000 ft	612825141679

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.