




**+** CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)

## COVER FOR 6W HSG MQS GEN2

MQS

953382-1

TE Internal Number: 953382-1

EU RoHS Compliant

EU ELV Compliant

**Connector System** Wire-to-Board, Wire-to-Component

**Accessory Type** Cover - Cable Exit

**Cable Exit Angle** 180 (In-Line)

**Strain Relief** With

**Color** Black

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### DOCUMENTATION

Product Drawings

#### **COVER FOR 6W HSG MQS GENE 2 PORTE-MODULE 6VOIES MQS GENE 2**

PDF (TIFF AVAILABLE)

English

CAD Files

#### **Customer View Model**

3D\_IGS.ZIP

English

#### **Customer View Model**

3D\_STP.ZIP

English

#### **Customer View Model**

2D\_DXF.ZIP

English

### 3D PDF

PDF

English

---

Product Specifications

Product Specification

### PORTE-CLIPS MQS 6 VOIES GENERATION II

PDF

English

---

Instruction Sheets

Instruction Sheet (non U.S.)

### 6 VOIES MQS GENE II

PDF

English

### 6 VOIES MQS GENE II

TIF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Connector System** Wire-to-Board, Wire-to-Component

**Accessory Type** Cover - Cable Exit

**Strain Relief** With

---

Body Features

**Cable Exit Angle** 180 (In-Line)

**Color** Black

**Material** PBT GF

---

Dimensions

**Cable Bundle Diameter** 5 mm [ .197 in ]

---

Usage Conditions

**Operating Temperature (Max) (°C)** 70, 75, 80, 85, 90, 100

**Operating Temperature (Max) (°F)** 158, 167, 176, 185, 194, 212

**Operating Temperature Range** -40 – 100 °C [ -40 – 212 °F ]

---

Industry Standards

**UL Flammability Rating** UL 94-HB

---

Packaging Features

**Packaging Method** Box

---

Other

**Serviceable** Yes

Statement of Compliance

**Statement of Compliance**

PDF