


Part Number & Date Code Printing

Pull Parts

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER	LEAD FREE P/N
09	30.81	24.99	16.96	16.21	D09S13A*GL00	D09S13A*GL00LF
15	39.14	33.32	25.18	24.54	D15S13A*GL00	D15S13A*GL00LF
25	53.03	47.04	39.12	38.25	D25S13A*GL00	D25S13A*GL00LF
37	69.32	63.50	55.68	54.71	D37S13A*GL00	D37S13A*GL00LF

4-200 MATING CYCLES
6-500 MATING CYCLES



GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

mat'l. code		surface		tolerance		projection		product family	
SEE NOTES		ISO 1302	ISO 406	ISO 1101	MM		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM		title	
G	105-0724	JS	2005/07/27	angles	O.X ±0.1	SOCKET CONNECT.DELTA D RIGHT ANGLE		WITH NUT,HARPON and metal plate.	
H	106-0074	SK	2006/06/08	linear	O.XX ±0.1	scale 1:1		dwg no	
J	ELX-I-15060	AB	2013/06/25	0.XX±2°	O.XXX±0.1	FCJ		C01-8646-0165	
K	ELX-I-18948	AB	2014/09/29	dr	JOHN.SLEEBA	1994/10/14		sheet 1 of 1	
				engr	ALIAS.BABU	2014/09/29		size	
				chr	MITHUN.PAUL	2014/09/29		A3	
				appd	BIJU.K.PAUL	2014/09/29		CUSTOMER Drawing	
sheet index	revision	sheet	1	K					