

Bolt Fixing Ball Transfer Units



General Tolerance unless stated ±0.3mm

The individual **product features** are displayed at the foot of the table...

REF. NO.	Ball Size (mm)	Max Torque on Nut (Nm)		Support Load (Kgs)			
					E 13 Bearings, Zinc essings Load Down	Press	Bearings and
3001	19	15	0.060	25	10	25	10
3002	10	13	0.080	20	10	20	10
1003			0.160	55	25	55	25
1009	25.4	15	0.140	- 55	20	55	20
1501			0.180	100	50	100	50
2001	40	20	0.400	140	60	140	60
2005	40	20	0.460	140	00	140	- 00
4004*	50	25	1.720	340	100	250	400

^{*}Pattern 4004 can be supplied with other screw sizes or plain shanks.

To order, specify Ref No., Type and LENGTH OF THREAD, i.e. 3001-13-25

3002

1009

3001



Features: Adjustable height, drilled hole fixing.

Optional extras: Additional nuts, alternative thread sizes, dirt exit hole.



Features: Large support area, drilled hole fixing

Optional extras: Alternative thread sizes, dirt exit hole.

1003



Features: Large support area, drilled hole

fixing

Optional extras: Alternative thread sizes, dirt exit hole.



Features: Adjustable height, drilled hole fixing.

Optional extras: Additional nuts, alternative thread sizes, dirt exit hole.

1501



Features: Large support area, greater stability, drilled hole fixing. High load capacity, knife edge seal on main ball.

Optional extras: Alternative thread sizes, dirt exit hole.



2001

Features: Adjustable height, drilled hole fixing.

Optional extras: Additional nuts, alternative thread sizes, dirt exit hole.

2005



Features: Large support area, greater stability, drilled hole fixing.

Optional extras: Alternative thread sizes, dirt exit hole.



4004

Features: Adjustable height, drilled hole fixing. High load capacity, dirt exit hole. Can be dismantled for cleaning.

Optional extras: Grease points can be fitted. Alternative thread sizes.