

# Data logger Temperature

testo 175 T3

Large, easily legible display

High data security

Measurement data memory for 1 million measurement values

Up to 3 years' battery life

Data transfer via USB cable or SD card

Two external sensor connections (thermocouple Type T and Type K)





Illustration 1:1

Temperature often needs to be monitored and recorded simultaneously at two sites. The testo 175 T3 is excellently suited to this job, thanks to two connections for external thermocouple probes (Type K and Type T). The wide measuring range makes the data logger universally applicable.

The free ComSoft Basic software allows fast programming of the data logger and easy data analysis.

In the autumn, the heating period begins, and with it the time for complaints by tenants that their appartments cannot be heated to the desired extent. With the testo 175 T3 and the versatile external thermocouple probes, you can, for example, perform targeted checks on the flow and return temperatures of individual radiators, in order to identify and remedy causes.



## **Technical data / Accessories**

### testo 175 T3

testo 175 T3, 2-channel temperature data logger with external sensor connections (TC Type T and Type K) incl. wall holder, lock, batteries and calibration protocol

Part no. 0572 1753



#### General technical data

| Channels              | 2 x external                  |
|-----------------------|-------------------------------|
| Battery type          | 3 x AlMn Typ AAA or Energizer |
| Battery life          | 3 years at 15 min. meas. rate |
| Operating temperature | -20 to +55 °C                 |
| Storage temperature   | -20 to +55 °C                 |
| Dimensions            | 89 x 53 x 27 mm               |
| Protection class      | IP65                          |
| Measuring rate        | 10 s - 24 h                   |
| Memory                | 1 mio. measurement values     |

#### **Sensor types**

|                      | Type T (Cu-CuNi)  | Type K (NiCr-Ni)  |
|----------------------|---|---|
| Measuring range      | -50 to +400 °C  | -50 to +1000 °C   |
| Accuracy<br>±1 digit | ±0.5 °C (-50 to +70 °C)<br>±0.7 % of mv (+70.1 to +1000 °C) | ±0.5 °C (-50 to +70 °C)<br>±0.7 % of mv (+70.1 to +1000 °C) |
| Resolution           | 0.1 °C  | 0.1 °C  |

Accessories Part no.

#### **Accessories for measuring instrument**

| Wall holder (black) with lock for testo 175   | 0554 1702 |  |
|---|-----------|--|
| Cable for connecting the data loggers testo 175 and testo 176 to the PC, Mini-USB to USB  | 0449 0047 |  |
| SD card - for collecting the measurement data from the data loggers testo 175 and testo 176; 2 GB; application range to -20 °C  | 0554 8803 |  |
| Battery for testo 175 Range of application to -10 °C, alkali manganese microcell AAA (please order 3 batteries per logger)  | 0515 0009 |  |
| ComSoft Basic, Basic software for programming and readout of Testo data loggers; graphic and tabular measurement value presentation as well as export function (if free download with registration not desired) | 0572 0580 |  |
| ComSoft Professional, Pro software incl. data archiving   | 0554 1704 |  |
| ComSoft CFR 21 Part 11, Software for requirements according to CFR 21 Part 11 for Testo data loggers  | 0554 1705 |  |
| ISO calibration certificate temperature temperature probe; calibration points -18°C; 0°C; +40°C per channel/instrument  | 0520 0153 |  |
| DAkkS calibration certificate temperature Temp. data logger; cal. points -20°C; 0°C; +60°C; per channel/instrument  | 0520 0261 |  |
|   |           |  |



## **Probes**

| Probe type  | Dimensions<br>Probe shaft/probe shaft tip | Measuring range     | Accuracy               | t <sub>99</sub> | Part no.  |
|---|---|---------------------|------------------------|-----------------|-----------|
| Probes Type K   |   |                     |                        |                 |           |
| Immersion tip, flexible, TC Type K  | Ø 1.5 mm 500 mm                           | -200 to<br>+1000 °C | Class 1 <sup>1)</sup>  | 5 s             | 0602 5792 |
| Immersion tip, flexible, TC Type K  | Ø 1.5 mm 500 mm                           | -200 to +40 °C      | Class 3 <sup>1)</sup>  | 5 s             | 0602 5793 |
| Immersion measurement tip,<br>flexible, for measurements in<br>air/exhaust gases (not suitable for<br>measurements in smelters), TC<br>Type K                     | Ø 3 mm 1000 mm                            | -200 to<br>+1300 °C | Class 1 <sup>1)</sup>  | 4 s             | 0602 5693 |
| Magnetic probe, adhesive force<br>approx. 20 N, with magnets, for<br>measurements on metal surfaces,<br>TC Type K, Fixed cable                                    | 35 mm Ø 20 mm                             | -50 to +170 °C      | Class 2 <sup>1)</sup>  | 150 s           | 0602 4792 |
| Magnetic probe, adhesive force<br>approx. 10 N, with magnets, for<br>higher temp., for measurements on<br>metal surfaces, TC Type K, Fixed<br>cable               | 75 mm Ø 21 mm                             | -50 to +400 °C      | Class 2 <sup>1)</sup>  |                 | 0602 4892 |
| Pipe wrap probe with velcro strip;<br>for temperature measurement on<br>pipes with diameter up to max. 120<br>mm; Tmax. +120 °C; TC Type K ,<br>Fixed cable 1.5 m | 395 mm                                    | -50 to +120 °C      | Class 1 <sup>1)</sup>  | 90 s            | 0628 0020 |
| Pipe wrap probe for pipe diameter 5 to 65 mm, with exchangeable measuring head. Meas. range short-term up to +280°C, TC Type K, Fixed cable 1.2 m                 |   | -60 to +130 °C      | Class 2 1)             | 5 s             | 0602 4592 |
| Clamp probe for measurements on<br>pipes, pipe diameter 15 to 25 mm<br>(max. 1"), meas. range short-term<br>up to +130°C, TC Type K, Fixed<br>cable               |   | -50 to +100 °C      | Class 2 <sup>1)</sup>  | 5 s             | 0602 4692 |
| Waterproof food probe made of<br>stainless steel (IP65), TC Type K,<br>Fixed cable  | 125 mm 30 mm<br>Ø 4 mm Ø 3.2 mm           | -60 to +400 °C      | Class 2 <sup>(1)</sup> | 7 s             | 0602 2292 |
| Waterproof robust immersion/penetration probe with metal protection hose Tmax +230°C, e.g. for monitoring temp. in cooking oil, T/C Type K, Fixed cable           | 240 mm  Ø 4 mm                            | -50 to +230 °C      | Class 1 <sup>1)</sup>  | 15 s            | 0628 1292 |
| Thermocouple with TC adapter, flexible, 800 mm long, fibre glass, TC Type K   | 800 mm<br>Ø 1.5 mm                        | -50 to +400 °C      | Class 2 <sup>1)</sup>  | 5 s             | 0602 0644 |
| Thermocouple with TC adapter, flexible, length 1500 mm , fibreglass, TC Type K  | 1500 mm<br>Ø 1.5 mm                       | -50 to +400 °C      | Class 2 1)             | 5 s             | 0602 0645 |

<sup>1)</sup> According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K).

0981 3914/msp/A/08.2013



## **Probes**

| Probe type   | Dimensions<br>Probe shaft/probe shaft tip | Measuring range     | Accuracy   | t <sub>99</sub> | Part no.  |
|--|---|---------------------|--|-----------------|-----------|
| Probes Type K  |   |                     |  |                 |           |
| Thermocouple with TC adapter,<br>flexible, 1500 mm long, PTFE, TC<br>Type K  | 1500 mm<br>Ø 1.5 mm                       | -50 to +250 °C      | Class 2 <sup>1)</sup>  | 5 s             | 0602 0646 |
| Stationary probe with stainless<br>steel sleeve, TC Type K, Fixed<br>cable 1.9 m   | 40 mm Ø 6 mm                              | -50 to +205 °C      | Class 2 <sup>1)</sup>  | 20 s            | 0628 7533 |
| Flexible, low-mass immersion measurement tip, ideal for measurements in small volumes such as petri dishes, or for surface measurements (e.g. attached with adhesive tape), TC Type K, 2 m, FEP insulated thermal wire, temperature proof up to 200 °C, oval wire with dimensions: 2.2 mm x 1.4 mm | Ø 0.25 mm 500 mm                          | -200 to<br>+1000 °C | Class 1 <sup>1)</sup>  | 1 s             | 0602 0493 |
| Probes Type T  |   |                     |  |                 |           |
| Frozen food probe, corkscrew<br>design, T/C Type T, Plug-in cable  |   | -50 to +350 °C      | ±0.2 °C (-20 to +70 °C)<br>Class 1 (remaining range) <sup>2)</sup> | 8 s             | 0603 3292 |
| Stainless steel food probe (IP67), with FEP cable to +200 °C, TC Type T, Fixed cable   |   | -50 to +350 °C      | ±0.2 °C (-20 to +70 °C)<br>Class 1 (remaining range) <sup>2)</sup> | 7 s             | 0603 3392 |
| Waterproof, super-quick needle<br>probe for measurements without<br>visible penetration hole, T/C Type<br>T, Fixed cable   | 150 mm<br>Ø 1.4 mm                        | -50 to +250 °C      | ±0.2 °C (-20 to +70 °C)<br>Class 1 (remaining range) <sup>2)</sup> | 2 s             | 0628 0027 |
| Flexible oven probe,<br>Tmax +250 °C, PTFE<br>cable  | 2000 mm<br>Ø 1.5 mm                       | -50 to +250 °C      | Class 1 <sup>2)</sup>  |                 | 0603 0646 |

<sup>1)</sup> According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K). 2) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +350 °C (Type T).