

Wire-wound Chip Power Inductors (BR series)

BRL3225T470K



■ Features

- Item Summary
47 μ H \pm 10%, 0.39A, 1210/3225 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 2000pcs

■ Products characteristics table

Inductance	47 μ H \pm 10 %
Case Size (EIA/JIS)	1210/3225
Rated Current (max)	0.39 A
Saturation Current (max)	0.42 A
Temperature Rise Current (max)	0.39 A
DC Resistance (max)	1.2 Ω
DC Resistance (typ)	1 Ω
LQ Measuring Frequency	0.1 MHz
Self Resonant Frequency (min)	7 MHz
Operating Temp. Range	-40 to +105 $^{\circ}$ C (Including-self-generated heat)
Temperature characteristic (Inductance change)	\pm 15 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	3.2 \pm 0.2 mm
Dimension W	2.5 \pm 0.2 mm
Dimension T	Max 1.7 mm
Dimension e	0.75 \pm 0.2 mm

2017.01.21

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

Wire-wound Chip Power Inductors (BR series)

BRL3225T470K






Dimension	unit : mm	unit : inch
Length :	3.2 +/- 0.2	(0.126 +/- 0.008)
Width :	2.5 +/- 0.2	(0.098 +/- 0.008)
Height :	1.7 max.	(0.067 max.)

Inductance :	47	uH	(test freq at 0.1MHz)
DC Resistance :	1.0 / 1.2	ohm	(typ / max)
Saturation Current :	420	mA	
Temp. rise Current :	390	mA	

Saturation current typical : 30% reduction from initial L value.

Temp rise Current typical : Temperature will rise by 40 deg C



The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the data at any time without notice. Before making final selection, please check product specification.