


## Wire-wound Chip Power Inductors (BR series)

## BRL3225T6R8M



## ■ Features

- Item Summary  
6.8  $\mu$ H( $\pm$ 20%), 1050mA, 770mA, 1210
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping 2000pcs

## ■ Products characteristics table

CaseSize (EIA/JIS)	1210/3225
Inductance	6.8 $\mu$ H( $\pm$ 20%)
Inductance Measuring Frequency	0.1MHz
Rated Current -Saturation Current	1050mA
Rated Current -Temperature Rise Current	770mA
DC Resistance (max)	0.324 $\Omega$
Avg. of DC.Resistance	0.27 $\Omega$
Temperature Range	-40 to +105 $^{\circ}$ C
Self-resonant Frequency (min)	90MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

## ■ External Dimensions

L	3.2mm $\pm$ 0.2
W	2.5mm $\pm$ 0.2
H	1.7mm max

2015.06.28

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.