



SHELL	A ± 0.38	B ± 0.12	C ± 0.10	D ± 0.25	E ± 0.07	G ± 0.25
09	30.81	24.99	16.96	16.79	10.96	5.90
15	39.14	33.32	25.18	25.12	19.18	5.90
25	53.03	47.04	39.12	38.84	33.12	5.70
37	69.32	63.50	55.68	55.30	49.68	5.70



SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A6GV00LF	D09P24A6GV00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A6GV00LF	D15P24A6GV00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A6GV00LF	D25P24A6GV00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A6GV00LF	D37P24A6GV00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

4 = Performance level PL3 ≥ 200 OPERATIONS  
 6 = Performance level PL1 ≥ 500 OPERATIONS

PC card drilling dimensions(after plating)  
 (thickness 1.60±0.20mm)



SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A*GI00LF	D09P24A*GI00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A*GI00LF	D15P24A*GI00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A*GI00LF	D25P24A*GI00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A*GI00LF	D37P24A*GI00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

4 = Performance level PL3 ≥ 200 OPERATIONS  
 6 = Performance level PL1 ≥ 500 OPERATIONS

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
 SEE DRAWING C01-8646-0000

rev	ecn no	dr	date
A	-	BAR	2003/04/16
B	LS05-001	MPE	2005/03/14
C	LS05-0056	LGO	2005/07/07
D	LS06-0097	LGO	2006/07/28
E	I09-0268	NG	2009-11-24
F	I10-0059	NG	2010-02-23

www.fciconnect.com

Dr JARRY 1995/08/11  
 Eng PESSON 1995/08/11  
 Chr NIRMAL GEORGE 2010-02-23  
 Appr SUDHIR VARMA 2010-02-23

ISO 1302 surface tolerance std ISO 406 ISO 1101  
 TOLERANCES UNLESS OTHERWISE SPECIFIED

ANGULAR 0.X  
 LINEAR 0.XX  
 0.XXX ± 0.1

projection A3  
 size A3  
 ECN I10-0059

Product family D-SUB Spec ref -

European Views  
 mm  
 Scale 2

FCI logo  
 HEADERS DELTA D STD EUROPE  
 HEADERS DELTA D STD EUROPE

C01-8646-0816  
 CUSTOMER sheet 1 of 1