


SPAX®

BN 20184 - Hexalobular (6 Lobe) socket flat countersunk head chipboard screws T-STAR plus, partially threaded with 4CUT point



Manufacturer



Product description

Other documentation: www.spax.com

Additional information

The WIROX® coating is an alternative chromium free (VI) surface coating with considerably higher corrosion protection compared to yellow electrogalvanizing.

Headform

Countersunk

Drive

Hexalobular socket

Thread

partially threaded

Brand

SPAX®

Material

Steel

Material execution

case-hardened

Surface

WIROX® added lubricant

Version

with 4CUT point

Certificates



Warnings

ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!

Further notice to residual risks can be found in the introduction section.

d1 6; 8: 4CUT cutter for screw lengths of 160 mm and over (significantly reduces the screwing torque)

Article no	p	d1	L	d2	k max	Hexalobular socket	b
------------	---	----	---	----	-------	--------------------	---

Article no	p	d1	L	d2	k max	Hexalobular socket	b
3373513	200	3	30	6	1.8	T10	18
3336986	1000	3	30	6	1.8	T10	18
3337055	200	3	35	6	1.8	T10	23
3336987	1000	3	35	6	1.8	T10	23
3336988	1000	3	40	6	1.8	T10	23
3337057	200	3.5	30	7	2.1	T20	18
3336989	1000	3.5	30	7	2.1	T20	18
3337058	200	3.5	35	7	2.1	T20	23
3336990	1000	3.5	35	7	2.1	T20	23
3337059	200	3.5	40	7	2.1	T20	23
3336992	1000	3.5	40	7	2.1	T20	23
3337060	200	3.5	45	7	2.1	T20	30
3336994	1000	3.5	45	7	2.1	T20	30
3337061	200	3.5	50	7	2.1	T20	32
3336995	500	3.5	50	7	2.1	T20	32
3337063	200	4	30	8	2.4	T20	18
3336996	1000	4	30	8	2.4	T20	18
3337064	200	4	35	8	2.4	T20	23
3336997	1000	4	35	8	2.4	T20	23
3337065	200	4	40	8	2.4	T20	23
3336998	1000	4	40	8	2.4	T20	23
3337066	200	4	45	8	2.4	T20	30
3336999	500	4	45	8	2.4	T20	30
3337067	200	4	50	8	2.4	T20	32
3337000	500	4	50	8	2.4	T20	32
3337068	100	4	60	8	2.4	T20	35
3337001	500	4	60	8	2.4	T20	35
3373514	100	4	70	8	2.4	T20	37
3337003	500	4	70	8	2.4	T20	37
3373515	200	4	80	8	2.4	T20	37
3337070	200	4.5	30	8.8	2.7	T20	17
3337004	1000	4.5	30	8.8	2.7	T20	17
3337071	200	4.5	35	8.8	2.7	T20	25
3337007	500	4.5	35	8.8	2.7	T20	25
3337072	200	4.5	40	8.8	2.7	T20	25
3337008	500	4.5	40	8.8	2.7	T20	25
3337073	200	4.5	45	8.8	2.7	T20	30
3337009	500	4.5	45	8.8	2.7	T20	30
3337074	200	4.5	50	8.8	2.7	T20	32
3337010	500	4.5	50	8.8	2.7	T20	32
3337075	100	4.5	60	8.8	2.7	T20	37
3337011	500	4.5	60	8.8	2.7	T20	37
3337077	100	4.5	70	8.8	2.7	T20	42
3337012	500	4.5	70	8.8	2.7	T20	42
3337078	100	4.5	80	8.8	2.7	T20	47
3337014	200	4.5	80	8.8	2.7	T20	47
3373516	200	5	30	9.7	2.9	T20	17
3337016	500	5	30	9.7	2.9	T20	17
3337017	500	5	35	9.7	2.9	T20	25
3373518	200	5	40	9.7	2.9	T20	27

Article no	p	d1	L	d2	k max	Hexalobular socket	b
3337018	500	5	40	9.7	2.9	T20	27
3337019	500	5	45	9.7	2.9	T20	30
3337079	200	5	50	9.7	2.9	T20	32
3337020	500	5	50	9.7	2.9	T20	32
3337021	500	5	55	9.7	2.9	T20	37
3337080	100	5	60	9.7	2.9	T20	37
3337022	500	5	60	9.7	2.9	T20	37
3373520	100	5	70	9.7	2.9	T20	41
3337025	200	5	70	9.7	2.9	T20	41
3337081	100	5	80	9.7	2.9	T20	46
3337026	200	5	80	9.7	2.9	T20	46
3373521	100	5	90	9.7	2.9	T20	61
3337027	200	5	90	9.7	2.9	T20	61
3373522	100	5	100	9.7	2.9	T20	61
3337028	200	5	100	9.7	2.9	T20	61
3337030	200	5	120	9.7	2.9	T20	69
3337032	500	6	40	11.6	3.4	T30	24
3620428	100	6	50	11.6	3.4	T30	32
3337033	200	6	50	11.6	3.4	T30	32
3337082	100	6	60	11.6	3.4	T30	37
3337034	200	6	60	11.6	3.4	T30	37
3337083	100	6	70	11.6	3.4	T30	41
3337035	200	6	70	11.6	3.4	T30	41
3337085	100	6	80	11.6	3.4	T30	46
3337036	200	6	80	11.6	3.4	T30	46
3337086	100	6	90	11.6	3.4	T30	61
3337037	200	6	90	11.6	3.4	T30	61
3337039	100	6	100	11.6	3.4	T30	61
3337040	100	6	110	11.6	3.4	T30	68
3337041	100	6	120	11.6	3.4	T30	68
3337042	100	6	130	11.6	3.4	T30	68
3337043	100	6	140	11.6	3.4	T30	68
3337044	100	6	150	11.6	3.4	T30	68
3337046	100	6	160	11.6	3.4	T30	65
3337047	100	6	180	11.6	3.4	T30	65
3337048	100	6	200	11.6	3.4	T30	65
3337049	100	6	220	11.6	3.4	T30	65
3337050	100	6	240	11.6	3.4	T30	65
3337051	100	6	260	11.6	3.4	T30	65
3337053	100	6	280	11.6	3.4	T30	65
3337054	100	6	300	11.6	3.4	T30	65