

**VG S (standard stainless steel cable gland)
VGM16-SS 68 KB 4-8**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



This cable gland series is made from stainless steel and is well suited for industrial applications requiring IP68 protection. Its excellent resistance against seawater and impacts make it ideal for use in harsh conditions.

General ordering data

Type	VGM16-SS 68 KB 4-8
Order No.	1009850000
Version	VG S (standard stainless steel cable gland), Cable glands, M 16, 7 mm, OD min. 4 - OD max. 8 mm, Stainless steel 1.4305 (303)
GTIN (EAN)	4032248714674
Qty.	50 pc(s).

**VG S (standard stainless steel cable gland)
VGM16-SS 68 KB 4-8**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	30 mm	Length (inches)	1.181 inch
Net weight	18.66 g		

General information

Material	Stainless steel 1.4305 (303)	Cable glands	metric
External thread	M 16	Pitch of thread	1.5 mm
Length of thread	7 mm	AF size 1	17 mm
AF size 2	19 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Outer cable diameter, min.	4 mm	Outer cable diameter, max.	8 mm
O-Ring	NBR	Seal insert	CR
Sealing	NBR	Tightening torque	5.5 Nm
Torque for cap nut, min.	8 Nm	Torque for cap nut, max.	10 Nm
Torque for connecting adapter, min.	15 Nm	Torque for connecting adapter, max.	12 Nm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP