

PRECISION,
QUALITY,
INNOVATION

Starrett®

NEW

BI-METAL HOLE SAWS

NEW

FAST CUT

**FASTER &
SMOOTHER**

NEW

DEEP CUT

**DEEPER &
STRONGER**

**NEW DEEP CUT
HOLE SAW DEPTH
51MM / 2"**

**NEW EXTRA COBALT HSS FOR
ENHANCED HEAT AND WEAR
RESISTANCE**


**NEW EXTRA 30% GULLET
VOLUME FOR BETTER
MATERIAL PENETRATION**

**NEW POSITIVE RAKE 5.5 TPI
PROVIDES LESS TORQUE FOR
A SMOOTHER, FASTER CUT**



FASTER...SMOOTHER...

NEW BI-METAL HOLE SAWS



Starrett[®]
FAST CUT



Starrett[®]
DEEP CUT

The new Fast Cut Bi-Metal Hole Saws contain an extra cobalt HSS tooth material for enhanced heat and wear resistance, along with a new 5.5 TPI positive rake tooth design, to ensure a smoother and faster cut when compared against our previous Constant Pitch Hole Saw. Specifically designed to cut stainless steel, metals and mild steel sheet, the Fast Cut Saws will also cut through wood, plastic, plaster and other materials.

Recommended cutting depth - up to 3mm (1/8").

FEATURES

- New tooth material with extra cobalt for enhanced heat and wear resistance - improving the product life.
- New 5.5 TPI positive rake tooth form provides less torque for a smoother, faster cut in all materials.
- 30% extra gullet volume for better material penetration.
- Ideal for stainless steel and mild steel sheet, tubes and other materials with a thickness of up to 3mm (1/8").
- Size range: 14mm - 152mm (9/16" - 6").
- 41mm (1.5/8") hole saw depth.

The new Deep Cut Bi-Metal Hole Saws combine the aggressive tooth form from our previous Dual Pitch Hole Saws, with the new extra cobalt HSS teeth to provide enhanced heat and wear resistance. Featuring a 10mm increase in hole saw depth and aggressive material penetration and kerf clearance, it is the complete multi-purpose hole saw to penetrate deep into metals, wood, plastic, plaster and other materials.

Recommended cutting depth - greater than 3mm (1/8").

FEATURES

- 51mm (2") hole saw depth improves cutting performance on tubes, particularly where there is a need to cut through both sides.
- New tooth material with extra cobalt for enhanced heat and wear resistance - improving the product life.
- Ideal for solid materials greater than 3mm (1/8") in thickness.
- Aggressive material penetration and kerf clearance.
- Size range: 19mm - 210mm (3/4" - 8.9/32").
- 51mm (2") hole saw depth - requires arbors with an extended length pilot drill (e.g. A1E, A2E or A17-38E etc.).

....DEEPER...STRONGER.

NEW

FAST CUT HOLE SAW KITS

Description	No. of Pcs	Cat No	Fast Cut Bi-Metal Hole Saw Diameters	Arbors and Accessories
General Purpose Kit	6	KFC06023	22mm, 29mm, 35mm, 44mm, 51mm & 64mm	A1 & A10 Arbors
Electricians Kit	6	KFC06022	16mm, 20mm, 25mm, 29mm, 44mm & 51mm	A1 & A10 Arbors
Electricians Kit 1	6	KFC06021	16mm, 20mm, 25mm, 32mm, 40mm & 51mm	A1 & A10 Arbors
Ulti-Mate Electricians Kit	6	KFC06071	16mm, 20mm, 25mm, 32mm, 40mm & 51mm	A3 Ulti-Mate Arbor 6 Ulti-Mate Arbor Adapters
Deluxe Electricians Kit	11	KFC11021	16mm, 20mm, 22mm, 25mm, 29mm, 35mm, 44mm, 51mm, 64mm, 68mm & 76mm	A1 & A2 Arbors
Plumbers Kit	7	KFC07021	19mm, 22mm, 29mm, 38mm, 44mm, 51mm & 57mm	A1 & A10 Arbors
Deluxe Plumbers Kit	11	KFC11022	16mm, 19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm, 65mm & 68mm	A1 & A2 Arbors
Plumbers and Electricians Kit	12	KFC12021	16mm, 20mm, 22mm, 29mm, 35mm, 38mm, 40mm, 44mm, 51mm, 57mm, 65mm & 68mm	A1 & A2 Arbors
Universal Kit	14	KFC14021	16mm, 20mm, 22mm, 25mm, 29mm, 32mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm, 68mm & 76mm	A1 & A2 Arbors
Universal Kit 2	11	KFC11031	19mm, 22mm, 25mm, 32mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm & 76mm	A1 & A2 Arbors A5 Extension

NEW

DEEP CUT HOLE SAW KITS

Description	No. of Pcs	Cat No	Deep Cut Bi-Metal Hole Saw Diameters	Arbors
General Purpose Kit	6	KDC06021	22mm, 29mm, 35mm, 44mm, 51mm & 64mm	A1E & A10E Arbors
Electricians Kit	5	KDC05021	20mm, 25mm, 29mm, 44mm & 51mm	A1E & A10E Arbors
Deluxe Electricians Kit	10	KDC10021	20mm, 22mm, 25mm, 29mm, 35mm, 44mm, 51mm, 64mm, 68mm & 76mm	A1E & A2E Arbors
Plumbers Kit	7	KDC07021	19mm, 22mm, 29mm, 38mm, 44mm, 51mm & 57mm	A1E & A10E Arbors
Deluxe Plumbers Kit	10	KDC10022	19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm, 65mm & 68mm	A1E & A2E Arbors
Universal Kit	13	KDC13021	20mm, 22mm, 25mm, 29mm, 32mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm, 68mm & 76mm	A1E & A2E Arbors



New EVA (Ethylene Vinyl Acetate) Case for Unbreakable Protection.



New POS Packaging with Kit Contents.

BI-METAL FAST CUT HOLE SAWS

Cat. No.	Saw Diameter		Appropriate Arbors
	mm	in	
FCH0096	14	9/16	A1
FCH0058	16	5/8	
FCH1016	17	11/16	
FCH0034	19	3/4	
FCH2532	20	25/32	
FCH1036	21	13/16	
FCH0078	22	7/8	
FCH1056	24	15/16	
FCH0100	25	1	
FCH0116	27	1.1/16	
FCH0118	29	1.1/8	
FCH0136	30	1.3/16	
FCH0114	32	1.1/4	
FCH0156	33	1.5/16	
FCH0138	35	1.3/8	
FCH0176	37	1.7/16	
FCH0112	38	1.1/2	
FCH0196	40	1.9/16	
FCH0158	41	1.5/8	
FCH1116	43	1.11/16	
FCH0134	44	1.3/4	
FCH1136	46	1.13/16	
FCH0178	48	1.7/8	
FCH0200	51	2	
FCH0216	52	2.1/16	
FCH0218	54	2.1/8	
FCH056M	56	2.3/16	
FCH0214	57	2.1/4	
FCH0256	59	2.5/16	
FCH0238	60	2.3/8	
FCH0212	64	2.1/2	
FCH0296	65	2.9/16	
FCH0258	67	2.5/8	
FCH068M	68	2.11/16	
FCH0234	70	2.3/4	
FCH0278	73	2.7/8	
FCH0300	76	3	
FCH0318	79	3.1/8	
FCH0314	83	3.1/4	
FCH0338	86	3.3/8	
FCH0312	89	3.1/2	
FCH0358	92	3.5/8	
FCH0334	95	3.3/4	
FCH0378	98	3.7/8	
FCH0400	102	4	
FCH0418	105	4.1/8	
FCH0414	108	4.1/4	
FCH0438	111	4.3/8	
FCH0412	114	4.1/2	
FCH0434	121	4.3/4	
FCH0500	127	5	
FCH0514	133	5.1/4	
FCH0512	140	5.1/2	
FCH0600	152	6	
N/A	N/A	N/A	
N/A	N/A	N/A	
N/A	N/A	N/A	
N/A	N/A	N/A	

BI-METAL DEEP CUT HOLE SAWS

Cat. No.	Saw Diameter		Appropriate Arbors
	mm	in	
N/A	N/A	N/A	N/A
N/A	N/A	N/A	
N/A	N/A	N/A	
DCH0034	19	3/4	A1E
DCH2532	20	25/32	
DCH1036	21	13/16	
DCH0078	22	7/8	
DCH1056	24	15/16	
DCH0100	25	1	
DCH0116	27	1.1/16	
DCH0118	29	1.1/8	
DCH0136	30	1.3/16	
DCH0114	32	1.1/4	
DCH0156	33	1.5/16	
DCH0138	35	1.3/8	
DCH0176	37	1.7/16	
DCH0112	38	1.1/2	
DCH0196	40	1.9/16	
DCH0158	41	1.5/8	
DCH1116	43	1.11/16	
DCH0134	44	1.3/4	
DCH1136	46	1.13/16	
DCH0178	48	1.7/8	
DCH0200	51	2	
DCH0216	52	2.1/16	
DCH0218	54	2.1/8	
DCH056M	56	2.3/16	
DCH0214	57	2.1/4	
DCH0256	59	2.5/16	
DCH0238	60	2.3/8	
DCH0212	64	2.1/2	
DCH0296	65	2.9/16	
DCH0258	67	2.5/8	
DCH068M	68	2.11/16	
DCH0234	70	2.3/4	
DCH0278	73	2.7/8	
DCH0300	76	3	
DCH0318	79	3.1/8	
DCH0314	83	3.1/4	
DCH0338	86	3.3/8	
DCH0312	89	3.1/2	
DCH0358	92	3.5/8	
DCH0334	95	3.3/4	
DCH0378	98	3.7/8	
DCH0400	102	4	
DCH0418	105	4.1/8	
DCH0414	108	4.1/4	
DCH0438	111	4.3/8	
DCH0412	114	4.1/2	
DCH0434	121	4.3/4	
DCH0500	127	5	
DCH0514	133	5.1/4	
DCH0512	140	5.1/2	
DCH0600	152	6	
DCH160M	160	6.5/16	
DCH168M	168	6.5/8	
DCH177M	177	6.31/32	
DCH210M	210	8.9/32	