

LR Type Approval Certificate Extension

This is to certify that Certificate No. 95/00134(E1) for the undernoted products is extended and renumbered as shown.

This certificate is issued to:

PRODUCER	Tyco Electronics
PLACE OF PRODUCTION	Raychem Products 300 Constitution Drive Menlo Park CA 94025 United States of America
DESCRIPTION	Raychem flame-retardant heat-shrinkable tubing with or without adhesive sealing.
TYPES	SST-FR, HRSR-FR, HRHF-FR, BSTS-FR and HF-FR
APPLICATION	Marine, offshore and industrial applications
SPECIFIED STANDARDS	IEC60332-1 ASTM D876
SPECIFICATIONS	Temperature rating: Operating temperature range: -55°C to +90°C Minimum recovery temperature: +120°C Voltage rating: 1000V See also sheets 2 to 5

Certificate No.	95/60134(E2)
Issue Date	17 December 2002
Expiry Date	23 October 2005
Sheet	1 of 5


J. Croston

Type SST-FR flame-retardant adhesive-sealing heat-shrinkable tubing.

Part number reference:

Example	SST	-48	-07	M	/FR	/97	/RED	/NM
Description	Product family	Length	Size	Medium wall thickness designation	Flame-retardant tubing designation	Pre-coat adhesive/sealant options	Colour	Options
Options		For 03-04: 30 inches For 07 to 45: 48 inches	See table	Leave blank when not applicable		/97 - hot melt adhesive /226 - mastic sealant	Black (standard - leave blank) Other colors special order: /RED /WHIT	NM - No mark

Product dimensions (in (mm)):

Size	As supplied	Recovered	
	Inside diameter minimum (D)*	Inside diameter maximum (d)	Wall thickness nominal (W)
-03	0.30 (8)	0.10 (3)	0.06 (1.5)
-04	0.40 (10)	0.15 (4)	0.06 (1.5)
-07M	0.75 (19)	0.22 (6)	0.06 (1.5)
-07	0.75 (19)	0.22 (6)	0.10 (2.5)
-11M	1.10 (28)	0.375 (10)	0.11 (2.8)
-11	1.10 (28)	0.375 (10)	0.12 (3.0)
-13M	1.30 (33)	0.375 (10)	0.11 (2.8)
-13	1.30 (33)	0.375 (10)	0.12 (3.0)
-15M	1.50 (38)	0.50 (13)	0.12 (3.0)
-15	1.50 (38)	0.50 (13)	0.14 (3.6)
-17M	1.70 (43)	0.50 (13)	0.12 (3.0)
-17	1.70 (43)	0.50 (13)	0.14 (3.6)
-20M	2.00 (51)	0.75 (19)	0.12 (3.0)
-20	2.00 (51)	0.75 (19)	0.16 (4.1)
-27	2.70 (69)	0.90 (23)	0.16 (4.1)
-30	3.00 (76)	1.25 (32)	0.16 (4.1)
-40	4.00 (102)	1.75 (44)	0.16 (4.1)
-45	4.50 (114)	1.75 (44)	0.16 (4.1)

* When specifications call for coated tubing, reduce allowed minimum inside diameter by 0.10 inch to allow for sealant thickness.

Certificate No. 95/60134(E2)

Issue Date 17 December 2002

Expiry Date 23 October 2005

Sheet 2 of 5

J. Croston

Type HRSR-FR flame-retardant high-ratio semi-rigid heat-shrinkable tubing with or without adhesive.
Type HRSF-FR flame-retardant high-ratio flexible heat-shrinkable tubing with or without adhesive.

Part number reference:

Example	HR	SR	-125	FR	-10	/97	/NM
Description	Product family	Material type	Size	Flame-retardant material designation	Length	Pre-coat adhesive/sealant options	Options
Options		SR: Semi-rigid HF: High-flex	See table below		Standard: 10 inches	/97 - hot melt adhesive /226 - sealant	NM - No mark

Product dimensions (in (mm)):

Size	As supplied	Recovered	
	Inside diameter minimum (D)*	Inside diameter maximum (d)	Wall thickness nominal (W)
-060	0.60 (15)	0.15 (4)	0.06 (1.5)
-125	1.25 (32)	0.24 (6)	0.06 (1.5)
-175	1.75 (44)	0.32 (8)	0.10 (2.5)
-200	2.00 (51)	0.38 (10)	0.11 (2.8)
-250	2.50 (64)	0.50 (13)	0.12 (3.0)
-300	3.00 (76)	0.75 (19)	0.12 (3.0)
-400	4.00 (102)	0.90 (23)	0.14 (3.6)

* When specifications call for coated tubing, reduce allowed minimum inside diameter by 0.10 inch to allow for sealant thickness.

Certificate No. 95/60134(E2)
Issue Date 17 December 2002
Expiry Date 23 October 2005
Sheet 3 of 5


J. Croston

Type BSTS-FR general purpose flame-retardant heat-shrinkable tubing.

Part number reference:

Example	BSTS	-07	M	X25	FR	/RED	/NM
Description	Product family	Size	Medium wall thickness designation	Length	Flame-retardant tubing designation	Colour	Options
Options		See table	Leave blank when not applicable	In feet, Standard: 4 feet and 25 feet		Black (standard - leave blank) Other colors special order: /RED /WHT	NM - No mark

Product dimensions (in (mm)):

Size	As supplied	Recovered	
	Inside diameter minimum (D)	Inside diameter maximum (d)	Wall thickness nominal (W)
-03	0.30 (8)	0.10 (3)	0.06 (1.5)
-04	0.40 (10)	0.15 (4)	0.06 (1.5)
-07M	0.75 (19)	0.22 (6)	0.06 (1.5)
-07	0.75 (19)	0.22 (6)	0.10 (2.5)
-11M	1.10 (28)	0.38 (10)	0.11 (2.8)
-11	1.10 (28)	0.38 (10)	0.12 (3.0)
-13M	1.30 (33)	0.38 (10)	0.11 (2.8)
-13	1.30 (33)	0.38 (10)	0.12 (3.0)
-15M	1.50 (38)	0.50 (13)	0.12 (3.0)
-15	1.50 (38)	0.50 (13)	0.14 (3.6)
-17M	1.70 (43)	0.50 (13)	0.12 (3.0)
-17	1.70 (43)	0.50 (13)	0.14 (3.6)
-20M	2.00 (51)	0.75 (19)	0.12 (3.0)
-20	2.00 (51)	0.75 (19)	0.16 (4.1)
-27	2.70 (69)	0.90 (23)	0.16 (4.1)
-30	3.00 (76)	1.25 (32)	0.16 (4.1)
-35	3.50 (89)	1.25 (32)	0.16 (4.1)
-40	4.00 (102)	1.75 (44)	0.16 (4.1)
-45	4.50 (114)	1.75 (44)	0.16 (4.1)

Certificate No. 95/60134(E2)
 Issue Date 17 December 2002
 Expiry Date 23 October 2005
 Sheet 4 of 5

J. Croston

Type HF-FR flame-retardant high flex heat-shrinkable tubing.

Part number reference:

Example	HF	-11	FR	-25
Description	Product family	Size	Flame-retardant tubing designation	Length
Options		See table below		Standard: 4 feet and 25 feet

Product dimensions (in (mm)):


Size	As supplied	Recovered	
	Inside diameter minimum (D)	Inside diameter maximum (d)	Wall thickness nominal (W)
-04	0.40 (10)	0.15 (4)	0.06 (1.5)
-07	0.75 (19)	0.22 (6)	0.06 (1.5)
-11	1.10 (28)	0.38 (10)	0.11 (2.8)
-13	1.30 (33)	0.38 (10)	0.11 (2.8)
-15	1.50 (38)	0.50 (13)	0.12 (3.0)
-17	1.70 (43)	0.50 (13)	0.12 (3.0)
-20	2.00 (51)	0.75 (19)	0.14 (3.6)
-27	2.70 (69)	0.90 (23)	0.16 (4.1)

"This Certificate is not valid for equipment, the design, ratings or operating parameters of which have been varied from the specimen tested. The manufacturer should notify LR of any modification or changes to the equipment in order to obtain a valid certificate."

The attached Design Appraisal Document No. 95/60134(E2) and its supplementary Type Approval Terms and Conditions form part of this Certificate.

All other details remain as the previous Certificate No. 95/00134(E1) to which this extension should be attached

Certificate No. 95/60134(E2)
Issue Date 17 December 2002
Expiry Date 23 October 2005
Sheet 5 of 5


J. Croston