

Electronics

Accessories Interface Plug-in Relay XT

- For Interface Plug-in Relay XT, pinning 5mm
- Retainer clip with ejection function
- **■** Easy replacement of relays on a densely packed DIN rail
- No reduction of protection class or creepage/clearance with plastic retainer
- Simple plug-in indicator- and protection modules
- **■** White snap-on marking tags
- RoHS compliant (Directive 2002/95/EC)




SCHRACK

Premium socket with screwless terminals for DIN rail mounting

RT 78 72P Premium socket, logical terminal arrangement

- Screwless Clamps
- **■** Mounting of solid wires without tool
- **■** Double Clamps per terminal
- **■** Jumper bars for interconnection
- Open coil circuit for active modules
- **■** Logical terminal arrangement






Approvals

REG.-Nr. 6106 in preparation, c Sus E135149



*) For 1 pole relays (16 A) the relay terminals 11-21, 12-22 and 14-24 have to be bridged.

Technical data	
Rated current	2 x 8 A, 16 A*)
Rated voltage / max.switching voltage AC	240/400 VAC
Dielectric strength coil-contact circuit	5000 Vrms
open contact circuit	1000 Vrms
adjacent contact circuits	2500 Vrms
Clearance / creepage coil-contact circuit	≥ 10 / 10 mm
Material group of insulation parts	≥ IIIa
Insulation to IEC 60664-1	
Type of insulation coil-contact circuit	reinforced
open contact circuit	functional
adjacent contact circuits	functional
Rated insulation voltage	250 V
Pollution degree	2
Rated voltage system	230/400 V
Overvoltage category	III
RoHS - Directive 2002/95/EC	compliant
Degree of protection DIN 40050	IP20









Accessories Interface Plug-in Relay XT (Continued)

2 x 1.5 mm²

1 x 0.75/1/1.5 mm²

2 x 0.75/1 mm²

2 x 1.5 mm²

1 x 0.75/1 mm² 2 x 0.75 mm²

1 x 1.5 mm²

Technical data (Continued)	
Ambient temperature range	
for mounting/handling	-20+70°C
in operation	-40+70°C
Terminals	screwless
Wire strip length	12 mm
Wire cross section	

Wire cross section

solid wire $1 \times 0.75/1/1.5 \text{ mm}^2$ $2 \times 0.75/1 \text{ mm}^2$

with standard isolation (no oversize isolation)

stranded wire without bootlace crimp


·


without bootlace crimp with standard isolation with bootlace crimp


with bootides shirth


with bootlace crimp without isolation or isolation min 18 mm long

How to use, Precautions









For stranded wires with braids 0.05 mm or smaller the use of bootlace crimps is recommended. When using stranded wires without bootlace crimp the clamp must be opened during insertion. Insertion cycles

A (10)

Insertion cycles	A (10)
Max. Insertion Force total	100 N
Mounting distance	0, dense packing
Weight	36 g
Packaging unit	10 pcs

Socket with screwless terminals for DIN rail mounting			
Туре		Part Number	
RT 78 72P	Premium socket, logical terminal arrangement Socket with screwless terminals, pinning 5 mm for DIN rail mounting	1860200-1	
	· · · · · · · · · · · · · · · · · · ·		

Accessories for RT 78 72P			
Туре		Part Number	
RT 17 016	Plastic retaining clip, relay height 15.7 and 25.5 mm	1-1415038-1	
RT 17 040	Marking tag	2-1415038-1	
RT 17 0P1	Jumper bar	1860211-1	








Accessories Interface Plug-in Relay XT (Continued)


Socket with screw-type terminals for DIN rail mounting

RT 78 726 Socket with screw-type terminals, logical terminal arrangement

- Din-rail socket with logical setup of connections (input/output)
- **■** High quality rising clamp terminals
- Captive combination terminal screws









RT 78 725 Socket with screw-type terminals, conventional terminal arrangement

■ Conventional terminal arrangement








Approvals

REG.-Nr. 6106 in process, c Sus E135149 in process

*) For 1 pole relays (16 A) the relay terminals 11-21, 12-22 and 14-24 have to be bridged.

Technical data	RT 78 726	RT 78 725
Rated current	2 x 8 A	, 16 A *)
Rated voltage / max.switching voltage AC	240/4	00 VAC
Dielectric strength coil-contact circuit	5000 Vrms	4000 Vrms
open contact circuit	1000 Vrms	1000 Vrms
adjacent contact circuits	2500 Vrms	2500 Vrms
	≥ 10 / 10 mm	≥ 4.7 / 4.7 mm
Material group of insulation parts	≥	Illa
Insulation to IEC 60664-1		
Type of insulation coil-contact circuit	reinforced	basic
open contact circuit	func	tional
adjacent contact circui	ts func	tional
Rated insulation voltage	25	0 V
Pollution degree		2
Rated voltage system	230/-	400 V
Overvoltage category	I	II
RoHS - Directive 2002/95/EC	com	pliant
Degree of protection DIN 40050	IP	20
Ambient temperature range	-20	+70°C



change.






Electronics

Accessories Interface Plug-in Relay XT (Continued)

Technical data (Continued)	RT 78 726	RT 78 725	
Terminals	scr	ew	
Terminal screw torque acc. IEC 61984	0.5	Nm	
max.	0.7	Nm	
Wire cross section			
single wire	2 x 2.5 mm ²		
fine wire	2 x 2.5 mm ²		
with bootlace crimp (DIN 46228/1)	2 x 1.5 mm ²		
Insertion cycles	n cycles A (10)		
Max. Insertion Force total) N		
Mounting distance 0, dense packing			
Weight	Veight 36 g		
Packaging unit	10 p	ocs	

Socket with	screw-type terminals for DIN rail mounting	
Туре		Part Number
RT 78 726	Socket with screw-type terminals,	
	pinning 5 mm for DIN rail mounting,	
	logical terminal arrangement	6-1415035-1
RT 78 725	Socket with screw-type terminals,	
	pinning 5 mm for DIN rail mounting,	
	conventional terminal arrangement	1860306-1

Accessories for RT 78 725, RT 78 726			
Туре		Part Number	
RT 17 016	Plastic retaining clip, relay height 15.7 and 25.5 mm	1-1415038-1	
RT 17 040	Marking tag	2-1415038-1	



Marking tags

- ■White marking area 15.5 x 6 mm
 ■Snaps on socket in up to 4 positions

LED- and Pr	otectio	n Modules for RT 78 72P, RT 78 725, F	RT 78 726
Easy insertion	of modu	lle into the socket	
Wiring in paral	lel to the	e coil	
Туре			Part Number
PTM TO 0A0	EM09	Protection diode (standard, A1+, A2-)	9-1415036-1
PTM TO OLO	EM01	Protection diode (A1-, A2+)	1415037-1

Type			i ait i vui i ibei
PTM TO 0A0	EM09	Protection diode (standard, A1+, A2-)	9-1415036-1
PTM TO OLO	EM01	Protection diode (A1-, A2+)	1415037-1
PTM U0 524	EM02	RC-network 660 VAC	1-1415037-1
PTM U0 730	EM03	RC-network 110230 VAC	2-1415037-1
PTM V0 524	EM04	Varistor 24 VAC	3-1415037-1
PTM V0 615	EM13	Varistor 115 VAC	6-1415365-1
PTM V0 730	EM05	Varistor 230 VAC	4-1415037-1
PTM R0 730	EM29	Bleeder Resistor 110230 VAC	1-1415539-2

LED			
PTM L0 024	EM18	red LED 624 VDC w. prot.diode (std, A1+, A2-)	5-1415036-1
PTM G0 024	EM12	green LED 624 VDC w. prot.diode (std, A1+, A2-)	2-1415036-1
PTM L1 024	EM08	red LED 624 VDC w. prot. diode (A1-, A2+)	8-1415036-1
PTM L0 060	EM16	red LED 2460 VDC w. prot.diode (std, A1+, A2-)	5-1415539-3
PTM G0 060	EM25	green LED 2460 VDC w. prot.diode (std, A1+, A2-)	7-1415539-7
PTM L0 110	EM19	red LED 48110 VDC w. prot. diode (A1+, A2-)	2-1415392-1
PTM G0 110	EM26	green LED 48110 VDC w. prot diode (A1+, A2-)	1-1415539-7
PTM L0 220	EM27	red LED 110220 VDC w. prot. diode (A1+, A2-)	1-1415539-4
PTM G0 220	EM28	green LED 110220 VDC w. prot diode (A1+, A2-)	1-1415539-6
PTM L0 524	EM07	red LED 624 VDC/VAC	6-1415036-1
PTM G0 524	EM11	green LED 624 VDC/VAC	3-1415036-1
PTM L0 560	EM14	red LED 2460 VDC/VAC	1-1415539-3
PTM G0 560	EM30	green LED 2460 VDC/VAC	1-1415539-5
PTM L0 730	EM06	red LED 110230 VAC	7-1415036-1
PTM G0 730	EM10	green LED 110230 VAC	4-1415036-1



F0231-A

