

APHF1608LSEEQBDZGKC

1.6 x 0.8 mm Full-Color Surface Mount LED



DESCRIPTIONS

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- The Blue source color devices are made with InGaN Light Emitting Diode
- The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- . It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 1.6 x 0.8 mm SMD LED, 0.5 mm thickness
- · Low power consumption
- Package in 8mm tape on 7" diameter reel, 4000 pcs / reel
- · Can produce any color in visible spectrum, including white light
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- Backlight
- · Status indicator
- Home and smart appliances
- · Wearable and portable devices
- Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units: mm; tolerance: ± 0.1)



- Toles.

 1. All dimensions are in millimeters (inches).

 2. Tolerance is ±0.15(0.006") unless otherwise noted.

 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color (Material)	Lens Type	Iv (mcd) @ 2mA [2]		Viewing Angle [1]
			Min.	Тур.	201/2
APHF1608LSEEQBDZGKC	■ Hyper Red (AlGaInP)	Water Clear	4	15	140°
	■ Blue (InGaN)		4	10	
	Green (InGaN)		20	70	

Notes.
1. 61/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
2. Luminous intensity / luminous flux: +/-15%.

3. Luminous intensity value is traceable to CIE127-2007 standards.



ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

D			Va	Value		
Parameter	Symbol	Emitting Color	Тур.	Max.	Unit	
		Hyper Red	630			
Wavelength at Peak Emission I _F = 2mA	λ_{peak}	Blue	460	-	nm	
		Green	515			
		Hyper Red	621		nm	
Dominant Wavelength I _F = 2mA	λ_{dom} [1]	Blue	465	-		
		Green	525			
Spectral Bandwidth at 50% Φ REL MAX		Hyper Red	20			
Spectral Baridwidth at $50\% $	Δλ	Blue	25	-	nm	
IF - ZIIIA		Green	35			
		Hyper Red	25			
Capacitance	С	Blue	100	-	pF	
		Green	45			
		Hyper Red	1.8	2.1		
Forward Voltage I _F = 2mA	V _F ^[2]	Blue	2.65	3.1	V	
•		Green	2.65	3.1		
		Hyper Red		10		
Reverse Current (V _R = 5V)	I _R	Blue	-	50	μΑ	
, ,		Green		50		
Townsendure Coefficient of)		Hyper Red	0.13			
Temperature Coefficient of λ _{peak}	TC_{\lambdapeak}	Blue	0.04	-	nm/°C	
I_F = 2mA, -10°C \leq T \leq 85°C	.,,	Green	0.05			
Tomporature Coefficient of)		Hyper Red	0.06			
Temperature Coefficient of λ _{dom}	TC_{\lambdadom}	Blue	0.03	-	nm/°C	
$I_F = 2mA, -10^{\circ}C \le T \le 85^{\circ}C$		Green	0.03			
Tananaratura Caaffiniant of V		Hyper Red	-1.9			
Temperature Coefficient of V _F	TC_V	Blue	-2.9	-	mV/°C	
I_F = 2mA, -10°C \leq T \leq 85°C	,	Green	-2.9			

Notes:

- Notes.

 1. The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd:±1nm.)

 2. Forward voltage: ±0.1V.

 3. Wavelength value is traceable to CIE127-2007 standards.

 4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at T_A=25°C

Parameter	Symbol	Value			Unit
raiametei		Hyper Red	Blue	Green	Offic
Power Dissipation	P _D ^[1]	75	80	82	mW
Reverse Voltage	V_R	5	5	5	V
Junction Temperature	T _j	115	115	115	°C
Operating Temperature T _{op} -40 to +85			°C		
Storage Temperature	T_{stg}	-40 to +85			°C
DC Forward Current	I _F ^[1]	30	20	20	mA
Peak Forward Current	I _{FM} ^[2]	195	100	100	mA
Electrostatic Discharge Threshold (HBM)	-	3000	250	450	V
Thermal Resistance (Junction / Ambient)	R _{th JA} [3]	730	720	700	°C/W
Thermal Resistance (Junction / Solder point)	R _{th JS} [3]	610	620	590	°C/W

Notes:

1. The maximum ratings are valid for the case of lighting a single chip
When two chips are lit at the same time, each chip should be driven at a current lower than 50% of the absolute maximum ratings
When three chips are lit at the same time, each chip should be driven at a current lower than 30% of the absolute maximum ratings
2. 1/10 Duty Cycle, 0. This Pulse Width.


3. R_{th JA}, R_{th JS} Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad).

4. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity − Ref JEDEC/JESD625-A and JEDEC/J-STD-033.




TECHNICAL DATA

RELATIVE INTENSITY vs. WAVELENGTH





SPATIAL DISTRIBUTION




HYPER RED


Forward Current vs. Forward Voltage T_a = 25 °C 8 Forward current (mA) 2 0 2.1 1.7 1.8 1.9 2.0 Forward voltage (V)










BLUE













GREEN













REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS

300 above 255°C (°C) 260°C max. 30s max. 10s max. 250 3°C/s max. 6°C/s max. 200 150 Temperature pre-heating 100 150~200°C above 217°C 60~120s 60~150s 50 _25°C n 0 50 100 150 200 250 300 (sec) Time




REEL DIMENSION (units: mm)

TAPE SPECIFICATIONS (units:mm)



- 1. Don't cause stress to the LEDs while it is exposed to high temperature.
 2. The maximum number of reflow soldering passes is 2 times.
 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.

 The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening
- liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright
- All design applications should refer to Kingbright application notes available at <a href="https://www.Ki

