

Note: This datasheet may be out of date Please download the latest datasheet of BLM03EB500SH1# from the official website of Murata Manufacturing

https://www.murata.com/en-eu/products/productdetail?partno=BLM03EB500SH1%23

### BLM03EB500SH1#

"#" indicates a package specification code.










< List of part numbers with package codes >


BLM03EB500SH1B BLM03EB500SH1D BLM03EB500SH1J



### Appearance & Shape









(in mm)



### **Features**

- 1. Horizontal winding inner coil structure enables low storage capacitance which result to high noise suppression performance. Effective in LTE range up to 2.6GHz from 700MHz.
- 2. Low DC Resistance. Large Rated Current.
- 3. The small size of BLM03E series (0.6x0.3mm) is suitable for noise suppression in small equipment such as cellular phones.



Automotive
Usage

Powertrain/Safety



# Packaging Information

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	1000
D	180mm Paper Tape	15000
J	330mm Paper Tape	50000

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/08/21



 $\underline{ Please \ download \ the \ latest \ data sheet \ of \ BLM03EB500SH1\# from \ the \ official \ website \ of \ Murata \ Manufacturing} }$ Co., Ltd. https://www.murata.com/en-eu/products/productdetail?partno=BLM03EB500SH1%23

## BLM03EB500SH1#

"#" indicates a package specification code.

Note: This datasheet may be out of date



Shape	SMD
Size Code (in mm)	0603
Size Code (in inch)	0201
Length	0.6mm
Length Tolerance	±0.03mm
Width	0.3mm
Width Tolerance	±0.03mm
Thickness	0.3mm
Thickness Tolerance	±0.03mm
Impedance (at 100MHz)	50Ω
Impedance (at 100MHz) Tolerance	±25%
Impedance (at 1GHz)	255Ω
Impedance (at 1GHz) Tolerance	±40%
Rated Current (at 85°C)	400mA
Rated Current (at 125°C)	300mA
DC Resistance(max.)	0.58Ω
Operating Temperature Range	-55°C to 125°C

Mass(typ.)	0.3mg
Number of Circuit	1

2 of 3

### Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/08/21

<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.




 $\underline{ Please \ download \ the \ latest \ data sheet \ of \ BLM03EB500SH1\# from \ the \ official \ website \ of \ Murata \ Manufacturing} }$ 

https://www.murata.com/en-eu/products/productdetail?partno=BLM03EB500SH1%23

## BLM03EB500SH1#


"#" indicates a package specification code.






In operating temperature exceeding +85°C, derating of current is necessary for BLM03E series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Impedance-Frequency Characteristics



**Derating of Rated Current** 

**Equivalent Circuit** 

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/08/21