



Surface Mount Ultra Fast Rectifier



SMA (DO-214AC)

FEATURES

- Low profile package
- Ideal for automated placement
- Glass passivated pallet chip junction
- Ultrafast reverse recovery time
- Low switching losses, high efficiency
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
Available

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	1.0 A
V_{RRM}	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V
I_{FSM}	30 A
t_{rr}	50 ns, 75 ns
V_F at I_F	1.0 V, 1.7 V
T_J max.	150 °C
Package	SMA (DO-214AC)
Diode variations	Single

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, automotive, and telecommunication.

MECHANICAL DATA

Case: SMA (DO-214AC)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified

Base P/NHM3_X - halogen-free, RoHS-compliant and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B,.....)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS ($T_A = 25\text{ °C}$ unless otherwise noted)									
PARAMETER	SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT
Device marking code		UA	UB	UD	UG	UJ	UK	UM	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at $T_L = 110\text{ °C}$	$I_{F(AV)}$	1.0							A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	30							A
Operating and storage temperature range	T_J, T_{STG}	-55 to +150							°C



ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)										
PARAMETER	TEST CONDITIONS	SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT
Maximum instantaneous forward voltage	1.0 A	$V_F^{(1)}$	1.0			1.7				V
Maximum DC reverse current at rated DC blocking voltage	$T_A = 25\text{ }^\circ\text{C}$	I_R	10							μA
	$T_A = 100\text{ }^\circ\text{C}$		50							
Maximum reverse recovery time	$I_F = 0.5\text{ A}$, $I_R = 1.0\text{ A}$, $I_{rr} = 0.25\text{ A}$	t_{rr}	50			75			ns	
Typical junction capacitance	4.0 V, 1 MHz	C_J	15			10			pF	

Note

(1) Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)										
PARAMETER	SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT	
Maximum thermal resistance	$R_{\theta JA}^{(1)}$	75							$^\circ\text{C/W}$	
	$R_{\theta JL}^{(1)}$	27								

Note

(1) PCB mounted on 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad area

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
US1J-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel
US1J-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel
US1JHE3_A/H (1)	0.064	H	1800	7" diameter plastic tape and reel
US1JHE3_A/I (1)	0.064	I	7500	13" diameter plastic tape and reel
US1J-M3/61T	0.064	61T	1800	7" diameter plastic tape and reel
US1J-M3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel
US1JHM3_A/H (1)	0.064	H	1800	7" diameter plastic tape and reel
US1JHM3_A/I (1)	0.064	I	7500	13" diameter plastic tape and reel

Note

(1) AEC-Q101 qualified

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 5 - Typical Instantaneous Forward Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 6 - Typical Reverse Leakage Characteristics




Fig. 7 - Typical Junction Capacitance





Fig. 8 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[US1B/1T](#) [US1B-E3/1T](#) [US1G/1T](#) [US1G-E3/1T](#) [US1J/1T](#) [US1J-E3/1T](#) [US1M/1T](#) [US1M-E3/1T](#) [US1A/11T](#)
[US1A/13T](#) [US1A/5AT](#) [US1A/61T](#) [US1A/63T](#) [US1A-E3/2GT](#) [US1A-E3/5AT](#) [US1A-E3/61T](#) [US1A-E3/63T](#)
[US1AHE3/2GT](#) [US1AHE3/5AT](#) [US1AHE3/61T](#) [US1AHE3/63T](#) [US1B/11T](#) [US1B/2FT](#) [US1B/2GT](#) [US1B/51T](#)
[US1B/5AT](#) [US1B/61T](#) [US1B/63T](#) [US1B-E3/2GT](#) [US1B-E3/51T](#) [US1B-E3/5AT](#) [US1B-E3/61T](#) [US1B-E3/63T](#)
[US1BHE3/2GT](#) [US1BHE3/5AT](#) [US1BHE3/61T](#) [US1BHE3/63T](#) [US1D/11T](#) [US1D/13T](#) [US1D/2FT](#) [US1D/2GT](#)
[US1D/5AT](#) [US1D/61T](#) [US1D/63T](#) [US1D-E3/11T](#) [US1D-E3/2GT](#) [US1D-E3/5AT](#) [US1D-E3/61T](#) [US1D-E3/63T](#)
[US1DHE3/2GT](#) [US1DHE3/5AT](#) [US1DHE3/61T](#) [US1DHE3/63T](#) [US1G/11T](#) [US1G/13T](#) [US1G/2FT](#) [US1G/2GT](#)
[US1G/51T](#) [US1G/5AT](#) [US1G/61T](#) [US1G/63T](#) [US1G-E3/11T](#) [US1G-E3/2GT](#) [US1G-E3/51T](#) [US1G-E3/5AT](#) [US1G-](#)
[E3/61T](#) [US1G-E3/63T](#) [US1GHE3/2GT](#) [US1GHE3/5AT](#) [US1GHE3/61T](#) [US1GHE3/63T](#) [US1J/11T](#) [US1J/13T](#)
[US1J/2FT](#) [US1J/2GT](#) [US1J/51T](#) [US1J/5AT](#) [US1J/61T](#) [US1J/63T](#) [US1J-E3/11T](#) [US1J-E3/2GT](#) [US1J-E3/51T](#)
[US1J-E3/5AT](#) [US1J-E3/61T](#) [US1J-E3/63T](#) [US1JHE3/2GT](#) [US1JHE3/5AT](#) [US1JHE3/61T](#) [US1JHE3/63T](#) [US1K/11T](#)
[US1K/51T](#) [US1K/5AT](#) [US1K/61T](#) [US1K-E3/5AT](#) [US1K-E3/61T](#) [US1KHE3/5AT](#) [US1KHE3/61T](#) [US1M/11T](#)
[US1M/13T](#) [US1M/2FT](#)