#### T340 Molded Radial



#### **Overview**

The compact, space-saving T340 is transfer molded in precision, with a high impact-resistant plastic that has excellent electrical, physical and moisture-resistant properties. The gold color plastic case permits laser marking with outstanding permanency and legibility. Marking is provided on the top of the case to allow visual inspection for proper polarity and placement after insertion. In addition, positive polarity identification is achieved by an easily recognized molded radius on the positive end of the case. Additionally, this physical polarity identification is readily observed after capacitor placement as a further aid


in the prevention of possible reverse insertion. Standoffs, located in the base of all case sizes, provide vents for air circulation and also to allow easy removal of flux residues from leadwire and circuit board solder joints. With very low impedance and ESR values, the T340 features exceptionally low DC leakage and DF characteristics. The T340 is available in standard ±20%, ±10%, and ±5% (special order) capacitance tolerance. T340 capacitors are highly reliable and exhibit performance characteristics typical of military test standards.

#### **Benefits**

- · Taped and reeled per EIA Specification RS-468
- · Laser-marked case
- Capacitance values of 0.1 μF 330 μF
- Tolerances of ±20% standard, ± 5% and ±10% special order
- Voltage rating of 3 50 VDC
- · Case sizes: A, B, C, D, E, F

## **Applications**

Typical applications include bypassing, coupling, and timing applications in computers, military ordinance, industrial, entertainment, and consumer electronic equipment.



# **Ordering Information**

Т	340	Α	105	M	035	Α	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Packaging
T = Tantalum	Radial Lead Precision Molded Polar Solid Tantalum	A, B, C, D, E,	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = $\pm 20\%$ (standard K = $\pm 10\%$ J = $\pm 5\%$ (available on request)	003 = 3 006 = 6 010 = 10 015 = 15/16 020 = 20 025 = 25 035 = 35 040 = 40 050 = 50	Not Applicable	S = Standard (solder-coated copperweld) T = 100% tin (Sn)-plated	Blank = Bulk 7301 = Tape & Reel 7305 = Ammo 7317 = Ammo

One world. One KEMET




#### **Performance Characteristics**

Item	Performance Characteristics
Operating Temperature	-55°C to 125°C
Rated Capacitance Range	0.1 – 330 μF at 120 Hz/25°C
Capacitance Tolerance	M tolerance (20%) standard, J tolerance (5%), K tolerance (10%) special order
Rated Voltage Range	3 –50 V
DF (120 Hz at 25°C)	Refer to Part Number Electrical Specification Table
ESR and Impedance (100 kHz at 25°C)	Refer to Part Number Electrical Specification Table (for reference only)
Leakage Current	Refer to Part Number Electrical Specification Table (at rated voltage up to +85°C and 2/3 of rated voltage applied at 125°C)

# **Dimensions - Millimeters (Inches)**

Metric will govern



F case size is the same as D, but with 0.200" (5.0 mm) lead spacing. Specify T340F when ordering this spacing.

Case Size	H** (MAXIMUM)	W (MAXIMUM)	T (MAXIMUM)	Lead Spacing S	Lead Length L	Lead Diameter D
А	0.287	0.185	0.165	0.100 ±0.020	0.600±0.078	0.020±0.001
A	(7.3)	(4.7)	(4.2)	(2.5 ±0.5)	(15.0±2.0)	(0.50±0.03)
В	0.327	0.283	0.157	0.200±0.020	0.600±0.078	0.020±0.001
D	(8.3)	(7.2)	(4.0)	(5.0±0.5)	(15.0±2.0)	(0.50±0.03)
С	0.413	0.287	0.169	0.200±0.020	0.600±0.078	0.020±0.001
L C	(10.5)	(7.3)	(4.3)	(5.0±0.5)	(15.0±2.0)	(0.50±0.03)
D	0.413	0.484	0.287	0.400±0.020	0.600±0.078	0.025±0.001
D D	(10.5)	(12.3)	(7.3)	(10.0±0.5)	(15.0±2.0)	(0.64±0.03)
Е	0.413	0.484	0.484	0.400±0.020	0.600±0.078	0.025±0.001
	(10.5)	(12.3)	(12.3)	(10.0±0.5)	(15.0±2.0)	(0.64±0.03)
F	0.413	0.484	0.287	0.200±0.020	0.600±0.078	0.025±0.001
г	(10.5)	(12.3)	(7.3)	(5.0±0.5)	(15.0±2.0)	(0.64±0.03)

<sup>\*\*</sup>Includes Standoff Height of 0.015±0.005" (0.38±0.13 mm) for All Case Sizes.



# **Table 1 - Ratings & Part Number Reference**

Rated Voltage	Rated Capacitance	Case Code	KEMET Part Number	DC Leakage	DF	ΙΜΡ Ω
(V) 85°C	μF			μΑ at 25°C Maximum/5 Minutes	% at 25°C 120 Hz Maximum	at 10 kHz Maximum
3	10.0	A	T340A106(1)003A(3)	1.0	6	6.0
3	15.0	А	T340A156(1)003A(3)	1.0	6	3.2
3	33.0	В	T340B336(1)003A(3)	1.5	6	2.1
3	47.0	В	T340B476(1)003A(3)	3.0	6	1.8
3	68.0	С	T340C686(1)003A(3)	4.0	6	1.5
3	100.0	C	T340C107(1)003A(3)	5.0	6	1.2
6	6.8	A	T340A685(1)006A(3)	1.0	6	6.0
6	10.0	В	T340B106(1)006A(3)	1.0	6	
6	12.0	В	T340B126(1)006A(3)	1.0	6	
6	15.0	В	T340B156(1)006A(3)	1.0	6	
6	18.0	В	T340B186(1)006A(3)	1.0	6	0.1
6	22.0	В	T340B226(1)006A(3)	2.5	6	2.1
6	27.0	С	T340C276(1)006A(3)	2.5	6	
6	33.0	C	T340C336(1)006A(3)	2.5	6	
6	39.0	C	T340C476(1)006A(3)	2.5	6	1.5
6 6	47.0 56.0	C	T340C476(1)006A(3) T340C566(1)006A(3)	3.0 5.0	6 6	1.5
6	56.0 68.0	C C	T340C566(1)006A(3)	5.0	6	
6	82.0	D/F		1	6	
6	100.0	D/F	T340(2)826(1)006A(3)	5.0 5.0	6	
6	120.0	D/F	T340(2)107(1)006A(3)	5.0	6	
6	150.0	D/F	T340(2)127(1)006A(3) T340(2)157(1)006A(3)	8.0	6	0.8
6	180.0	D/F	T340(2)187(1)000A(3)	10.0	6	0.0
6	220.0	D/F	T340(2)187(1)000A(3)	10.0	6	
6	330.0	E E	T340E337(1)006A(3)	10.0	8	0.5
10	4.7	A	T340A475(1)010A(3)	1.0	6	7.5
10	5.6	В	T340B565(1)010A(3)	1.0	6	7.5
10	6.8	В	T340B303(1)010A(3)	1.0	6	
10	8.2	В	T340B825(1)010A(3)	1.0	6	
10	10.0	В	T340B106(1)010A(3)	1.0	6	
10	12.0	В	T340B126(1)010A(3)	1.0	6	
10	15.0	В	T340B156(1)010A(3)	3.0	6	2.5
10	18.0	C	T340C186(1)010A(3)	3.0	6	2.0
10	22.0	C	T340C226(1)010A(3)	3.0	6	
10	27.0	C	T340C276(1)010A(3)	3.0	6	
10	33.0	C	T340C336(1)010A(3)	5.0	6	1.7
10	39.0	Č	T340C396(1)010A(3)	5.0	6	
10	47.0	D/F	T340(2)476(1)010A(3)	5.0	6	
10	56.0	D/F	T340(2)566(1)010A(3)	5.0	6	
10	68.0	D/F	T340(2)686(1)010A(3)	5.0	6	
10	82.0	D/F	T340(2)826(1)010A(3)	8.0	6	
10	100.0	D/F	T340(2)107(1)010A(3)	10.0	6	1.0
10	120.0	D/F	T340(2)127(1)010A(3)	10.0	6	
10	150.0	D/F	T340(2)157(1)010A(3)	10.0	6	
10	220.0	Ē	T340E227(1)010A(3)	10.0	6	0.5
15	3.3	Α	T340A335(1)015A(3)	1.0	6	9.0
15	3.9	В	T340B395(1)015A(3)	1.0	6	
15	4.7	В	T340B475(1)015A(3)	1.0	6	
15	5.6	В	T340B565(1)015A(3)	1.0	6	
15	6.8	В	T340B685(1)015A(3)	1.0	6	
15	8.2	В	T340B825(1)015A(3)	1.0	6	
15	10.0	В	T340B106(1)015A(3)	3.0	6	3.2
15	12.0	С	T340C126(1)015A(3)	3.0	6	
(V) 85°C	μF		(see below for part options)	µA at 25°C Maximum/5 Minutes	% at 25°C 120 Hz Maximum	at 10 kHz Maximum
Rated Voltage	Rated Capacitance	Case Code	KEMET Part Number	DC Leakage	DF	IMP Ω

<sup>(1)</sup> To complete KEMET part number, insert M for  $\pm 20\%$ , K for  $\pm 10\%$  or J for 5%. Designates Capacitance tolerance.

 $<sup>(2) \</sup> To \ complete \ \textit{KEMET part number, insert letter "D" for 10.0 \ mm \ (0.394) \ lead \ spacing \ or \ letter "F" for 5.0 \ mm \ (0.197) \ lead \ spacing.} \ Designates \ Lead \ spacing.$ 

<sup>(3)</sup> To complete KEMET part number, insert T = 100% Matte Tin (Sn) Plated, S = Standard Solder coated (SnPb 5% Pb minimum). Designates termination finish. Higher voltage and better capacitance tolerance products may be substitued for an order within the same case size at KEMET's option.



# Table 1 - Ratings & Part Number Reference cont'd

Rated Voltage	Rated Capacitance	Case Code	KEMET Part Number	DC Leakage	DF	ΙΜΡ Ω
(V) 85°C	μF			μΑ at 25°C Maximum/5 Minutes	% at 25°C 120 Hz Maximum	at 10 kHz Maximum
15	15.0	С	T340C156(1)015A(3)	3.5	6	2.5
15	18.0	С	T340C186(1)015A(3)	4.0	6	0.1
15	22.0	С	T340C226(1)015A(3)	4.0	6	2.1
15	27.0	С	T340C276(1)015A(3)	5.0	6	
15 15	33.0 39.0	C D/F	T340C336(1)015A(3) T340(2)396(1)015A(3)	5.0 7.0	6 6	
15	47.0	D/F	T340(2)476(1)015A(3)	7.0	6	1.3
15	56.0	D/F	T340(2)470(1)013A(3)	8.0	6	1.3
15	68.0	D/F	T340(2)686(1)015A(3)	9.0	6	1.1
15	82.0	D/F	T340(2)826(1)015A(3)	10.0	6	1.1
15	100.0	E	T340(2)020(1)015A(3)	10.0	6	0.8
15	150.0	E	T340E157(1)015A(3)	10.0	6	0.6
20	2.2	A	T340A225(1)020A(3)	1.0	6	12.0
20	3.3	В	T340B335(1)020A(3)	1.0	6	8.0
20	4.7	В	T340B475(1)020A(3)	1.5	6	5.5
20	6.8	В	T340B685(1)020A(3)	2.5	6	4.2
20	15.0	С	T340C156(1)020A(3)	5.0	6	2.5
20	47.0	D	T340D476(1)020A(3)	9.0	6	1.3
20	100.0	E	T340E107(1)020A(3)	10.0	6	0.8
25	1.5	Α	T340A155(1)025A(3)	1.0	6	17.0
25	2.7	В	T340B275(1)025A(3)	1.0	6	
25	3.3	В	T340B335(1)025A(3)	1.0	6	
25	3.9	В	T340B395(1)025A(3)	1.0	6	
25	4.7	В	T340B475(1)025A(3)	2.0	6	5.5
25	5.6	С	T340C565(1)025A(3)	2.0	6	
25	6.8	С	T340C685(1)025A(3)	3.0	6	4.2
25	8.2	С	T340C825(1)025A(3)	3.0	6	
25	10.0	С	T340C106(1)025A(3)	3.5	6	3.0
25	12.0	С	T340C126(1)025A(3)	3.5	6	
25	15.0	C	T340C156(1)025A(3)	4.0	6	
25	18.0	D/F	T340(2)186(1)025A(3)	5.0	6	
25	22.0	D/F	T340(2)226(1)025A(3)	5.5	6	2.0
25	27.0	D/F	T340(2)276(1)025A(3)	7.0	6	1.5
25 25	33.0	D/F D/F	T340(2)336(1)025A(3)	8.0	6	1.5
25 25	39.0 47.0	D/F D/E/F	T340(2)396(1)025A(3) T340(2)476(1)025A(3)	10.0 10.0	6 6	1.3
25 25	47.0 68.0	D/E/F Е	T340E686(1)025A(3)	10.0	6	0.9
35	0.10	A	T340L080(1)025A(3)	1.0	6	220.0
35	0.10	A	T340A104(1)035A(3)	1.0	6	150.0
35	0.13	A	T340A134(1)035A(3)	1.0	6	100.0
35	0.33	Ā	T340A334(1)035A(3)	1.0	6	75.0
35	0.47	Ä	T340A474(1)035A(3)	1.0	6	50.0
35	0.68	A	T340A684(1)035A(3)	1.0	6	36.0
35	1.0	A	T340A105(1)035A(3)	1.0	6	25.0
35	1.2	В	T340B125(1)035A(3)	1.0	6	15.0
35	1.5	В	T340B155(1)035A(3)	1.0	6	[
35	1.8	В	T340B185(1)035A(3)	1.0	6	
35	2.2	В	T340B225(1)035A(3)	1.0	6	11.0
35	2.7	В	T340B275(1)035A(3)	1.0	6	
35	3.3	B/C	T340(2)335(1)035A(3)	1.0	6	7.5
35	3.9	С	T340C395(1)035A(3)	1.0	6	
35	4.7	С	T340C475(1)035A(3)	2.5	6	5.5
35	5.6	С	T340C565(1)035A(3)	2.5	6	
(V) 85°C	μF		(see below for part options)	μΑ at 25°C Maximum/5 Minutes	% at 25°C 120 Hz Maximum	at 10 kHz Maximum
Rated Voltage	Rated Capacitance	Case Code	KEMET Part Number	DC Leakage	DF	IMP Ω

<sup>(1)</sup> To complete KEMET part number, insert M for  $\pm 20\%$ , K for  $\pm 10\%$  or J for 5%. Designates Capacitance tolerance.

<sup>(2)</sup> To complete KEMET part number, insert letter "D" for 10.0 mm (0.394) lead spacing or letter "F" for 5.0 mm (0.197) lead spacing. Designates Lead spacing.

<sup>(3)</sup> To complete KEMET part number, insert T = 100% Matte Tin (Sn) Plated, S = Standard Solder coated (SnPb 5% Pb minimum). Designates termination finish. Higher voltage and better capacitance tolerance products may be substitued for an order within the same case size at KEMET's option.



# Table 1 - Ratings & Part Number Reference cont'd

Rated Voltage	Rated Capacitance	Case Code	KEMET Part Number	DC Leakage	DF	ΙΜΡ Ω
(V) 85°C	μF			μΑ at 25°C Maximum/5 Minutes	% at 25°C 120 Hz Maximum	at 10 kHz Maximum
35	6.8	С	T340C685(1)035A(3)	3.0	6	4.2
35	8.2	С	T340C825(1)035A(3)	4.0	6	
35	10.0	C/D	T340(2)106(1)035A(3)	4.0	6	2.8
35	12.0	D/F	T340(2)126(1)035A(3)	5.0	6	
35	15.0	D/F	T340(2)156(1)035A(3)	5.0	6	2.2
35	18.0	D/F	T340(2)186(1)035A(3)	8.0	6	4.0
35	22.0	D/F	T340(2)226(1)035A(3)	8.0	6	1.9
35	27.0	D/F	T340(2)276(1)035A(3)	10.0	6	1.4
35 35	33.0 47.0	D/E/F E	T340(2)336(1)035A(3)	10.0	6 6	1.4
40	0.10	A	T340E476(1)035A(3) T340A104(1)040A(3)	10.0 1.0	6	200.0
40	0.10	A	T340A104(1)040A(3)	1.0	6	140.0
40	0.15	A	T340A134(1)040A(3)	1.0	6	95.0
40	0.22	A	T340A334(1)040A(3)	1.0	6	70.0
40	0.47	A	T340A474(1)040A(3)	1.0	6	46.0
40	0.47	A	T340A474(1)040A(3)	1.0	6	34.0
40	1.0	A	T340A004(1)040A(3)	1.0	6	23.0
40	1.5	В	T340B155(1)040B(3)	1.0	6	14.0
40	2.2	В	T340B133(1)040A(3)	1.7	6	10.0
40	3.3	C	T340C335(1)040A(3)	2.3	6	7.0
40	4.7	Č	T340C475(1)040A(3)	3.0	6	5.0
40	6.8	Č	T340C685(1)040A(3)	3.5	6	3.9
40	10.0	D	T340D106(1)040A(3)	4.5	6	2.6
40	15.0	D	T340D156(1)040A(3)	6.0	6	2.0
40	22.0	D	T340D226(1)040A(3)	9.0	6	1.7
40	33.0	E	T340E336(1)040A(3)	10.0	6	1.3
40	47.0	Е	T340E476(1)040A(3)	10.0	6	1.0
50	0.10	Α	T340A104(1)050A(3)	1.0	6	220.0
50	0.15	Α	T340A154(1)050A(3)	1.0	6	150.0
50	0.22	Α	T340A224(1)050A(3)	1.0	6	100.0
50	0.33	Α	T340A334(1)050A(3)	1.0	6	75.0
50	0.39	В	T340B394(1)050A(3)	1.0	6	
50	0.47	В	T340B474(1)050A(3)	1.0	6	50.0
50	0.56	В	T340B564(1)050A(3)	1.0	6	
50	0.68	В	T340B684(1)050A(3)	1.0	6	36.0
50	0.82	В	T340B824(1)050A(3)	1.0	6	
50	1.0	В	T340B105(1)050A(3)	1.0	6	25.0
50	1.2	В	T340B125(1)050A(3)	1.0	6	
50	1.5	B/C	T340(2)155(1)050A(3)	1.1	6	15.0
50	1.8	В	T340B185(1)050A(3)	1.1	6	
50	2.2	B/C	T340(2)225(1)050A(3)	1.5	6	11.0
50	2.7	C	T340C275(1)050A(3)	1.5	6	7.5
50	3.3	C/D	T340(2)335(1)050A(3)	2.5	6	7.5
50	3.9	C	T340(3)475(1)050A(3)	3.0	6	F. F.
50	4.7	C/D	T340(2)475(1)050A(3)	3.5	6	5.5
50 50	5.6	C D/F	T340C565(1)050A(3)	4.0	6 6	4.0
50 50	6.8 8.2	D/F	T340(2)685(1)050A(3) T340(2)825(1)050A(3)	5.0 6.0	6	4.0
50 50	10.0	D/F	T340(2)825(1)050A(3)	7.0	6	2.8
50	12.0	D/F	T340(2)126(1)050A(3)	8.0	6	2.0
50	15.0	D/F	T340(2)156(1)050A(3)	9.0	6	2.2
50	18.0	D/F	T340(2)186(1)050A(3)	10.0	6	2.2
50	22.0	E	T340E226(1)050A(3)	10.0	6	1.7
(V) 85°C	μF	-	(see below for part options)	μA at 25°C Maximum/5 Minutes	% at 25°C 120 Hz Maximum	at 10 kHz Maximum
Rated Voltage	Rated Capacitance	Case Code	KEMET Part Number	DC	DF	IMP Ω
Rateu voitage	катей бараспансе	Case Code	NEWEL PARL NUMBER	Leakage	νr	IIWP 11

<sup>(1)</sup> To complete KEMET part number, insert M for  $\pm 20\%$ , K for  $\pm 10\%$  or J for 5%. Designates Capacitance tolerance.


<sup>(2)</sup> To complete KEMET part number, insert letter "D" for 10.0 mm (0.394) lead spacing or letter "F" for 5.0 mm (0.197) lead spacing. Designates Lead spacing.

<sup>(3)</sup> To complete KEMET part number, insert T = 100% Matte Tin (Sn) Plated, S = Standard Solder coated (SnPb 5% Pb minimum). Designates termination finish. Higher voltage and better capacitance tolerance products may be substitued for an order within the same case size at KEMET's option.



#### **Recommended Voltage Derating Guidelines**

	−55°C to 85°C	85°C to 125°C
% Change in working DC voltage with	$V_{_{R}}$	66% of V <sub>R</sub>
temperature		



## **Ripple Current/Ripple Voltage**

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage that may be applied is limited by following criteria:

- 1. Dissipated power must not exceed the limits specified for the Series.
- 2. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.
- 3. The negative peak AC voltage in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage.

Thermal capacities for the various case sizes have been determined empirically and are listed below. The "ripple voltage" permissible may be calculated from the impedance and ESR data shown in the respective product section.

Temperature Compensation Multipliers for Maximum Power Dissipation					
T ≤ 25°C	T ≤ 85°C	T ≤ 125°C			
1.00 0.90 0.40					

T= Environmental Temperature

Maximum allowable rms ripple voltage or current may be determined as follows:

 $I(max) = \sqrt{P max/R}$  $E(max) = \sqrt{P max/R}$ 

I = rms ripple current (amperes)

E = rms ripple voltage (volts)


P max = Maximum power dissipation (watts)

R = ESR at specified frequency (ohms)

Case Size	Maximum Power Dissipation (Pmax) Watts at 25°C
А	0.09
В	0.09
С	0.100
D/F	0.125



# **Optimum Solder Wave Profile**



# **Reverse Voltage**

Although these are polar capacitors, some degree of transient voltage reversal is permissible, as seen below. The capacitors should not be operated continuously in reverse mode, even within these limits.


Temperature	Pecentage of Rated Voltage
+25°C	15
+85°C	5
+125°C	1




#### **Mounting**

All encased capacitors will pass the Resistance to Soldering Heat Test of MIL-STD-202, Method 210, Condition C. This test simulates wave solder of topside board mount product. This demonstration of resistance to solder heat is in accordance with what is believed to be the industry standard. More severe treatment must be considered reflective of an improper soldering process. The above figure is a recommended solder wave profile for both axial and radial leaded solid tantalum capacitors.

# **Capacitor Marking**







#### **Storage**

Tantalum molded radial capacitors should be stored in normal working environments. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 60°C RH. Storage at high temperature may cause a small, temporary increase in leakage current (measured under standard conditions), but the original value is usually restored within a few minutes after application of rated voltage. Storage at high humidity may increase capacitance and dissipation factor. Solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. For optimized solderability capacitors stock should be used promptly, preferably within three years of receipt.

#### **Tape & Reel Packaging Information**


KEMET offers Solid Tantalum Capacitors fully compatible for use with automatic insertion machines for radial-lead components. Aris Reeling meets all requirements of EIA Standard RS-468. KEMET capacitors are wound on a precision made ARIS Reel Package. ARIS Ammo Package is also available.

**Table 2 - Packaging Quantity** 

Case Size	Standard Bulk Quantity	Standard Reel Quantity	Reel C-Spec	Ammo Pack Quantity
А	300	1,000	C-7301	1,600
В	300	1,000	C-7301	1,500
С	200	1,000	C-7301	1,500
D	100	250	C-7301	450
Е	50	150	C-7301	N/A
F	100	N/A	N/A	N/A



# Figure 1



Dimension	Symbol	Nominal mm (inch)		Tolerance mm (inch)	
Body Height (1)	Α	10.50 (0.413)		±0.38 (±0.015) Maximum	
Body Width (1)	A <sub>1</sub>	15.24	(0.600)	±0.38 (±0.01	5) Maximum
Sprocket Hole Diameter	$D_{o}$	4.0 (0	).157)	±0.3 (±	0.012)
Lead Diameter	d	0.51 (0.020)	or 0.64 (0.025)	±0.05	±0.03 (±0.001)
Lead Center (5)	F	5.0 (0.197)	2.5 (0.098)	+0.8 (+0.032)	-0.2 (-0.008)
Component Base to Tape Center (2) (4) (6)	Н	16.0 - 21.0 (0	0.630 - 0.827)	Referen	ce Only
Lead Standoff Height	H <sub>o</sub>		N	/A	
Component Height Above Tape Center	H <sub>1</sub>	32.25 (1.270)		Maximum	
Component Alignment Front to Rear	ΔΗ	0		±2.0 (±0.079)	
Cut Out Length	L	11.0 (	0.433)	Maximum	
Lead Protrusion	L,	2.0 (0	0.079)	Maximum	
Component Pitch (5)	Р	12.7 (	0.500)	±1.0 (±0.039)	
Sprocket Hole Pitch (3)	$P_0$	12.7 (	0.500)	±0.03 (±0.012)	
Sprocket Hole Center to Lead Center (4) (5)	P <sub>1</sub>	3.85 (0.152)	4.76 (0.188)	5.1 (0.201)	±0.7 (±0.028)
Sprocket Hole Center to Component Center	$P_{2}$	6.35 (	0.250)	±1.31 (:	±0.051)
Body Thickness	T <sub>0</sub>	6.35 (	0.250)	±1.3 Maximum	
Total Tape Thickness	T	0.7 (	0.28)	±0.02 (±0.008)	
Carrier Tape Width	W	18.0 (0.709)		+1.0/-0.5 (+0	.039/-0.020)
Hold-Down Tape Width	W <sub>o</sub>	15 (0.561) or 6 (0.236)		+1.0/-0.8 (+0.039/-0.031	
Sprocket Hole Location	W <sub>1</sub>	9.0 (0	0.354)	+0.075/-0.5 (+0.030/-0.020)	
Hold-Down Tape Location	W <sub>2</sub>	3.0 (0.118) o	r 12.0 (0.472)	Maximum	

#### Notes:

- (1) See Dimensions table for specific values per case size
- (2) Reference only
- (3) Cumulative pitch error ±1.0 mm (0.039") maximum in 20 consecutive sprocket hole locations.
- (4) Measured at bottom of standoff.
- (5) P, P1 and F measured at egress from carrier tape.
- (6) H dimensions for T370 D and E 16.5 mm  $\pm 0.5$  mm  $(0.650"\pm 0.020")$

On polar devices, the positive (+) lead exits from container first.

<sup>\*</sup> Lead spacings are 2.5 mm (0.098") center to center

<sup>\*\*</sup> Lead spacings are 5.0 mm (0.197") center to center.



#### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### **Disclaimer**

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### KEMET:

T340C396J010AS T340C156K025AS T340D227K006AS T340F476K025AS T340F107M010AS T340A105M040AS T340C226M015AS T340C106K025AS T340C106K035AS T340C106M025AS T340D476K025AS T340E227M010AS T340D107M010AS T340C336K015AS T340B106M015AS T340C475M035AS T340A105K035AS7301 T340D336K035AS T340D336M035AS T340C685M035AS T340D186K025AS T340B225M050AS T340A105M035AS T340C106K035AS7301 T340C565K050AS T340D476M020AS T340E227K010AS T340E476K035AS T340E476M035AS T340B105M050AS T340C685K035AS T340D476M016AS T340D106M035AS T340A105M035AT7301 T340C336K015AT T340D106M035AT T340B106M015AT T340C106M025AT T340C156K025AT7301 T340A105M035AT T340E227K010AT T340C685M035AT7301 T340D476K025AT T340E476K035AT T340C475M035AT7301 T340E227K010AT7301 T340A155K025AS T340A155M025AS T340A475M010AS T340A684K035AS T340B106M016AS T340B225K035AS T340B225K050AS T340B335K035AS7301 T340B475M025AS T340C226K015AS T340C226M016AS T340C685M040AS T340D106K050AS T340D106M050AS T340D186K035AS T340D186M050AS T340D226K035AS T340D226M040AS T340D686M016AS T340D825K050AS T340E107K020AS T340E107M020AS T340C476K006AS7301 T340C476M006AS7301 T340C475M050AS7301 T340E107M016AS7301 T340B225K050AS7301 T340C106M035AS7301 T340E157M016AS7301 T340C336M015AS7301 T340E226K050AS7301 T340A155K025AS7301 T340A155M025AS7301 T340A224M040AS7301 T340C156M020AS7301 T340A685K006AS T340C475K035AS T340D156M050AT7301 T340A684K035AT7301 T340B105K050AT7301 T340B105M050AT7301 T340E686M025AT7301 T340D476M020AS7301 T340A225K020AS7301 T340A225M020AS7301 T340A684K035AS7301 T340B125K035AS7301 T340B155M035AS7301 T340B155K035AS7301 T340C155M050AS7301 T340D106M040AS7301 T340D686M016AS7301 T340D156M035AS7301 T340C335M035AS7301