



Type 2536 Rotor-X Standard Mount Paddlewheel

Flow:

- Operating range: 0.1 to 6 m/s, 0.3 to 20 ft/s
- Open collector output
- Installs into pipe sizes: DN15 to DN900, 0.5 to 36 in
- Max Pressure rating: PP 12.5 bar @ 20 °C, 180 psi @ 68 °F PVDF 14 bar @ 20 °C, 200 psi @ 68 °F
- Rotor: PVDF
- Compatibility: 8900, 9900, 9900-1BC, 9950
- Power source: <20mA @ 3.3 to 24 VDC
- *Only Signet installation fittings
- PVC 2536 version DN15 to DN100 (½ to 4 in.) for concentrated Sodium Hypochlorite 12.5% dosing application in water treatment

MFR #	Body	Pin	Pipe Size (inch)	Sensor Type	Code
3-2536-P0	PP	Titanium	0.5 - 4.0	-X0	198 840 143
3-2536-P1	PP	Titanium	5.0 - 8.0	-X1	198 840 144
3-2536-P2	PP	Titanium	10.0 - 36.0	-X2	198 840 145
3-2536-T0	PVDF	PVDF	0.5 - 4.0	-X0	198 840 149
3-2536-V0	PVDF	Hastelloy C	0.5 - 4.0	-X0	198 840 146
3-2536-V1	PVDF	Hastelloy C	5.0 - 8.0	-X1	198 840 147
3-2536-U0	PVC	Titanium	0.5 - 4.0	-X0	159 001 843

The technical data are not binding. They neither constitute expressly warranted characteristics nor guaranteed properties nor a guaranteed durability. They are subject to modification. Our General Terms of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland

Phone +41 -(0)52-631 1111

e-mail: info.ps@georgfischer.com

Internet: <http://www.gfps.com>