

Single Phase Bridge Rectifier, 25 A, 35 A



D-34

FEATURES

- Universal, 3 way terminals: push-on, wrap around or solder
- High thermal conductivity package, electrically insulated case
- Center hole fixing
- Excellent power/volume ratio
- Nickel plated terminals solderable using lead (Pb)-free solder; solder alloy Sn/Ag/Cu (SAC305); solder temperature 260 °C to 275 °C
- UL E300359 approved 
- Designed and qualified for industrial and consumer level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

I_O	25 A, 35 A
V_{RRM}	1400 V to 1600 V
Package	D-34
Circuit configuration	Single phase bridge

DESCRIPTION

A range of extremely compact, encapsulated single phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and instrumentation applications.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES 26MB..A	VALUES 36MB..A	UNITS
I_O		25	35	A
	T_C	70	55	°C
I_{FSM}	50 Hz	400	475	A
	60 Hz	420	500	
I^2_t	50 Hz	790	1130	A ² s
	60 Hz	725	1030	
V_{RRM}	Range	1400 to 1600		V
T_J		-55 to +150		°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT T_J MAXIMUM mA
26MB..A	140	1400	1500	2
36MB..A	160	1600	1700	

**FORWARD CONDUCTION**

PARAMETER	SYMBOL	TEST CONDITIONS		VALUES 26MB..A	VALUES 36MB..A	UNITS	
Maximum DC output current at case temperature	I _O	Resistive or inductive load		25	35	A	
		Capacitive load		20	28		
				65	60	°C	
Maximum peak, one cycle non-repetitive forward current	I _{FSM}	t = 10 ms	No voltage reapplied	Initial T _J = T _J maximum	400	475	A
		t = 8.3 ms			420	500	
		t = 10 ms	100 % V _{RRM} reapplied		335	400	
		t = 8.3 ms			350	420	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied	Initial T _J = T _J maximum	790	1130	A ² s
		t = 8.3 ms			725	1030	
		t = 10 ms	100 % V _{RRM} reapplied		560	800	
		t = 8.3 ms			512	730	
Maximum I ² √t for fusing	I ² √t	I ² t for time t _x = I ² √t x √t _x ; 0.1 ≤ t _x ≤ 10 ms, V _{RRM} = 0 V		5.6	11.3	kA ² √s	
Low level of threshold voltage	V _{F(TO)1}	(16.7 % x π x I _{F(AV)}) < I < π x I _{F(AV)} , T _J maximum		0.70	0.74	V	
High level of threshold voltage	V _{F(TO)2}	(I > π x I _{F(AV)}), T _J maximum		0.75	0.79		
Low level forward slope resistance	r _{t1}	(16.7 % x π x I _{F(AV)}) < I < π x I _{F(AV)} , T _J maximum		7.0	5.5	mΩ	
High level forward slope resistance	r _{t2}	(I > π x I _{F(AV)}), T _J maximum		6.4	5.2		
Maximum forward voltage drop	V _{FM}	T _J = 25 °C, t _p = 400 μs, I _{FM} = 40 A _{pk} (26MB), I _{FM} = 55 A _{pk} (36MB)		1.25	1.3	V	
Maximum DC reverse current per diode	I _{RRM}	T _J = 25 °C, at V _{RRM}		10	10	μA	
RMS isolation voltage base plate	V _{ISOL}	f = 50 Hz, t = 1 s		2700	2700	V	

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES 26MB-A	VALUES 36MB-A	UNITS
Junction and storage temperature range	T _J , T _{Stg}		-55 to 150		°C
Maximum thermal resistance, junction to case per bridge	R _{thJC}		1.7	1.35	K/W
Maximum thermal resistance, case to heatsink	R _{thCS}	Mounting surface, smooth, flat, and greased	0.2		
Mounting torque ± 10 %		Bridge to heatsink	2.0		Nm
Approximate weight			20		g




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Forward Voltage Drop Characteristics




Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Current Ratings Characteristics




Fig. 7 - Forward Voltage Drop Characteristics




Fig. 8 - Total Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current





Fig. 10 - Maximum Non-Repetitive Surge Current

ORDERING INFORMATION TABLE

Device code	VS-	36	MB	160	A
	1	2	3	4	5
1	Vishay Semiconductors product				
2	Current rating code				
3	Circuit configuration:				
	MB = Single phase european coding				
4	Voltage code x 10 = V_{RRM}				
5	Diode bridge rectifier:				
	A = 26 MB, 36 MB series				


CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95326

D-34

DIMENSIONS in millimeters (inches)



Suggested plugging force:
200 N max; axially applied to fast-on terminals



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[VS-26MB05A](#) [VS-26MB100A](#) [VS-26MB10A](#) [VS-26MB120A](#) [VS-26MB140A](#) [VS-26MB160A](#) [VS-26MB20A](#) [VS-26MB40A](#) [VS-26MB60A](#) [VS-26MB80A](#) [VS-36MB05A](#) [VS-36MB100A](#) [VS-36MB10A](#) [VS-36MB120A](#) [VS-36MB140A](#) [VS-36MB160A](#) [VS-36MB20A](#) [VS-36MB40A](#) [VS-36MB60A](#) [VS-36MB80A](#) [VS-26MB06](#)