



# IMPACT WRENCH 1/2" XR 18V BRUSHLESS 1396 NM DCF900NT-XJ

- XR 18V Latest Generation High Torque impact wrench
- Performance: Torque of up to 1898 Nm ensures the removal of the tightest bolts
- Access to the most difficult to access confined areas and bolts: Ultra compact and lightweight
- O'Ring fixing: quick change of sockets
- Full speed and brightness control on all applications: Variable Speed Trigger + Touch Selector – 4 modes (3 speeds + Precision Mode)
- Work area lighting: Bright white LED with delay function for improved visibility and functionality
- Comfort and user control: Comfortable rubber handle
- Brushless motor: More power, efficiency and durability



Reference	DCF900
Motor	Brushless
MAX TORQUE OFF	1898 Nm
MAX TORQUE	1396 Nm
No load speed	0-2300 tr/min
IMPACTS PER MIN	0-1800 cps/min
LENGTH	223 mm
Weight	2.9 Kg
Gencod	5,03505E+12

**Standard equipment:**

No battery or charger, belt clip, TSTAK box.