


www.vishay.com

Vishay Semiconductors

Side View LED, Ø 5 mm Tinted Diffused Package



PRODUCT GROUP AND PACKAGE DATA

Product group: LED
Package: 5 mm side view
Product series: standard
Angle of half intensity: ± 80°

FEATURES

- · Even luminance of the emitting surface
- · Wide viewing angle
- Yellow and green color categorized
- For DC and pulse operation
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Pb-free



COMPLIANT
HALOGEN
FREE

GREEN (5-2008)

APPLICATIONS

• Indicating and illumination purposes

PARTS TABLE														
PART	COLOR		LUMINOUS INTENSITY (mcd)			WA	/ELEN	GTH	at I _F (mA)		ORWAI OLTAC (V)		at I _F	TECHNOLOGY
		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.	, ,	MIN.	TYP.	MAX.		
TLPR5600	Red	1	3.5	-	10	-	630	-	10	-	2	3	20	GaAsP on GaP
TLPR5600-AS12Z (1)	Red	1	3.5	-	10	-	630	-	10	-	2	3	20	GaAsP on GaP
TLPH5600	Red	0.63	3.5	-	10	612	-	625	10	-	2	3	20	GaAsP on GaP
TLPY5600	Yellow	0.63	2.25	-	10	581	-	594	10	-	2.4	3	20	GaAsP on GaP
TLPY5600-ASZ (1)	Yellow	0.63	2.25	-	10	581	-	594	10	-	2.4	3	20	GaAsP on GaP
TLPG5600	Green	0.63	2.25	-	10	562	-	575	10	-	2.4	3	20	GaP on GaP
TLPG5600-AS12Z (1)	Green	0.63	2.25	-	10	562	-	575	10	-	2.4	3	20	GaP on GaP
TLPP5600 (1)	Pure green	0.63	1.6	-	10	555	-	565	10	-	2.4	3	20	GaP on GaP
TLPP5600-AS12Z (1)	Pure green	0.63	1.6	-	10	555	-	565	10	-	2.4	3	20	GaP on GaP

Note

⁽¹⁾ Not for new designs

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified) TLPR5600, TLPH5600, TLPY5600, TLPP5600						
PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT	
Reverse voltage			V_{R}	6	V	
		TLPR5600	I _F	20	mA	
		TLPH5600	IF	30	mA	
DC forward current		TLPY5600	I _F	30	mA	
		TLPG5600	I _F	30	mA	
		TLPP5600	I _F	30	mA	
Surge forward current	t _p ≤ 10 μs		I _{FSM}	1	Α	
		TLPR5600	P_V	60	mW	
		TLPH5600	P_V	100	mW	
Power dissipation	T _{amb} ≤ 60 °C	TLPY5600	P_V	100	mW	
		TLPG5600	P _V	100	mW	
		TLPP5600	P _V	100	mW	
Junction temperature			Tj	100	°C	

Rev. 2.2, 29-Sep-2021 **1** Document Number: 83043



www.vishay.com

Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25 ^{\circ}C$, unless otherwise specified) TLPR5600, TLPH5600, TLPY5600, TLPG5600, TLPP5600							
PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT		
Operating temperature range			T _{amb}	-40 to +100	°C		
Storage temperature range			T _{stg}	-55 to +100	°C		
Soldering temperature	$t \le 5$ s, 2 mm from body		T _{sd}	260	°C		
		TLPR5600	R _{thJA}	500	K/W		
		TLPH5600	R _{thJA}	400	K/W		
Thermal resistance junction to ambient		TLPY5600	R _{thJA}	400	K/W		
		TLPG5600	R _{thJA}	400	K/W		
		TLPP5600	R _{thJA}	400	K/W		

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLPR5600, RED							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 10 mA	l _V	1	3.5	-	mcd	
Dominant wavelength	I _F = 10 mA	λ_{d}	-	630	-	nm	
Peak wavelength	I _F = 10 mA	λ_{p}	-	640	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 80	-	٥	
Forward voltage	I _F = 20 mA	V _F	-	2	3	V	
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	50	-	pF	

Note

 $^{^{(1)}}$ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLPH5600, RED							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 10 mA	I _V	0.63	3.5	-	mcd	
Dominant wavelength	I _F = 10 mA	λ_{d}	612	-	625	nm	
Peak wavelength	I _F = 10 mA	λ_{p}	-	635	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 80	-	٥	
Forward voltage	I _F = 20 mA	V _F	-	2	3	V	
Reverse voltage	$I_R = 10 \mu A$	V _R	6	15	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	50	-	pF	

Note

 $^{^{(1)}~}$ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLPY5600, YELLOW							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 10 mA	I _V	0.63	2.25	-	mcd	
Dominant wavelength	I _F = 10 mA	λ _d	581	-	594	nm	
Peak wavelength	I _F = 10 mA	λρ	-	585	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 80	-	0	
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V	
Reverse voltage	$I_R = 10 \mu A$	V _R	6	15	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	50	-	pF	

Note

 $^{^{(1)}~}$ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$



www.vishay.com

Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 ^{\circ}\text{C}$, unless otherwise specified) TLPG5600, GREEN							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 10 mA	I _V	0.63	2.25	-	mcd	
Dominant wavelength	I _F = 10 mA	λ_{d}	562	-	575	nm	
Peak wavelength	I _F = 10 mA	λρ	-	565	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 80	-	٥	
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V	
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	50	-	pF	

Note

⁽¹⁾ In one packing unit $I_{Vmin.}/I_{Vmax.} \le 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLPP5600, PURE GREEN, NOT FOR NEW DESIGNS							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 10 mA	I _V	0.63	1.6	-	mcd	
Dominant wavelength	I _F = 10 mA	λ_{d}	555	-	565	nm	
Peak wavelength	I _F = 10 mA	λ_{p}	-	555	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 80	-	0	
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V	
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	50	-	pF	

Note

⁽¹⁾ In one packing unit $I_{Vmin.}/I_{Vmax.} \le 0.5$

LUMINOUS	LUMINOUS INTENSITY CLASSIFICATION					
GROUP	LIGHT INTE	NSITY (mcd)				
STANDARD	MIN.	MAX.				
K	0.63	1.25				
L	1	2				
М	1.6	3.2				
N	2.5	5				
Р	4	8				
Q	6.3	12.5				
R	10	20				
S	16	32				
Т	25	50				
U	40	80				

Note

Luminous intensity is tested at a current pulse duration of 25 ms.
These type numbers represent the order groups which include
only a few brightness groups. Only one group will be shipped on
each bag (there will be no mixing of two groups on each bag).
In order to ensure availability, single brightness groups will not
be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one bag.

In order to ensure availability, single wavelength groups will not be orderable

COLOR	COLOR CLASSIFICATION							
		DON	I. WAVE	LENGTH	(nm)	•		
GROUP	YEL	LOW	GRI	EEN	PURE GREEN			
	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.		
0					555	559		
1	581	584			558	561		
2	583	586			560	563		
3	585	588	562	565	562	565		
4	587	590	564	567				
5	589	592	566	569				
6	591	594	568	571				
7			570	573				
8			572	575				

Note

• Wavelengths are tested at a current pulse duration of 25 ms

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 2 - Forward Current vs. Pulse Length




Fig. 3 - Relative Luminous Intensity vs. Angular Displacement




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 5 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 6 - Relative Luminous Intensity vs. Forward Current

www.vishay.com

Vishay Semiconductors




Fig. 7 - Relative Intensity vs. Wavelength




Fig. 8 - Forward Current vs. Forward Voltage




Fig. 9 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 10 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 11 - Relative Luminous Intensity vs. Forward Current




Fig. 12 - Relative Intensity vs. Wavelength

www.vishay.com

Vishay Semiconductors




Fig. 13 - Forward Current vs. Forward Voltage




Fig. 14 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 15 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 16 - Relative Luminous Intensity vs. Forward Current




Fig. 17 - Relative Intensity vs. Wavelength




Fig. 18 - Forward Current vs. Forward Voltage

www.vishay.com

Vishay Semiconductors




Fig. 19 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 20 - Specific Luminous Intensity vs. Forward Current




Fig. 21 - Relative Luminous Intensity vs. Forward Current




Fig. 22 - Relative Intensity vs. Wavelength




Fig. 23 - Forward Current vs. Forward Voltage




Fig. 24 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 25 - Specific Luminous Intensity vs. Forward Current




Fig. 27 - Relative Intensity vs. Wavelength





Fig. 26 - Relative Luminous Intensity vs. Forward Current

www.vishay.com

Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters



Drawing-No.: 6.544-5127.01-4

Issue: 1; 15.11.95

95 11321

AMMOPACK (Z)




Fig. 28 - Tape Direction

Note


• The new nomenclature for ammopack is ASZ only, without suffix for the LED orientation. The carton box has to be turned to the desired position: "+" for anode first, or "-" for cathode first. AS12Z and AS21Z are still valid for already existing types, BUT NOT FOR NEW DESIGN.



www.vishay.com

Vishay Semiconductors

TAPE DIMENSIONS in millimeters



OPTION	DIMENSION "H" ± 0.5 mm
AS	16

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.