

Ø 7.5 mm Film Dielectric Trimmers



FEATURES

- Housing diameter 7.5 mm
- For a basic grid of 2.54 mm (0.1") or 2.50 mm
- Top and bottom or top adjustment
- · Vertical and horizontal versions
- · Round head
- · Mounting: radial
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>






APPLICATIONS

- Antennas
- Impedance matching circuits
- Medical
- RF
- For consumer and industrial equipment


QUICK REFERENCE DATA				
Rated DC voltage		250 V _{DC}		
Test DC voltage for 1 min		500 V _{DC}		
Maximum contact resistance		10 mΩ		
Minimum insulation resistance		10 000 MΩ		
Category temperature range	PP	-40 °C to +70 °C		
Category temperature range	PE, PTFE, PET	-40 °C to +85 °C		
Climatic actagony (IEC 60069)	PP	40/070/21		
Climatic category (IEC 60068)	PE, PTFE, PET	40/085/21		
Minimum storage temperature		-55 ℃		
Related specification		IEC 60418-1 and 4		
Effective angle of rotation		180° (rotation in 180° only, see "Life of trimmer")		
Operating torque	C _{max.} < 33 pF	1 mNm to 15 mNm		
Operating torque	C _{max.} ≥ 33 pF	1 mNm to 25 mNm		
Maximum axial thrust		2 N		
Capacitance range (C _{min.} / C _{max.})		1.4 pF / 5.5 pF to 3 pF / 33 pF		
Life of trimmer		Maximum 10 cycles: rotation in 180° only (the electrical and mechanic performance is not guaranteed if rotated beyond 10 cycles)		
	Sampling and data evaluation for quality level i with "MIL-STD-105D" and "IEC 6041			
Quality level		< 0.15 % major defects < 0.65 % minor defects		
		Each capacitor is tested for minimum $C_{\text{max.}}$ and is also subjected to the full test voltage.		




DIMENSIONS in millimeters



Trimmers BFC2 808 series, vertical version




Trimmers BFC2 808 series, horizontal version



R = Rotor, S = Stator

The large hole is for bottom adjustment and the diameter is determined by user's requirements.




R = Rotor, S = Stator

Hole pattern

ADJUSTMENT

For top adjustment a screwdriver or trimming key can be used; for bottom adjustment a key is required as shown below.



Bottom adjustment key



ORDERING INFORMATION							
	CATALOG NUMBER BFC2 808						
C _{min.} / C _{max.}	VERTICAL	HORIZONTAL VERSION					
(pF)	ROUNE	ROUND HEAD					
	TOP AND BOTTOM ADJUSTMENT	TOP ADJUSTMENT ONLY	TOP AND BOTTOM ADJUSTMENT				
1.4 / 5.5	11558	00004	51558				
2/9	00018	-	-				
2/10	11109	00005	51109				
2/10	-	11004	-				
2 / 15	11159	-	-				
2 / 18	00016	-	-				
2.5 / 20	-	11006	-				
2.5 / 22	11229	00006	51229				
3 / 33	11339	-	-				

MOUNTING

The trimmer can be mounted on printed-circuit boards with a grid of 2.50 mm or 2.54 mm and a minimum hole diameter of 1.25 mm.

PACKAGING

Bulk packaged in cardboard boxes lined with expanded plastic. For smallest packaging quantity (SPQ) see "Electrical Data" table.

ELECTRICAL DATA											
GUARANTEED MAX. C _{min.} / MIN. C _{max.} AT 200 kHz (pF) SPINDLE	COINDLE	SHAPE OF HEAD	ADJ. MODE	DIEL.	tan δ AT C _{max.} x 10 ⁻⁴		TEMP. COEFF.	MIN. f _{res}	COL. OF	SPQ	CATALOG NUMBER
	SPINDLE				1 MHz	100 MHz	(10 ⁻⁶ /K)	AT C _{max.} (MHz)	BASE	SPU	BFC2
	Vertical	Round	Top + bottom	PE	≤ 10	≤ 25	-250 ± 350	850	Grey	1400	808 11558
1.4 / 5.5			Тор							1400	808 00004
	Horizontal	Round	Top + bottom							1200	808 51558
2/9	Vertical	Round	Top + bottom	PTFE	≤ 10	≤ 15	-150 ± 800	400	Yellow	1400	808 00018
	Vertical	Round	Top + bottom	PP	≤ 10	≤ 25	-250 ± 800	480	Yellow	1400	808 11109
2/10			Тор							1400	808 00005
	Horizontal	Round	Top + bottom							1200	808 51109
2 / 15	Vertical	Round	Top + bottom	PP	≤ 10	≤ 25	-250 ± 600	450	Blue	1400	808 11159
2 / 18	Vertical	Round	Top + bottom	PTFE	≤ 10	≤ 15	-250 ± 350	350	Green	1400	808 00016
2.5 / 20	Vertical	Round	Тор	PET	≤ 160	-	0 ± 1100	250	Green	1000	808 11006
	Vertical	ertical Round	Top + bottom	PP	≤ 10	≤ 25	-200 ± 500	350	Green	1400	808 11229
2.5 / 22			Тор							1400	808 00006
	Horizontal	Round	Top + bottom							1200	808 51229
3 / 33	Vertical	Round	Top + bottom	PP	≤ 10	-	-250 ± 350	300	Brown	1400	808 11339



SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile, we refer to the application note "Soldering Guidelines for Film Capacitors": www.vishay.com/doc?28171

IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS		
4.2		Method of mounting	Method A			
14		Capacitance drift	After TC measurement	$\begin{array}{l} \Delta C/C : \leq 1 \text{ \% for } C_{max.} < 40 \text{ pF}; \\ \Delta C/C : \leq 2.5 \text{ \% for } C_{max.} \geq 40 \text{ pF} \end{array}$		
19		Thrust	Axial thrust of 2 N	ΔC/C: ≤ 0.3 %		
21		Robustness of terminations:				
21.1	Ua	Tensile	1 N	No damage		
21.2	Ub	Bending	1 cycle	No damage		
22	Na	Rapid change of temperature	1 cycle; 0.5 h at lower and 0.5 h at upper category temperature	ΔC/C: ≤ 2 %		
23	Т	Soldering:				
	Та	Solderability	Solder bath immersion 3 mm; 235 °C; 2 s	Good wetting, no mechanical damage		
	Tb	Resistance to heat	Solder bath: 260 °C; 10 s	No mechanical damage		
24	Eb	Impact bump	4000 ± 10 bumps; 40 g; 6 ms	ΔC/C: ≤ 0.6 %; no mechanical damage		
25	Fc	Vibration	Frequency 10 Hz to 55 Hz; amplitude 0.35 mm; 1.5 h	ΔC/C: ≤ 0.6 %; no mechanical damage		
26		Climatic sequence:		ΔC/C: ≤ 4 %		
26.1	В	Dry heat	16 h at upper category temperature	$\begin{array}{l} tan \ \delta : \leq 10 \ x \ 10^{-4} \ for \ C_{max.} < 27 \ pF; \\ tan \ \delta : \leq 70 \ x \ 10^{-4} \ for \ C_{max.} \geq 27 \ pF; \\ tan \ \delta : \leq 80 \ x \ 10^{-4} \ for \ C_{max.} \geq 40 \ pF \\ \\ R_{ins.} : \geq 10 \ 000 \ M\Omega; \\ rotor \ contact \ R : \leq 10 \ m\Omega \end{array}$		
26.2	D	Damp heat accelerated, first cycle	1 cycle; 24 h; +40 °C; 95 % to 100 % RH	Voltage proof: 500 V for 1 min		
26.3	Aa	Cold	16 h; -40 °C	Visual examination: no mechanical damage		
26.5		Damp heat accelerated, remaining cycles	1 cycle; 24 h; +40 °C; Operating torque: 1 mNm to 15 mNm for $C_{max.}$ 1 mNm to 25 mNm for $C_{max.}$			



www.vishay.com

Vishay BCcomponents

TEST PF	TEST PROCEDURES AND REQUIREMENTS							
IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS				
27	Ca	Damp heat steady state	21 days; +40 °C; 90 % to 95 % RH	Δ C/C: \leq 5 % tan δ : \leq 30 x 10 ⁻⁴ for $C_{max.}$ $<$ 27 pF; tan δ : \leq 70 x 10 ⁻⁴ for $C_{max.}$ \geq 27 pF; tan δ : \leq 80 x 10 ⁻⁴ for $C_{max.}$ \geq 40 pF $R_{ins.}$: \geq 10 000 MΩ; rotor contact R: \leq 10 mΩ Voltage proof: 500 V for 1 min Visual examination: no mechanical damage Operating torque: 1 mNm to 15 mNm for $C_{max.}$ $<$ 33 pF; 1 mNm to 25 mNm for $C_{max.}$ \geq 33 pF				
29		Mechanical endurance	10 cycles Maximum 10 cycles: rotation in 180° only (the electrical and mechanical performance is not guaranteed if rotated beyond 10 cycles)	Δ C/C: \leq 1.5 % Δ C/C after axial thrust: \leq 0.3 %; rotor contact R: \leq 10 m Ω Voltage proof: 500 V for 1 min Visual examination: no mechanical damage Operating torque: 1 mNm to 15 mNm for C _{max.} $<$ 33 pF; 1 mNm to 25 mNm for C _{max.} \geq 33 pF				

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.