


QYX Foil Type Polyester Film Capacitor (Standard type)


- Inductive construction, using a dielectric of polyester film together with aluminum foil.
- Coated with epoxy resin for superior heat resistance, humidity resistance and solvent resistance.
- Suited for use in commercial and industrial applications.
- Available for automatic insertion systems.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).




Specifications

Item	Performance Characteristics
Category Temperature Range	-40 to +85°C
Rated Voltage	50, 100VDC
Rated Capacitance Range	0.001 to 0.47μF
Capacitance Tolerance	±5% (J), ±10% (K)
Dielectric Loss Tangent	0.8% or less (at 1kHz 20°C)
Insulation Resistance	30000 MΩ or more
Withstand Voltage	Between Terminals : Rated Voltage × 250%, 1 to 5 secs. Between Terminals and Coverage : Rated Voltage × 200%, 1 to 5 secs.
Encapsulation	Epoxy resin

Drawing



Type numbering system (Example : 50V 0.047μF)



Dimensions

Unit : mm

Cap. (μF)	V (Code)	Code	Size	50VDC (1H)					100VDC (2A)						
				T	W	H	d	P	F	T	W	H	d	P	F
0.001	102			2.5	5.0	8.5	0.5	3.5 ± 0.75	5.0	2.8	5.5	11.5	0.5	3.5 ^{+1.0} / _{-1.2}	5.0
0.0015	152			2.5	5.0	8.5	0.5	3.5 ± 0.75	5.0	2.8	5.5	12.0	0.5	3.5 ^{+1.0} / _{-1.2}	5.0
0.0022	222			3.0	5.5	8.5	0.5	3.5 ± 0.75	5.0	2.8	5.5	12.0	0.5	3.5 ^{+1.0} / _{-1.2}	5.0
0.0033	332			3.0	5.5	8.5	0.5	3.5 ± 0.75	5.0	2.8	5.5	12.0	0.5	3.5 ^{+1.0} / _{-1.2}	5.0
0.0047	472			3.0	6.0	8.5	0.5	3.5 ± 0.75	5.0	3.0	6.0	12.0	0.5	3.5 ^{+1.0} / _{-1.2}	5.0
0.0068	682			3.5	6.0	8.5	0.5	3.5 ± 0.75	5.0	3.0	6.0	12.0	0.5	5.0 ± 1.0	5.0
0.01	103			3.5	6.0	8.5	0.5	3.5 ± 0.75	5.0	3.0	6.5	12.0	0.5	5.0 ± 1.0	5.0
0.015	153			3.5	6.0	10.0	0.5	3.5 ± 0.75	5.0	3.0	6.5	13.0	0.5	5.0 ± 1.0	5.0
0.022	223			3.5	6.5	10.5	0.5	3.5 ± 0.75	5.0	3.5	7.0	13.0	0.5	5.0 ± 1.0	5.0
0.033	333			4.0	7.0	10.5	0.5	3.5 ± 0.75	5.0	3.5	7.5	13.0	0.5	5.0 ± 1.0	5.0
0.047	473			4.5	7.5	11.0	0.5	5.0 ± 1.0	5.0	4.5	8.5	14.0	0.5	5.0 ± 1.0	5.0
0.068	683			5.0	8.0	11.0	0.5	5.0 ± 1.0	5.0	4.5	9.5	14.0	0.5	7.5 ^{+1.0} / _{-1.2}	7.5
0.1	104			5.5	9.0	12.0	0.5	5.0 ± 1.0	5.0	5.5	11.0	14.0	0.5	7.5 ^{+1.0} / _{-1.2}	7.5
0.15	154			6.5	10.0	13.5	0.5	5.0 ± 1.0	5.0	6.0	12.5	15.5	0.5	10.0 ^{+1.0} / _{-1.2}	7.5
0.22	224			7.0	11.0	13.5	0.5	7.5 ^{+1.0} / _{-1.2}	7.5	7.0	14.0	15.5	0.5	10.0 ^{+1.0} / _{-1.2}	7.5
0.33	334			8.0	12.5	16.0	0.6	7.5 ^{+1.0} / _{-1.2}	7.5	8.0	14.5	18.5	0.6	10.0 ^{+1.0} / _{-1.2}	7.5
0.47	474			9.5	14.0	16.5	0.6	7.5 ^{+1.0} / _{-1.2}	7.5	9.5	16.5	18.5	0.6	10.0 ^{+1.0} / _{-1.2}	7.5

F : lead pitch for cut / formed lead wires.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[QYX1H683KTP3TA](#) [QYX2A102KTP1FD](#) [QYX2A153KTP](#) [QYX2A274JTP](#) [QYX2A333KTP](#) [QYX2A332KTP](#)
[QYX2A104KTP](#) [QYX1H223KTP](#) [QYX1H224KTP](#) [QYX1H223JTP](#) [QYX1H103KTP](#) [QYX2A102JTP](#)
[QYX1H333JTP3TA](#) [QYX1H103JTP3TA](#) [QYX1H102JTP3TA](#) [QYX1H473KTP](#) [QYX1H104JTP](#) [QYX2A103KTP](#)
[QYX2A103KTP1FD](#) [QYX2A102KTP](#) [QYX2A152KTP](#) [QYX2A222KTP](#) [QYX2A223KTP](#) [QYX2A472KTP](#)
[QYX2A473KTP](#) [QYX1H683KTP](#) [QYX1H102KTP](#) [QYX1H122KTP](#) [QYX1H152KTP](#) [QYX1H222KTP](#) [QYX1H332KTP](#)
[QYX1H392KTP](#) [QYX1H472KTP](#) [QYX1H682KTP](#) [QYX1H822KTP](#) [QYX1H123KTP](#) [QYX1H153KTP](#) [QYX1H183KTP](#)
[QYX1H333KTP](#) [QYX1H563KTP](#) [QYX1H104KTP](#) [QYX1H124KTP](#) [QYX1H154KTP](#) [QYX1H184KTP](#) [QYX1H274KTP](#)
[QYX1H334KTP](#) [QYX1H394KTP](#) [QYX1H474KTP](#) [QYX2A182KTP](#) [QYX2A272KTP](#) [QYX2A392KTP](#) [QYX2A562KTP](#)
[QYX2A682KTP](#) [QYX2A822KTP](#) [QYX2A183KTP](#) [QYX2A273KTP](#) [QYX2A393KTP](#) [QYX2A683KTP](#) [QYX2A124KTP](#)
[QYX2A154KTP](#) [QYX2A184KTP](#) [QYX2A224KTP](#) [QYX2A274KTP](#) [QYX2A334KTP](#) [QYX2A474KTP](#) [QYX2A472JTP](#)
[QYX1H103JTP1FD](#) [QYX1H473JTP](#) [QYX1H103JTP](#) [QYX1H222JTP](#) [QYX1H102JTP](#) [QYX1H152JTP](#) [QYX1H153JTP](#)
[QYX1H224JTP](#) [QYX1H332JTP](#) [QYX1H472JTP](#) [QYX1H474JTP](#) [QYX1H682JTP](#) [QYX2A103JTP](#) [QYX2A152JTP](#)
[QYX2A153JTP](#) [QYX2A222JTP](#) [QYX2A224JTP](#) [QYX2A332JTP](#) [QYX2A473JTP](#) [QYX2A682JTP](#) [QYX2A683JTP](#)
[QYX1H102JTP1FD](#) [QYX1H223KTP1FD](#) [QYX1H222JTP1FD](#) [QYX1H102KTP1FD](#) [QYX2A104JTP](#) [QYX1H334JTP](#)
[QYX2A474JTP](#) [QYX1H154JTP](#) [QYX1H683JTP](#) [QYX2A333JTP](#) [QYX2A223JTP](#) [QYX2A334JTP](#) [QYX1H333JTP](#)