


Ultra low drop voltage regulators compatible with low ESR output capacitors

Datasheet - production data



Features

- Stable with low ESR ceramic capacitors
- Ultra low dropout voltage (0.12 V typ. at 50 mA load, 7 mV typ. at 1 mA load)
- Very low quiescent current (80 μA typ. at no load in on mode; max 1 μA in off mode)
- Guaranteed output current up to 50 mA
- Logic-controlled electronic shutdown
- Output voltage of 1.8; 3.0; 3.3; 5.0 V
- · Internal current and thermal limit
- ± 0.5% Tolerance output voltage available (A version)
- Output low noise voltage 160 μVRMS
- Temperature range: -40 to 125 °C
- Smallest package SOT23-5L
- Fast dynamic response to line and load changes

Description

The low drop voltage and the ultra low quiescent current make them suitable for low noise, low power applications and in battery powered systems. The quiescent current in sleep mode is less than 1 µA when the INHIBIT pin is pulled low. A shutdown logic control function is available on pin n° 3 (TTL compatible). This means that when the device is used as local regulator, it is possible to put a part of the board in standby, decreasing the total power consumption. The LD2980 is designed to work with low ESR ceramic capacitors. Typical applications are cellular phone, laptop computer, personal digital assistant (PDA), personal stereo, camcorder and camera.

Table 1. Device summary

Part numbers				
AB version	C version	Output voltage		
	LD2980CM18TR	1.8 V		
LD2980ABM30TR		3.0 V		
LD2980ABM33TR	LD2980CM33TR	3.3 V		
LD2980ABM50TR	LD2980CM50TR	5.0 V		

November 2019 DocID6280 Rev 21 1/22

Contents LD2980

Contents

1	Diagram 3
2	Pin configuration
3	Maximum ratings
4	Typical application6
5	Electrical characteristics
6	Typical performance characteristics
7	Application notes15
	7.1 External capacitors
	7.2 Input capacitor
	7.3 Output capacitor
	7.4 Important
	7.5 Inhibit input operation
	7.6 Reverse current
8	Package mechanical data
9	Packaging mechanical data19
10	Revision history



LD2980 Diagram

1 Diagram




Figure 1. Schematic diagram

Pin configuration LD2980

2 Pin configuration

Figure 2. Pin connections (top view)




Table 2. Pin description

Pin n°	Symbol	Name and function
1	V_{IN}	Input port
2	GND	Ground pin
3	INHIBIT	Control switch ON/OFF. Inhibit is not internally pulled-up; it cannot be left floating. Disable the device when connected to GND or to a positive voltage less than 0.18 V
4	NC	Not connected
5	V _{OUT}	Output port

Table 3. Thermal data

Symbol	Parameter Value		Unit
R_{thJC}	Thermal resistance junction-case	81	°C/W
R_{thJA}	Thermal resistance junction-ambient	255	°C/W

4/22 DocID6280 Rev 21

LD2980 Maximum ratings

3 Maximum ratings

Table 4. Absolute maximum ratings


Symbol	Parameter	Value	Unit
V _I	DC input voltage	-0.3 to 16	V
V _{INH}	INHIBIT input voltage	-0.3 to 16	V
Io	Output current	Internally limited	
P _D	Power dissipation	Internally limited	
T _{STG}	Storage temperature range	-55 to 150	°C
T _{OP}	Operating junction temperature range	-40 to 125	°C

Note: Absolute maximum ratings are those values beyond which damage to the device may occur. Functional operation under these condition is not implied.

Typical application LD2980

4 Typical application

Figure 3. Application circuit



Note:

Inhibit pin is not internally pulled-up then it must not be left floating. Disable the device when connected to GND or to a positive voltage less than 0.18 V.

5 Electrical characteristics

(T $_J$ = 25 °C, V $_I$ = V $_{O(NOM)}$ +1 V, C $_I$ = 1 $\mu F,$ C $_O$ = 2.2 $\mu F,$ I $_O$ = 1 mA, V $_{INH}$ = 2 V, unless otherwise specified).

Table 5. Electrical characteristics for LD2980ABM

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
V_{OP}	Operating input voltage		2.5		16	V
	Output voltage	I _O = 1 mA	2.985	3	3.015	V
V_{O}		I _O = 1 to 50 mA	2.978		3.023	
		I _O = 1 to 50 mA, T _J = -40 to 125°C	2.925		3.075	
		I _O = 1 mA	3.284	3.3	3.317	
V_{O}	Output voltage	I _O = 1 to 50 mA	3.275		3.325	V
		I _O = 1 to 50 mA, T _J = -40 to 125°C	3.217		3.383	
		I _O = 1 mA	4.975	5	5.025	
V_{O}	Output voltage	I _O = 1 to 50 mA	4.963		5.038	V
		I _O = 1 to 50 mA, T _J = -40 to 125°C	4.875		5.125	
41/	Line regulation	V _{O(NOM)} + 1 < V _{IN} < 16 V, I _O = 1 mA		0.003	0.014	0/ /\/
ΔV_{O}	Line regulation	T _J = -40 to 125°C			0.032	%/V
	Quiescent current ON MODE	I _O = 0		80	100	
		I _O = 0, T _J = -40 to 125°C			150	
		I _O = 1 mA		100	150	
		I _O = 1 mA, T _J = -40 to 125°C			200	
		I _O = 10 mA		175	250	^
ΙQ		I _O = 10 mA, T _J = -40 to 125°C			450	μΑ
		I _O = 50 mA		500	700	
		I _O = 50 mA, T _J = -40 to 125°C			1200	
	OFF MODE	V _{INH} < 0.18 V		0		
	OFF MODE	V _{INH} < 0.18 V, T _J = -40 to 125°C			1	
		I _O = 0		1	3	
		I _O = 0, T _J = -40 to 125°C			5	
		I _O = 1mA		7	10	
V	Dropout voltage ⁽¹⁾	I _O = 1mA, T _J = -40 to 125°C			15	mV
V_{DROP}	Diopout voitage	I _O = 10mA		40	60	IIIV
		I _O = 10mA, T _J = -40 to 125°C			90	
		I _O = 50mA		120	150	
		I _O = 50mA, T _J = -40 to 125°C			225	



Electrical characteristics LD2980

Table 5. Electrical characteristics for LD2980ABM (continued)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
I _{SC}	Short circuit current	R _L = 0		150		mA
SVR	Supply voltage rejection	$C_{O} = 10 \mu F, f = 1 kHz$		63		dB
V _{INH}	Inhibit input logic low	LOW = Output OFF, T _J = -40 to 125°C		0.8	0.18	V
V _{INL}	Inhibit input logic high	HIGH = Output ON, T _J = -40 to 125°C	1.6	1.3		V
,	I _{INH} Inhibit input current	V _{INH} = 0V, T _J = -40 to 125°C		0	-1	
INH		V _{INH} = 5V, T _J = -40 to 125°C		5	15	μA
e _N	Output noise voltage	$B_W = 300 \text{ Hz to } 50 \text{ kHz}, C_O = 10 \mu\text{F}$		160		μV_{RMS}
T _{SHDN}	Thermal shutdown			170		°C

^{1.} For V_0 < 2.5 V dropout voltage can be calculated according to the minimum input voltage in full temperature range.



(T $_J$ = 25 °C, V $_I$ = V $_{O(NOM)}$ +1 V, C $_I$ = 1 $\mu F,$ C $_O$ = 2.2 $\mu F,$ I $_O$ = 1 mA, V $_{INH}$ = 2 V, unless otherwise specified).

Table 6. Electrical characteristics for LD2980CM

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
V_{OP}	Operating input voltage		2.5		16	V
		I _O = 1 mA	1.782	1.8	1.818	
V_{O}	Output voltage	I _O = 1 to 50 mA	1.773		1.827	V
		I _O = 1 to 50 mA, T _J = -40 to 125°C	1.737		1.863	
		I _O = 1 mA	3.267	3.3	3.333	
V_{O}	Output voltage	I _O = 1 to 50 mA	3.251		3.35	V
		I _O = 1 to 50 mA, T _J = -40 to 125°C	3.184		3.415	
		I _O = 1 mA	4.95	5	5.05	
V_{O}	Output voltage	I _O = 1 to 50 mA	4.925		5.075	V
		I _O = 1 to 50 mA, T _J = -40 to 125°C	4.825		5.175	
43.7	line mendetien	V _{O(NOM)} + 1 < V _{IN} < 16 V, I _O = 1 mA		0.003	0.014	0/ /\
ΔV_{O}	Line regulation	T _J = -40 to 125°C			0.032	%/V
	Quiescent current ON MODE	I _O = 0		80	100	
		I _O = 0, T _J = -40 to 125°C			150	
		I _O = 1 mA		100	150	
		I _O = 1 mA, T _J = -40 to 125°C			200	
		I _O = 10 mA		175	250	
IQ		I_{O} = 10 mA, T_{J} = -40 to 125°C			450	μA
		I _O = 50 mA		500	700	
		I_{O} = 50 mA, T_{J} = -40 to 125°C			1200	
	OFF MODE	V _{INH} < 0.18 V		0		
	OFF MODE	V _{INH} < 0.18 V, T _J = -40 to 125°C			1	
		I _O = 0		1	3	
		I _O = 0, T _J = -40 to 125°C			5	
		I _O = 1mA		7	10	
	D () (1)	I _O = 1mA, T _J = -40 to 125°C			15	mV
V _{DROP}	Dropout voltage ⁽¹⁾	I _O = 10mA		40	60	
		I _O = 10mA, T _J = -40 to 125°C			90	
		I _O = 50mA		120	150	
		I _O = 50mA, T _J = -40 to 125°C			225	
I _{SC}	Short circuit current	R _L = 0		150		mA
SVR	Supply voltage rejection	C _O = 10µF, f = 1kHz		63		dB



Electrical characteristics LD2980

Table 6. Electrical characteristics for LD2980CM (continued)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
V _{INH}	Inhibit input logic low	LOW = Output OFF, T _J = -40 to 125°C		0.8	0.18	V
V _{INL}	Inhibit input logic high	HIGH = Output ON, T _J = -40 to 125°C	1.6	1.3		V
1 15	Inhibit input ourrent	V _{INH} = 0V, T _J = -40 to 125°C		0	-1	μF
INH	Inhibit input current	V _{INH} = 5V, T _J = -40 to 125°C		5	15	μΓ
e _N	Output noise voltage	$B_W = 300 \text{ Hz to } 50 \text{ kHz}, C_O = 10 \mu\text{F}$		160		μV_{RMS}
T _{SHDN}	Thermal shutdown			170		°C

^{1.} For V_0 < 2.5 V dropout voltage can be calculated according to the minimum input voltage in full temperature range.



6 Typical performance characteristics

(T_J = 25 °C, V_I = V_{O(NOM)} +1 V, C_I = 1 μ F, C_O = 2.2 μ F, V_{INH} = 2 V, unless otherwise specified)

Figure 4. Output voltage vs temperature

Figure 5. Output voltage vs temperature




Figure 6. Line regulation vs temperature

Figure 7. Load regulation vs temperature





Figure 8. Dropout voltage vs temperature

Figure 9. Quiescent current vs temperature







Figure 10. Quiescent current vs output current

Figure 11. Off mode quiescent current vs temperature








Figure 12. Quiescent current vs input voltage

Figure 13. Dropout voltage vs output current






5/

12/22

Figure 14. Inhibit input current vs temperature

Figure 15. Inhibit voltage vs temperature







Figure 16. Supply voltage rejection vs frequency

Figure 17. Noise voltage vs frequency








Figure 18. Best case: highest output version

Figure 19. Worst case: lowest output version







5/

Figure 20. Load transient response

Figure 21. Line transient response





57

LD2980 Application notes

7 Application notes

7.1 External capacitors

Like any low-dropout regulator, the LD2980 requires external capacitors for regulator stability. This capacitor must be selected to meet the requirements of minimum capacitance and equivalent series resistance (please refer to *Figure 18* and *Figure 19*). We suggest to solder input and output capacitors as close as possible to the relative pins.

7.2 Input capacitor

An input capacitor whose value is 1 μ F is required with the LD2980 (amount of capacitance can be increased without limit). This capacitor must be located a distance of not more than 0.5" from the input pin of the device and returned to a clean analog ground. Any good quality ceramic, tantalum or film capacitors can be used for this capacitor.

7.3 Output capacitor

The LD2980 is designed specifically to work with ceramic output capacitors. It may also be possible to use Tantalum capacitors, but these are not as attractive for reasons of size and cost. By the way, the output capacitor must meet both the requirement for minimum amount of capacitance and ESR (equivalent series resistance) value. The *Figure 18* and *Figure 19* show the allowable ESR range as a function of the output capacitance. These curves represent the stability region over the full temperature and I_O range. Due to the different loop gain, the stability improves for higher output versions and so the suggested minimum output capacitor value, if low ESR ceramic type is used, is 1 μ F for output voltages equal or major than 3.8 V, 2.2 μ F for output voltages from 2.85 to 3.3 V, and 3.3 μ F for the other versions. However, if an output capacitor lower than the suggested one is used, it's possible to make stable the regulator adding a resistor in series to the capacitor (see *Figure 18* and *Figure 19* to choose the right value according to the used version and keeping in account that the ESR of ceramic capacitors has been measured @ 100 kHz).

7.4 Important

The output capacitor must maintain its ESR in the stable region over the full operating temperature to assure stability. Also, capacitor tolerance and variation with temperature must be considered to assure the minimum amount of capacitance is provided at all times. This capacitor should be located not more than 0.5" from the output pin of the device and returned to a clean analog ground.

7.5 Inhibit input operation

The inhibit pin can be used to turn OFF the regulator when pulled low, so drastically reducing the current consumption down to less than 1 μ A. When the inhibit feature is not used, this pin must be tied to V_I to keep the regulator output ON at all times. To assure proper operation, the signal source used to drive the inhibit pin must be able to swing above



Application notes LD2980

and below the specified thresholds listed in the electrical characteristics section under V_{IL} . Any slew rate can be used to drive the inhibit.

7.6 Reverse current

The power transistor used in the LD2980 has not an inherent diode connected between the regulator input and output. If the output is forced above the input, no current will flow from the output to the input across the series pass transistor. When a V_{REV} voltage is applied on the output, the reverse current measured, according to the test circuit in *Figure 22*, flows to the GND across the two feedback resistors. This current typical value is 160 μ A. R_1 and R_2 resistors are implanted type; typical values are, respectively, 42.6 $k\Omega$ and 51.150 $k\Omega$.




Figure 22. Reverse current test circuit

8 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.


Table 7. SOT23-5L mechanical data

Dim.		mm	
	Min.	Тур.	Max.
Α	0.90		1.45
A1	0		0.15
A2	0.90		1.30
b	0.30		0.50
С	2.09		0.20
D		2.95	
E		1.60	
е		0.95	
Н		2.80	
L	0.30		0.60
θ	0		8

7049676_k

Figure 23. SOT23-5L mechanical drawing





577

9 Packaging mechanical data





Figure 25. SOT23-5L reel mechanical drawing

577

User Direction of Feed

Figure 26. SOT23-5L oriented tape outline






Table 8. SOT23-5L reel mechanical data

Symbol	Dimensions (mm)				
	Min.	Тур.	Max.		
А	-	-	180		
С	12.8	13.0	13.2		
D	20.2	-	-		
N	60	-	-		
Т	-	-	14.4		

577

20/22

LD2980 Revision history

10 Revision history

Table 9. Document revision history

Date	Revision	Changes
03-Jul-2006	13	Order codes updated and new template.
13-Nov-2006	14	Add part number LD2980ABU18TR.
06-Sep-2007	15	Add Table 1 on page 1.
14-Feb-2008	16	Modified: Table 1 on page 1.
11-Jul-2008	17	Modified: Table 1 on page 1.
06-Nov-2013	18	Document name changed from LD2980ABxx and LD2980Cxx to LD2980. Updated Table 1: Device summary, Table 5: Electrical characteristics for LD2980ABM, Table 6: Electrical characteristics for LD2980CM and Section 8: Package information. Added Section 9: Packaging information. Minor text changes in title, in features and description in cover page.
30-Aug-2017	19	Removed 5.0 V versions of device (updated Features, Table 1: Device summary, Table 5: Electrical characteristics for LD2980ABM, and Table 6: Electrical characteristics for LD2980C. Minor textual updates.
07-Dec-2017	20	Updated Table 1: Device summary on the cover page.
11-Nov-2019 21 Updated Figure 25: SOT23-5L reel mechanical drawing added Figure 26: SOT23-5L oriented tape outline.		

IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics - All rights reserved

57

22/22