



IHLP® Commercial Inductors, Low DCR Series



DESIGN SUPPORT TOOLS

click logo to get started

3D
Models
AvailableDesign Tools
Available

STANDARD ELECTRICAL SPECIFICATIONS

L ₀ INDUCTANCE ± 20 % AT 100 kHz, 0.25 V, 0 A (μH)	DCR TYP. 25 °C (mΩ)	DCR MAX. 25 °C (mΩ)	HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾	SATURATION CURRENT DC TYP. (A) ⁽²⁾
0.19	0.70	0.80	40	46
0.22	0.85	0.95	33	44
0.24	0.85	0.95	33	44
0.36	1.05	1.15	32	30
0.47	1.53	1.68	30	30
0.56	1.61	1.80	32	22
0.78	1.80	1.90	27	22
1.0	2.30	2.50	25	20
1.8	4.50	5.00	17	16
2.0	5.20	5.80	16	14
4.7	12.9	14.2	9.5	7.6
6.8	17.5	19.3	9.0	7.5
10.0	27.8	30.5	7.5	7.1
15.0	40.9	45.0	6.25	6.0
22.0	60.4	66.0	5.0	4.5
33.0	87.5	94.5	4.4	4.0
47.0	132.0	145.0	3.3	3.0
100.0	249.0	270.0	2.5	2.25

Notes

- All test data is referenced to 25 °C ambient
 - Operating temperature range -55 °C to +125 °C
 - The part temperature (ambient + temp. rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
 - Rated operating voltage (across inductor) = 50 V
- (1) DC current (A) that will cause an approximate ΔT of 40 °C
(2) DC current (A) that will cause L₀ to drop approximately 20 %

FEATURES


- Shielded construction
- Frequency range up to 1.0 MHz
- Lowest DCR/μH, in this package size
- Handles high transient current spikes without saturation
- Ultra low buzz noise, due to composite construction
- Excellent temperature stability for inductance and saturation
- IHLP design. PATENT(S): www.vishay.com/patents
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- PDA/notebook/desktop/server applications
- High current POL converters
- Low profile, high current power supplies
- Battery powered devices
- DC/DC converters in distributed power systems
- DC/DC converter for Field Programmable Gate Array (FPGA)

DIMENSIONS in inches [millimeters]



DESCRIPTION

IHLP-4040DZ-11	2.0 μH	± 20 %	ER	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER









I	H	L	P	4	0	4	0	D	Z	E	R	2	R	0	M	1	1
PRODUCT FAMILY				SIZE						PACKAGE CODE		INDUCTANCE VALUE			TOL.	SERIES	

PATENT(S): www.vishay.com/patents

This Vishay product is protected by one or more United States and international patents.











PERFORMANCE GRAPHS







PERFORMANCE GRAPHS





PERFORMANCE GRAPHS





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

IHLP4040DZER1R0M11	IHLP4040DZER1R8M11	IHLP4040DZER220M11	IHLP4040DZER2R0M11
IHLP4040DZERR19M11	IHLP4040DZERR36M11	IHLP4040DZERR47M11	IHLP4040DZERR56M11
IHLP4040DZERR78M11	IHLP4040DZER100M11	IHLP4040DZER470M11	IHLP4040DZER4R7M11
IHLP4040DZER6R8M11	IHLP4040DZERR56M05	IHLP4040DZER150M11	IHLP4040DZER101M11
IHLP4040DZERR24M11	IHLP4040DZER330M11	IHLP2525CZET1R0M11	IHLP2525CZET100M11
IHLP4040DZET220M11	IHLP4040DZET330M11	IHLP4040DZET100M11	IHLP4040DZET1R0M11
IHLP4040DZET4R7M11	IHLP2020BZET2R2M11	IHLP2020BZET1R0M11	IHLP1616BZETR47M11
IHLP1616BZET2R2M11	IHLP1616BZET1R0M11	IHLP1616BZET4R7M11	IHLP1616BZET1R5M11
IHLP2020CZET3R3M11	IHLP2020CZET2R2M11	IHLP2020CZET1R0M11	IHLP2020CZET4R7M11
IHLP2525CZETR82M01	IHLP2525CZET3R3M01	IHLP2525CZET6R8M01	IHLP2525CZETR33M01
IHLP2525CZETR47M01	IHLP2525CZETR22N01	IHLP2525CZET2R2M01	IHLP2525CZET1R0M01
IHLP2525CZET8R2M01	IHLP2525CZET4R7M01	IHLP2525CZETR68M01	IHLP2525CZET1R5M01
IHLP2525CZET100M01	IHLP2020BZETR47M01	IHLP2020CZET2R2M01	IHLP2020BZET3R3M01
IHLP2020BZET2R2M01	IHLP2020BZET100M01	IHLP2020BZET1R0M01	IHLP2020BZET4R7M01
IHLP2020CZET3R3M01	IHLP2020CZET150M01	IHLP2020CZET1R0M01	IHLP1616BZET2R2M01
IHLP4040DZET1R0M01	IHLP4040DZET100M01	IHLP1616BZET1R0M01	IHLP4040DZET2R2M01
IHLP1616BZETR47M01	IHLP1616BZETR22N01	IHLP4040DZET4R7M01	IHLP4040DZET3R3M01
IHLP2525CZET2R2M11	IHLP2020CZET150M11	IHLP4040DZET470M11	IHLP4040DZETR36M01
IHLP2525CZET220M11	IWTX5050CZEB6R3KF1	IWTX5555DEEB100KF1	IWTX5050DEEB100KF1
IWAS4832AEEB120KF1	IWTX55R0DZEB8R9KF1	IWAS3010AZEB130KF1	IWTX9955DEEB110KF3
IWTX5050FEEB100KF1	IWTXA653FZEB120KF3	IWTX50R0DZEB6R3KF1	IWTX50R0CZEB6R3KF1
IWTX5050DZEB6R3KF1	IHLP4040DZETR19N01	IHLP4040DZET1R5M01	IHLP4040DZET5R6M01
IHLP2525CZET3R3M11	IHLP2525CZET6R8M11	IHLP2525CZET4R7M11	IHLP2525CZET8R2M11
IHLP1616BZETR22M11	IHLP2020CZETR47M11	IHLP2020CZET100M11	IHLP2020CZET1R5M11
IHLP2020CZET5R6M11	IHLP2020BZETR22M11	IHLP2020BZETR47M11	IHLP2020BZET3R3M11