

Heavy Duty Terminal Blocks

1600 Series

600 Volts AC/DC (UL/CSA)

Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Connector, Brass, Nickel Plated
- Phil-Slot Screws standard (slotted screws also available), Brass, Nickel Plated, 10-32
- Current rated up to 30 Amps with unprepared wire, #10-22 AWG Copper
- Current rated up to 75 Amps when wired with crimp type ring, spade or fork terminal
- 21/32" (.65625") Line To Line Spacing
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- **CE** - 1000 Volts
- RoHS Compliant



1604 H



1606 STD

Heavy Duty Terminal Blocks

# of Poles	Catalog #								Dimensions		Clear Cover	White Cover
	A	B										
2	1602 MCJ	1602 STD	1602 DJ	1602 DJSV	1602 ST	1602 SC	1602 H	2.44	1.78	CC 1602	CW 1602	
4	1604 MCJ	1604 STD	1604 DJ	1604 DJSV	1604 ST	1604 SC	1604 H	3.75	3.09	CC 1604	CW 1604	
6	1606 MCJ	1606 STD	1606 DJ	1606 DJSV	1606 ST	1606 SC	1606 H	5.06	4.41	CC 1606	CW 1606	
8	1608 MCJ	1608 STD	1608 DJ	1608 DJSV	1608 ST	1608 SC	1608 H	6.38	5.72	CC 1608	CW 1608	
12	1612 MCJ	1612 STD	1612 DJ	1612 DJSV	1612 ST	1612 SC	1612 H	9.00	8.34	CC 1610	CW 1610	

See page 35 for DIN Rail Adapter

mm = dim X 25.4

<p>16XX MCJ Multiple Circuit Jumper</p>	<p>16XX STD Standard Connector with Serrations for Anti-Rotation</p>	<p>16XX DJ Removable Connector with Brass Insert</p>	<p>16XX DJSV Removable Connector with Brass Insert, Removable Cover</p>	<p>16XX ST* 10-32 Stud, Removable Connector</p>	<p>16XX SC Short Circuiting Bar with Brass Insert, 4 Shorting Pins per Block</p>	<p>16XX H Standard Connector with Hinge Cover</p>
--	---	---	--	--	---	--

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

* STRC: 10-32 Stud with Riveted Connector

