

RM 8, RM 8 LP Cores and accessories

Series/Type: B65811, B65812

Date: June 2013

EPCOS AG is a TDK Group Company.

<sup>©</sup> EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.



## **Core and accessories**

	Individual parts	Part no.	Page
	Adjusting screw	B65812	10
	Core	B65811	3
	Clamps	B65812	9
	Insulating washer 1	B65812	9
	Coil former	B65812	5, 6
	Core	B65811	3
	Threaded sleeve (glued-in)		
3000	Insulating washer 2	B65812	9
FRM0051-5 Example of an assembly set			
Also available:	Coil former for SMPS transformers Coil former for	B65812	7
	power applications	B65812	8
	RM 8 low-profile:		
	Core	B65811P	11
	Clamp	B65812	12
	Insulating washers 1 + 2	B65812	12



Core B65811


- To IEC 62317-4
- Cores without center hole for transformer applications
- Delivery mode: sets

## Magnetic characteristics (per set)

	with center hole	without center hole	
ΣI/A	0.68	0.59	mm <sup>-1</sup>
l <sub>e</sub>	35.1	38	mm
l <sub>e</sub> A <sub>e</sub> A <sub>min</sub>	52	64	mm <sup>2</sup>
$A_{min}$	_	55	mm <sup>2</sup>
$V_e$	1825	2430	mm <sup>3</sup>

## Approx. weight (per set)

m	10.7	12	g



## Gapped

Material	A <sub>L</sub> value	S	$\mu_{e}$	Ordering code <sup>1)</sup> -D with center hole
		approx.		-F with threaded sleeve
	nH	mm		-J without center hole
N48	250 ± 3%	0.23	134	B65811+0250A048
	315 ± 3%	0.17	169	B65811+0315A048
	400 ± 3%	0.14	215	B65811+0400A048
	630 ± 5%	0.10	338	B65811+0630J048
N41	160 ± 3%	0.49	76	B65811J0160A041
	250 ± 5%	0.24	118	B65811J0250J041
	630 ± 5%	0.11	298	B65811J0630J041
	1600 ±10%	0.04	756	B65811J1600K041
N87	250 ± 3%	0.30	118	B65811J0250A087
	400 ± 3%	0.18	189	B65811J0400A087

<sup>1)</sup> Replace the + by the code letter "F" or "D" for the required version. Standard version is "D".



RM 8
Core B65811

# **Ungapped**

Material	A <sub>L</sub> value	$\mu_{e}$	P <sub>V</sub>	Ordering code -D with center hole
	nH		W/set	-J without center hole
N48	2900 +30/–20%	1550		B65811D0000R048
N30	5700 +30/–20%	2690		B65811J0000R030
T38	12500 +40/–30%	5910		B65811J0000Y038
N49	2200 +30/–20%	1040	< 0.37 ( 50 mT, 500 kHz, 100 °C)	B65811J0000R049
N87	3300 +30/–20%	1560	< 1.20 (200 mT, 100 kHz, 100 °C)	B65811J0000R087
N97	3300 +30/–20%	1560	< 1.00 (200 mT, 100 kHz, 100 °C)	B65811J0000R097
N41	4100 +30/–20%	1940	< 0.37 (200 mT, 25 kHz, 100 °C)	B65811J0000R041



Accessories B65812

#### Coil former, squared pins

Material: GFR thermosetting plastic (UL 94 V-0, insulation class to IEC 60085:

H 

max. operating temperature 180 °C), color code black

Sumikon PM 9630® [E41429 (M)], SUMITOMO BAKELITE CO LTD

Solderability: to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s


Resistance to soldering heat: to IEC 60068-2-20, test Tb, method 1B: 350 °C, 3.5 s

Winding: see Data Book 2013, chapter "Processing notes, 2.1"

For matching clamp and insulating washers see page 9.

Sections	A <sub>N</sub> mm <sup>2</sup>	I <sub>N</sub> mm	$A_R$ value $\mu\Omega$	Pins	Ordering code
1	30	42	47	5 8 12	B65812N1005D001 B65812N1008D001 B65812N1012D001
2	28.4	42	50	5 12	B65812N1005D002 B65812N1012D002

12 pins



 Version
 Pins omitted

 5 pins
 3, 4, 6, 7, 9, 10, 12

 8 pins
 3, 4, 9, 10



Accessories B65812

#### Coil former, pins squared in the start-of-winding area

Material: GFR thermosetting plastic (UL 94 V-0, insulation class to IEC 60085:

H 

max. operating temperature 180 °C), color code white

Bakelite UP 3420® [E61040 (M)], HEXION SPECIALTY CHEMICALS GMBH


Solderability: to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s

Resistance to soldering heat: to IEC 60068-2-20, test Tb, method 1B: 350 °C, 3.5 s

Winding: see Data Book 2013, chapter "Processing notes, 2.1"

For matching clamp and insulating washers see page 9.

Sections	A <sub>N</sub> mm <sup>2</sup>	I <sub>N</sub> mm	$A_R$ value $\mu\Omega$	Pins	Ordering code
1	30	42	47	5 8 12	B65812P1005D001 B65812P1008D001 B65812P1012D001
2	28.4	42	50	8	B65812P1008D002



Version	Pins omitted		
5 pins	3, 4, 6, 7, 9, 10, 12		
8 pins	3, 4, 9, 10		



Accessories B65812

#### Coil former for SMPS transformers with line isolation

The creepage distances and clearances are designed such that the coil former is suitable for use in SMPS transformers with line isolation.

- Closed center flange with external wire guide
- Pins squared in the start-of-winding area
- Optimized for use with automatic winding machines

Material: GFR thermosetting plastic (UL 94 V-0, insulation class to IEC 60085:

F 

max. operating temperature 180 °C), color code black


Sumikon PM 9630® [E41429 (M)], SUMITOMO BAKELITE CO LTD

Solderability: to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s

Resistance to soldering heat: to IEC 60068-2-20, test Tb, method 1B: 350 °C, 3.5 s

Winding: see Data Book 2013, chapter "Processing notes, 2.1"

Sections	A <sub>N</sub> mm <sup>2</sup>	I <sub>N</sub> mm	$A_R$ value $\mu\Omega$	Pins	Ordering code
2	28.4	42	50	8	B65812S1108D002





Accessories B65812

#### Coil former for power applications

Optimized for automatic winding

Material: GFR polyterephthalate (UL 94 V-0, insulation class to IEC 60085:

F 

max. operating temperature 155 °C), color code black

Valox 420-SE0® [E45329 (M)], GE PLASTICS B V


Solderability: to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s

Resistance to soldering heat: to IEC 60068-2-20, test Tb, method 1B: 350 °C, 3.5 s

Winding: see Data Book 2013, chapter "Processing notes, 2.1"

For matching clamp and insulating washer 1 see page 9.

Sections	A <sub>N</sub> mm <sup>2</sup>	I <sub>N</sub> mm	$A_R$ value $\mu\Omega$	Pins	Ordering code
1	30	42	47	12	B65812C1512T001



Hole arrangement View in mounting direction (Note half pitch!)



Accessories B65812

#### Clamp

- With ground terminal, made of stainless spring steel (tinned), 0.4 mm thick
- Solderability to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s
- Also available as strip clamp on reels on request

#### Insulating washer 1 between core and coil former


- For tolerance compensation and for insulation
- Made of polycarbonate (UL 94 V-0, insulation class to IEC 60085: E 120 °C), 0.08 mm thick Aryphan F685, [E167358 (M)], natural color, LOFO HIGH TECH FILM GMBH

#### Insulating washer 2 for double-clad PCBs


■ Made of polycarbonate (UL 94 V-0, insulation class to IEC 60085: E 120 °C), 0.25 mm thick Makrofol FR7-2, [E118859 (M)], natural color, BAYER MATERIALSCIENCE AG


	Ordering code
Clamp (ordering code per piece, 2 are required)	B65812A2203X000
Insulating washer 1 (reel packing, PU = 1 reel)	B65812A5000X000
Insulating washer 2 (bulk)	B65812C2005X000

#### Clamp




# Insulating washer 1 (preliminary data)





#### **Insulating washer 2**






RM 8
Accessories
B65812

## **Adjusting screw**

■ Tube core with thread and core brake made of GFR polyterephthalate Pocan B3235® [E245249 (M)], LANXESS AG

Tube core ∅ × length (mm)	Material	Color code	Ordering code
3.85 × 5.0	N22	gray	B65812B3003X022





## RM 8 »Low Profile«

Core B65811P

■ To IEC 62317-4

■ For compact transformers

■ Without center hole

■ Delivery mode: sets

## Magnetic characteristics (per set)

 $\Sigma I/A = 0.44 \text{ mm}^{-1}$ 


 $I_{e} = 28.7 \text{ mm}$ 

 $A_e = 64.9 \text{ mm}^2$ 

 $A_{min} = 55.4 \text{ mm}^2$ 

 $V_e = 1860 \text{ mm}^3$ 

## Approx. weight 9.2 g/set



## **Ungapped**

Material	A <sub>L</sub> value	μ <sub>e</sub>	P <sub>V</sub>	Ordering code
	nH		W/set	
N49	2900 +30/–20%	1020	< 0.33 ( 50 mT, 500 kHz, 100 °C)	B65811P0000R049
N92	3100 +30/–20%	1090	< 1.10 (200 mT, 100 kHz, 100 °C)	B65811P0000R092
N87	4100 +30/–20%	1440	< 0.92 (200 mT, 100 kHz, 100 °C)	B65811P0000R087



#### RM 8 »Low Profile«

Accessories B65812

#### Clamp

- With ground terminal, made of stainless spring steel (tinned), 0.4 mm thick
- Solderability to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s
- Also available as strip clamp on reels on request

### Insulating washer 1 between core and coil former


- For tolerance compensation and for insulation
- Made of polycarbonate (UL 94 V-0, insulation class to IEC 60085: E 120 °C), 0.08 mm thick Aryphan F685, [E167358 (M)], natural color, LOFO HIGH TECH FILM GMBH

#### Insulating washer 2 for double-clad PCBs


■ Made of polycarbonate (UL 94 V-0, insulation class to IEC 60085: E 120 °C), 0.25 mm thick Makrofol FR7-2, [E118859 (M)], natural color, BAYER MATERIALSCIENCE AG


	Ordering code
Clamp (ordering code per piece, 2 are required)	B65812P2203X000
Insulating washer 1 (reel packing, PU = 1 reel)	B65812A5000X000
Insulating washer 2 (bulk)	B65812C2005X000

#### Clamp




# Insulating washer 1 (preliminary data)





#### **Insulating washer 2**





#### **Cautions and warnings**

#### Mechanical stress and mounting

Ferrite cores have to meet mechanical requirements during assembling and for a growing number of applications. Since ferrites are ceramic materials one has to be aware of the special behavior under mechanical load.

As valid for any ceramic material, ferrite cores are brittle and sensitive to any shock, fast changing or tensile load. Especially high cooling rates under ultrasonic cleaning and high static or cyclic loads can cause cracks or failure of the ferrite cores.

For detailed information see chapter "Definitions", section 8.1.

#### Effects of core combination on A<sub>1</sub> value

Stresses in the core affect not only the mechanical but also the magnetic properties. It is apparent that the initial permeability is dependent on the stress state of the core. The higher the stresses are in the core, the lower is the value for the initial permeability. Thus the embedding medium should have the greatest possible elasticity.

For detailed information see chapter "Definitions", section 8.2.

#### Heating up

Ferrites can run hot during operation at higher flux densities and higher frequencies.

#### NiZn-materials

The magnetic properties of NiZn-materials can change irreversible in high magnetic fields.

#### **Processing notes**

- The start of the winding process should be soft. Else the flanges may be destroid.
- To strong winding forces may blast the flanges or squeeze the tube that the cores can no more be mount.
- To long soldering time at high temperature (>300 °C) may effect coplanarity or pin arrangement.
- Not following the processing notes for soldering of the J-leg terminals may cause solderability problems at the transformer because of pollution with Sn oxyd of the tin bath or burned insulation of the wire. For detailed information see chapter "Processing notes", section 8.2.
- The dimensions of the hole arrangement have fixed values and should be understood as a recommendation for drilling the printed circuit board. For dimensioning the pins, the group of holes can only be seen under certain conditions, as they fit into the given hole arrangement. To avoid problems when mounting the transformer, the manufacturing tolerances for positioning the customers' drilling process must be considered by increasing the hole diameter.



# Symbols and terms

Symbol	Meaning	Unit
A	Cross section of coil	mm <sup>2</sup>
$A_{e}$	Effective magnetic cross section	mm <sup>2</sup>
$A_L$	Inductance factor; $A_L = L/N^2$	nH
$A_{L1}$	Minimum inductance at defined high saturation ( $\triangleq \mu_a$ )	nH
A <sub>min</sub>	Minimum core cross section	mm <sup>2</sup>
A <sub>N</sub>	Winding cross section	mm <sup>2</sup>
A <sub>R</sub>	Resistance factor; $A_R = R_{Cu}/N^2$	$\mu\Omega = 10^{-6} \Omega$
В	RMS value of magnetic flux density	Vs/m <sup>2</sup> , mT
ΔΒ	Flux density deviation	Vs/m², mT
Ê	Peak value of magnetic flux density	Vs/m <sup>2</sup> , mT
ΔÂ	Peak value of flux density deviation	Vs/m <sup>2</sup> , mT
$B_{DC}$	DC magnetic flux density	Vs/m², mT
B <sub>R</sub>	Remanent flux density	Vs/m <sup>2</sup> , mT
B <sub>S</sub>	Saturation magnetization	Vs/m <sup>2</sup> , mT
$C_0$	Winding capacitance	F = As/V
CDF	Core distortion factor	mm <sup>-4.5</sup>
DF	Relative disaccommodation coefficient DF = $d/\mu_i$	
d	Disaccommodation coefficient	
Ea	Activation energy	J
f	Frequency	s <sup>-1</sup> , Hz
f <sub>cutoff</sub>	Cut-off frequency	s <sup>-1</sup> , Hz
f <sub>max</sub>	Upper frequency limit	s <sup>-1</sup> , Hz
f <sub>min</sub>	Lower frequency limit	s <sup>−1</sup> , Hz
f <sub>r</sub>	Resonance frequency	s <sup>-1</sup> , Hz
f <sub>Cu</sub>	Copper filling factor	
g	Air gap	mm
Н	RMS value of magnetic field strength	A/m
Ĥ	Peak value of magnetic field strength	A/m
$H_{DC}$	DC field strength	A/m
H <sub>c</sub>	Coercive field strength	A/m
h	Hysteresis coefficient of material	10 <sup>-6</sup> cm/A
h/μ <sub>i</sub> ²	Relative hysteresis coefficient	10 <sup>-6</sup> cm/A
1	RMS value of current	Α
$I_{DC}$	Direct current	Α
î	Peak value of current	Α
J	Polarization	Vs/m <sup>2</sup>
k	Boltzmann constant	J/K
k <sub>3</sub>	Third harmonic distortion	
k <sub>3c</sub>	Circuit third harmonic distortion	
L	Inductance	H = Vs/A



# Symbols and terms


Symbol	Meaning	Unit
$\Delta$ L/L	Relative inductance change	Н
$L_0$	Inductance of coil without core	Н
L <sub>H</sub>	Main inductance	Н
L <sub>p</sub>	Parallel inductance	Н
L <sub>rev</sub>	Reversible inductance	Н
L <sub>s</sub>	Series inductance	Н
l <sub>e</sub>	Effective magnetic path length	mm
I <sub>N</sub>	Average length of turn	mm
N	Number of turns	
$P_{Cu}$	Copper (winding) losses	W
P <sub>trans</sub>	Transferrable power	W
P <sub>V</sub>	Relative core losses	mW/g
PF	Performance factor	Ŭ
Q	Quality factor (Q = $\omega L/R_s = 1/\tan \delta_L$ )	
R	Resistance	$\Omega$
R <sub>Cu</sub>	Copper (winding) resistance (f = 0)	$\Omega$
R <sub>h</sub>	Hysteresis loss resistance of a core	$\Omega$
$\Delta R_h$	R <sub>h</sub> change	$\Omega$
R <sub>i</sub>	Internal resistance	$\Omega$
R <sub>p</sub>	Parallel loss resistance of a core	$\Omega$
R <sub>s</sub>	Series loss resistance of a core	$\Omega$
R <sub>th</sub>	Thermal resistance	K/W
R <sub>V</sub>	Effective loss resistance of a core	$\Omega$
S	Total air gap	mm
T	Temperature	°C
ΔT	Temperature difference	K
-	Curie temperature	°C
I <sub>C</sub> t	Time	s
t <sub>v</sub>	Pulse duty factor	
tan $\delta$	Loss factor	
$\tan \delta_{L}$	Loss factor of coil	
$\tan \delta_{r}$	(Residual) loss factor at $H \rightarrow 0$	
$\tan \delta_{\rm r}$ $\tan \delta_{\rm e}$	Relative loss factor	
•	Hysteresis loss factor	
tan $\delta_h$	Relative loss factor of material at $H \rightarrow 0$	
tan $\delta/\mu_i$		V
Û	RMS value of voltage	V
_	Peak value of voltage	mm <sup>3</sup>
V <sub>e</sub>	Effective magnetic volume	
Z	Complex impedance	$\Omega$
$Z_n$	Normalized impedance $ Z _n =  Z /N^2 \times \varepsilon ( e /A_e)$	$\Omega$ /mm



# Symbols and terms

Symbol	Meaning		
α	Temperature coefficient (TK)		
$\alpha_{F}$	Relative temperature coefficient of material	1/K	
$\alpha_{e}$	Temperature coefficient of effective permeability	1/K	
r	Relative permittivity		
Þ	Magnetic flux		
1	Efficiency of a transformer		
lB	Hysteresis material constant	mT-1	
li	Hysteresis core constant	$A^{-1}H^{-1/2}$	
'S	Magnetostriction at saturation magnetization		
,	Relative complex permeability		
0	Magnetic field constant	Vs/Am	
a	Relative amplitude permeability		
арр	Relative apparent permeability		
е	Relative effective permeability		
i	Relative initial permeability		
ρ <sup>'</sup>	Relative real (inductive) component of $\overline{\mu}$ (for parallel components)		
p	Relative imaginary (loss) component of $\overline{\mu}$ (for parallel components)		
r	Relative permeability		
rev	Relative reversible permeability		
S S	Relative real (inductive) component of $\overline{\mu}$ (for series components)		
s S	Relative imaginary (loss) component of $\overline{\mu}$ (for series components)		
tot	Relative total permeability		
	derived from the static magnetization curve		
	Resistivity	$\Omega$ m $^{-1}$	
I/A	Magnetic form factor	mm <sup>-1</sup>	
Cu	DC time constant $\tau_{Cu} = L/R_{Cu} = A_L/A_R$	s	
)	Angular frequency; $\omega$ = 2 $\Pi$ f	s <sup>-1</sup>	

All dimensions are given in mm.





#### Important notes

The following applies to all products named in this publication:

- Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.