


ASS'Y P/N	<u>CONTACTS</u>	<u>HOLE POS.</u> <u>CLOSED</u>
W4282-10PG-300	10 - #20	11, 12
W4282-11PG-300	11 - #20	12
W4282-12PG-300	12 - #20	NONE
W4282-1 <u>X</u> PG-300		

-NO. OF CONTACTS



WIRE VIEW W4282-10PG-300 - 10-POS. (11&12 CLOSED) W4282-11PG-300 - 11-POS. (12 CLOSED) W4282-12PG-300 - 12-POS. (ALL OPEN)

	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1					
V.	INIT.	DATE	DESCRIPTION					
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONKALL CORPORATION" UNAUTHORIZED UPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ate: 10/07/14					
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS 4.005 ANGLES 11* FRACTIONS 1/1/6					601 E. WILDWOOD VILLA PARK, IL 60181			
		APPROVED BY:			TITLE: PANEL PIN, E-KEY #20 SOLDER, 12-POS. PATTERN			
		scale NTS	size B	sheet 1 OF 1	MULTI-CON-X, WEATHER RESISTANT customer: STANDARD PRODUCT			
		FILE: DIRECTORY: W4282-1XPG-300 SLW			NUMBER: W4282-1XPG-300	REV A		