

Adafruit DotStar Digital LED Strip - White 60 LED - Per Meter - WHITE

PRODUCT ID: 2240

Select Length

[Learn about the benefits of ordering full reels](#)

IN STOCK

ADD TO CART

1-9

10-99

100+

ADD TO WISHLIST

DESCRIPTION

TECHNICAL DETAILS



DESCRIPTION

Move over NeoPixels, there's a new LED strip in town! These fancy new DotStar LED strips are a great upgrade for people who have loved and used NeoPixel strips for a few years but want something even better. DotStar LEDs use generic 2-wire SPI, so you can push data much faster than with the NeoPixel 800 KHz protocol and there's no specific timing required. They also have much higher PWM refresh rates, so you can do Persistence-of-Vision (POV) and have less flickering, particularly at low brightness levels.

Like NeoPixels, DotStar LEDs are 5050-sized LEDs with an embedded microcontroller **inside the LED**. You can set the color/brightness of each LED to 24-bit color (8 bits each red green and blue). Each LED acts like a shift register, reading incoming color data on the input pins, and then shifting the previous color data out on the output pin. By sending a long string of data, you can control an infinite number of LEDs, just tack on more or cut off unwanted LEDs at the end. The PWM is built into each LED-chip so once you set the color you can stop talking to the strip and it will continue to PWM all the LEDs for you

However, unlike NeoPixels, these LEDs have 2 wires (input and output) for sending data - one clock pin and one data pin. That means you need two pins, not one, to control DotStars.

Because the clock and data is seperated, you can use any processor speed or type to control these strips, and you don't have to worry about being careful with the timing.

Hardware SPI support is handy but not required. This makes them excellent for use with any microcontroller or microprocessor, including Arduino, Raspberry Pi, BeagleBone, Propeller, SparkCore, and any 'raw' microcontrollers/microprocessors. It's very easy to port the library, and you can send data to the pixels at up to 32MHz clock rate!

Another nice thing about DotStars is their high PWM rate. You only have to set the 24-bit color data for each pixel LED once, and then the LED+built-in-chip will handle the PWMing of the red, green and blue. On NeoPixels, this PWM rate happens 400 Hz, which works well but is noticeably at lower brightnesses and if the strip is moving in any way. DotStars have a 20 KHz PWM rate, so even when moving the strip around, you won't see the pixelation, the color blending is very smooth.

This is the 60 LED-per-meter version of our DotStar strips, on white flex PCB. [We have 30 LED/m, 60 LED/m and 144 LED/m on both white and black flex PCB.](#)

The strip is made of flexible PCB material, and comes with a weatherproof sheathing. You can cut this stuff pretty easily with wire cutters, there are cut-lines every 0.65"/1.7cm (1 LED each). Solder to the 0.1" copper pads and you're good to go. Of course, you can also connect strips together to make them longer, just watch how much current you need! [We have a 5V/2A supply that should be able to drive 1 meter](#), a [5V/4A that can drive a couple meters](#), and a [5V/10A supply that can drive up to 10 meters](#) (depending on use) **You must use a 5V DC power supply to power these strips, do not use higher than 6V or you can destroy the entire strip**

These strips come in 4 meter reels with a [4-pin JST SM connector](#) on each end. These strips are **sold by the meter!** If you buy 4 meters at a time, you'll get full reels with two connectors. If you buy less than 4m, you'll get a single strip, but it will be a cut piece from a reel **which may or may not have a connector on it**. If the piece comes from the end of the reel, the connector may be on the output end of the strip!

To wire up these strips we suggest picking up some [JST SM plug and receptacle cables](#) for the signal wires [For the power wires, you will also probably want a 2.1mm DC jack to wire in so you can connect one of our 5V wall adapters to power it.](#)

[We have a tutorial showing wiring, power usage calculations, example code for usage, etc. Please check it out!](#)

TECHNICAL DETAILS

- The manufacturer of the APA102C smart LED used in this strip used to be **DOTSTAR_GRB** order, and has changed in 2015 to have **DOTSTAR_BRG** color order and then in 2017 to **DOTSTAR_BGR** . This means if you are using our DotStar library, you'll need to change the initialization to tell it which you are using. Check the tutorial for details on how to do this! The LED colors are otherwise identical, you just have to pipe the data to it in a slightly different order.

Technical specs (for the strips):

- Width (with weatherstripping): 14mm / 0.55"
- Width (w/o weatherstripping): 12.7mm / 0.5"
- Thickness (with weatherstripping): 4mm / 0.16"
- 60 LEDs per meter
- Pixel pitch: 16.65mm / 0.65" between LEDs
- Operating temperature: -40°C - 40°C
- Storage temperature: -10°C - 50°C

Technical specs (for the LEDs):

- [SK9822 Datasheet](#)
- Light source: Epistar 5050 SMD LEDs
- LED Brightness: Red ~600mcd, Green ~500mcd, Blue ~150mcd
- Beam angle: ~160°
- Max current draw **per RGB LED**: ~60mA (20mA max per Red, Green & Blue LED)

Note: Strips come with 4 solder points per segment, but the arrangement may vary depending on the supplier, so please check when soldering/powering!

[We have a tutorial showing wiring, power usage calculations, example code for usage, etc. Please check it out!](#)



LEARN



[Adafruit DotStar LEDs](#)

Imagine NeoPixels with a double shot of espresso...




[DotStar Belly Dance Fans](#)

Dance like the Magical Stardust Pixie You Are



[LIGHTSHIP: LED Animation over WiFi](#)

Any sufficiently advanced technology is indistinguishable from magic.



[Adafruit Class Library for Windows IoT Core](#)

Windows IoT Drivers for Adafruit Products!

MAY WE ALSO SUGGEST...



Adafruit DotStar Digital LED



Adafruit DotStar Digital LED



Adafruit DotStar Digital LED



Adafruit DotStar Digital LED




Adafruit DotStar Digital LED



Adafruit DotStar LED Strip -



Adafruit DotStar LED Strip -




DotStar Addressable 5050



DotStar RGB LED Disk -



Adafruit DotStar LED Strip -



DotStar Addressable 5050



Adafruit DotStar Digital LED

DISTRIBUTORS [EXPAND TO SEE DISTRIBUTORS](#)

[CONTACT](#)

[SUPPORT](#)

[DISTRIBUTORS](#)

[EDUCATORS](#)

[JOBS](#)

[FAQ](#)

[SHIPPING & RETURNS](#)

[TERMS OF SERVICE](#)

[PRIVACY & LEGAL](#)

[ABOUT US](#)

"Human history becomes more and more a race between education and catastrophe" - H. G. Wells

ENGINEERED IN NYC Adafuit®



4.9 ★★★★★
Google
Customer Reviews