

# 2000 Slide Switches - Snap-in & 2 hole fixing 10A 250Vac



- ▶ 2 way 'voltage selector'
- ▶ Ratings up to 10A, 250V ac
- ▶ Snap in and flange mounting
- ▶ PCB & solder terminals
- ▶ 2 and 3 position
- ▶ Choice of circuits
- ▶ Choice of actuators



10 A 250Vac T85  
6(3)A 250Vac T85



UL CSA 16A 250Vac Non Inductive  
UL CSA 4A 300Vac  
UL65°C, file no. E45221, CSA file no. LR10990



RoHS compliant


μ contact gap

Please specify: Standard action (SP116) or light action (SP118).  
2000 series lubrication is inorganic and does not degrade plastics.

Technical data on pages 4 & 5.

115/230 is preferred legend

**B** BLACK  
**W** WHITE  
**R** RED



## ORDER FORMAT

▶ TERMINAL	▶ SERIES	▶ POS'N	▶ CIRCUIT <small>Viewed from back</small>	▶ SLIDER																	
<p><b>K</b></p> <p>2.8 x 0.8</p> <p><b>R</b></p> <p>2.8 x 0.8</p> <p><b>T</b></p> <p>Solder</p> <p><b>X</b></p> <p>PCB 0.8 Sq. For mounting stability switches have extra "support" terminals</p> <p>* Nominal - Dimension varies with body type. For exact figure call factory</p>	2	Switching positions	10	0	6	C	L	S	2	7	D	M	T								
			20	2	3	8	E	N													
			30	4	9	H	P														
			40	5	A	K	R														
3	Switching positions	10	3	4	9	H	P														
		20	4	9	H	P															
		30	5	A	K	R															
		40	5	A	K	R															



T22208E



T22308E



T2230MF



T22205B




T22305B




T23204B

**BODY**

**B** With fixing holes




**E** Snap-in



Cut-outs must be punched in the direction of insertion

**F** Snap-in (single pole ON OFF only)



Cut-outs must be punched in the direction of insertion

**OPTIONS**


**Color**

For custom slider colors call the factory. A full range is available for large orders

Standard body color is black

**Legend printing**

2 Frequently requested legends are shown




**436( ) 437( )**

( ) is legend color  
(B) - Black  
(W) - White  
(R) - Red

Please call the factory for custom legends


**DIMENSIONS (mm)**

**2 Pos B**





**Cut-out / PCB Matrix**

**3 Pos B**





**2 Pos E**



Panel thickness	Dim. Y
0.8-1.2	29.75/29.85
1.63	30.15/30.25
2.0	30.35/30.45
2.5	30.55/30.65

**2 Pos F**



Panel thickness	Dim. Y
0.8-1.2	29.75/29.85
1.63	30.15/30.25
2.0	30.35/30.45
2.5	30.55/30.65

for PCB, call factory for details